



Better tools for the job


Switch to Tork Industrial wipers and cloths



35%
Less time

31%
Less effort

40%
Less solvent*
Compared to rags



It's time to stop cleaning present-day equipment with tools from the past.

Your engineers and MRO crew are responsible for some of the most advanced maintenance jobs in the world and every second counts. Aircraft, spacecraft, watercraft and railed vehicle checks demand thousands of man-hours. Working with outdated tools like rags can steal valuable time.




Tork Industrial wipers are the next generation of industrial cleaning tools, engineered and tested to cope with the world's highest safety standards and efficiency goals. Compared to rags, they are designed for the job and consistent in quality, making cleaning and wiping easier and more efficient.

It's time to put rags where they belong – in the past.



Increase speed of service with faster cleaning

- Tork exelCLEAN® patented foam-spun technology, gives you quicker and more professional cleaning results
- Tork wipers are highly absorbent, durable enough for repeated use and withstand some of the toughest solvents without tearing or falling apart
- Tork wiping paper with QuickDry is stronger when wet and more absorbent than ordinary paper. Ideal for dealing with tough dirt, lubricants and grease




Improve workstation efficiency

- Tork dispensers keep the workplace organised and processes streamlined by delivering wipers in controlled amounts, directly to the point of use
- Portable and mobile dispensers allow you to keep wipers nearby, minimising downtime



Improve crew safety

- Tork wipers have consistent quality and size, contain no chemical residues or stains from pre-usage and do not have frayed edges that could catch in a machine
- OHS friendly Tork dispensers are designed for single-hand dispensing and can be installed at an ideal height-within-reach range to limit bending down
- Easy handling packaging makes Tork products easier to carry, handle and store



Easy to refill and check when needed

Wall mountable with magnets

Economical single wipe dispensing

W4

W4

W1

W1



Optimal height at 1m and one-hand dispensing with no need to bend

Bin liner for easy waste disposal

Portable dispenser is easy to move to where it's needed

Safe and stable when dispensing

MRO Task identifier

Absorbency

Strength

Technology

Spills & mess

Glass cleaning

Oil/grease

Rough surfaces

Delicate surfaces


Wiping – Limited use - mopping up spills, soaking up liquids and picking up dirt and dust with paper

Tork Industrial Heavy-Duty Wiping Paper 3 Ply	<div></div>	<div></div>	<div></div>	<div></div>	<div></div>	<div></div>	<div></div>	<div></div>
---	-------------	-------------	-------------	-------------	-------------	-------------	-------------	-------------



Cleaning – Repeated use - removing dirt and stains with non-woven cloths that are dry or used with water, solvents or detergent

Tork Cleaning Cloth – 510	<div></div>	<div></div>	<div></div>	<div></div>		<div></div>	<div></div>	<div></div>
Tork Heavy-Duty Cleaning Cloth – 530	<div></div>	<div></div>	<div></div>	<div></div>		<div></div>	<div></div>	
Tork Industrial Heavy-Duty Cleaning Cloth – 570	<div></div>	<div></div>	<div></div>	<div></div>		<div></div>	<div></div>	
Tork Long-Lasting Cleaning Cloth – Specialist	<div></div>	<div></div>				<div></div>	<div></div>	<div></div>
Tork Industrial Low-Lint Cleaning Cloth – Specialist	<div></div>	<div></div>				<div></div>		<div></div>



✈️ AMS 3819C

Aerospace Material Standard, SAE

An Independently measured Standard developed by The Society of Automotive Engineers as an alternative to BMS. Evaluates the strength of the wiper and how it works.













- Includes physical testing of wiper properties (weight, absorption, linting, integrity, chemical test, pH of material), how strong it is, how much it absorbs and how it performs
- Only white wipers are accepted for certifications


















✈️ BMS 15-5G

Boeing Manufacturing Standard

Boeing Standard includes chemical testing - how wipers work with a number of different chemicals, if they contain silicone and oils, and how they work with solvents

- Also shows indication of linting

Solvents/ detergents	Lint property rating	Max working temperature	Anti-static properties ESD protective, SP method 2472	ASTM Tested for solvent suitability	AMS Certified AMS 3819C	BMS Certified BMS 15-5G	Task	Area of use example
								
●	Low					Grade B	Wiping	    

Products									
●	●	●	●	●	●	●	●	●	●
●	Low	250°C				Grade A	Transport presentation services	   	
●	Low	250°C		●		Grade A	General maintenance of engines and aircraft frame	    	
●	Low	250°C				Grade A	Armoury or weaponry maintenance	   	
●	Extremely low	250°C		●	Grade A	Grade A	Paint stripping or interiors	 	
●	Extremely low	120°C	●	●			Fuel tanks & aeronautical electronics	 	

Tork wiper recommendations

Tork wipers and cloths are designed with different capabilities for a wide range of tasks, specifically for your MRO crew. When they're combined with our modern and convenient dispensers you get an efficient, well-organised work environment that inspires productivity and improves quality.

-  Aerospace
-  Rail
-  Defence Industries
-  Marine
-  Oil & Gas
-  Transportation



130081




130082

130083

- QuickDry technology means better absorption and strength for more demanding tasks
- Extra thick paper protects hand from heat, dirt and metal scraps
- Aviation certified



Tork Industrial Heavy-Duty Wiping Paper

Article number	Product name	Dispenser system	Technology	Ply	Material	Colour	Format	Size L x W	Per case
130081	Tork Industrial Heavy-Duty Wiping Paper	W1/W2	QuickDry	3	Virgin/Perf	 Blue	Combi Roll	34cm x 23cm	700w
130082	Tork Industrial Heavy-Duty Wiping Paper	W4	QuickDry	3	Virgin/Perf	 Blue	Folded	32cm x 38cm	500w
130083	Tork Industrial Heavy-Duty Wiping Paper	Handy Box	QuickDry	3	Virgin/Perf	 Blue	Folded	32cm x 38cm	200w



510478

510104

510137

510150

- Quickly absorb oils and liquids, making your cleaning effort easier
- Light and flexible to clean corners and into confined spaces
- Aviation certified, soft and non-scratching cloths, suitable for cleaning delicate surfaces



Tork Cleaning Cloths (510)

Article number	Product name	Dispenser system	Technology	Ply	Material	Colour	Format	Size L x W	Per case
510478	Tork Cleaning Cloth	W4	exelCLEAN	1	Non-Woven	White	Folded	43cm x 35.5cm	650c
510104	Tork Cleaning Cloth	W1	exelCLEAN	1	Non-Woven/Perf	White	Roll	38cm x 43cm	1,000c
510137	Tork Cleaning Cloth	W1/W2/W3	exelCLEAN	1	Non-Woven/Perf	White	Combi Roll	38cm x 32cm	400c
510150	Tork Cleaning Cloth	W8	exelCLEAN	1	Non-Woven	White	Folded	38.5cm x 32cm	440c



530178



530177



530137



530175



530150

- Multi-purpose cloth which is strong and absorbent to handle heavy-duty tasks
- Works well with most solvents and withstands hard-scrubbing without falling apart
- Low linting and aviation certified



Tork Heavy Duty Cloths (530)

Article number	Product name	Dispenser system	Technology	Ply	Material	Colour	Format	Size L x W	Per case
530178	Tork Heavy Duty Cleaning Cloth	W4	exelCLEAN	1	Non-Woven	White	Folded	43cm x 35.5cm	500c
530177	Tork Heavy Duty Cleaning Cloth	W4	exelCLEAN	1	Non Woven	White	Folded	64cm x 35.5cm	300c
510104	Tork Heavy Duty Cleaning Cloth	W1/W2/W3	exelCLEAN	1	Non-Woven/Perf	White	Combi Roll	38cm x 32cm	280c
510137	Tork Heavy Duty Cleaning Cloth	Handy Box	exelCLEAN	1	Non-Woven	White	Folded	64cm x 38cm	120c
510150	Tork Heavy Duty Cleaning Cloth	W8	exelCLEAN	1	Non-Woven	White	Folded	38.5cm x 32cm	360c



570478



570137

- Offers superior strength and excellent cleaning efficiency - ideal for tough cleaning, degreasing and removing stubborn spots
- Works well with many chemical solvents without falling apart
- Aviation certified, thick and bulky to protect hands from heat, dirt and metal scraps



Tork Industrial Heavy Duty Cleaning Cloths (570)

Article number	Product name	Dispenser system	Technology	Ply	Material	Colour	Format	Size L x W	Per case
570478	Tork Industrial Heavy Duty Cleaning Cloth	W4	exelCLEAN	1	Non Woven	White	Folded	43cm x 35.5cm	325c
570137	Tork Industrial Heavy Duty Cleaning Cloth	W1/W2/W3	exelCLEAN	1	Non Woven/Perf	White	Combi Roll	38cm x 32cm	160c



90477



190578

- Tork Industrial Low Lint Cleaning Cloth performs best when used with oil or water-based solvents, absorbs solvent without smearing and leaves surface dust and residue-free
- Tork Long Lasting Cleaning Cloth is a good multipurpose, aviation certified, soft and flexible wipe with very limited linting



Tork Specialist Cleaning Cloths

Article number	Product name	Dispenser system	Technology	Ply	Material	Colour	Format	Size L x W	Per case
90477	Tork Long Lasting Cleaning Cloth	W4	exelCLEAN	1	Non-Woven	White	Folded	42cm x 38cm	500c
190578	Tork Industrial Low-Lint Cleaning Cloth	W4	exelCLEAN	1	100% Polypropylene	Blue	Folded	40cm x 38.5cm	400c



2316793




2316794

- Wet wipes for convenient and efficient hand and surface cleaning when water is not available



Tork Wet Wipes

Article number	Product name	Dispenser system	Technology	Ply	Material	Colour	Format	Size L x W	Per case
2316793	Tork Hand Cleaning Wet Wipes	W4		1	Non-Woven/Perf	White	Roll	30cm x 22cm	288w
2316794	Tork Surface Cleaning Wet Wipes	W4		1	Non-Woven/Perf	White	Roll	30cm x 22cm	288w



Tork Floor and Wall Mounted Dispensers & Accessories

Article number	Dispensers	System	Dispenser capacity	Colour	Material	Height	Width	Depth	Per case
652008	Tork Floor Stand	W1	1 Roll	Red/Black	Plastic/Steel	1,006mm	646mm	530mm	1
652108	Tork Wall Stand Dispenser	W1	1 Roll	Red/Black	Plastic/Steel	463mm	646mm	274mm	1
653008	Tork Maxi Centrefeed Dispenser	W2	1 Roll	Red/Black	Plastic	447mm	328mm	302mm	1
207210	Tork Combi Roll Dispenser	W3	1 Roll	Black	Plastic	360mm	285mm	390mm	1
654008	Tork Folded Wiper/Cloth Dispenser	W4	2 Packs	Red/Black	Plastic	394mm	427mm	206mm	1
206550	Tork Accessory Bin Liner Holder	W1		Black	Plastic				1
206540	Tork Accessory Magnet Kit								1 kit

For more information visit tork.com.au or tork.co.nz



Australia
Sales & Support Centre
Free phone 1800 643 634
PO Box 1580
Clayton South, Victoria 3169
customerservice@asaleocare.com

New Zealand
Sales & Support Centre
Free phone 0800 523 565
Private Bag 93-100
Henderson, Waitakere 0650
customerservice@asaleocare.com

