

Tork carbon neutral dispensers certified by

Produced with purchased certified renewable electricity and remaining carbon emissions are offset with credits from climate projects



ClimatePartner
certified product
climate-id.com/9VIUDN



Switching from Tork C-fold to **Tork PeakServe®** will help reduce waste by **28%¹**



552520
Tork PeakServe Continuous
Hand Towel Dispenser White



552528
Tork PeakServe Mini Continuous
Hand Towel Dispenser Black



552530
Tork PeakServe Mini Continuous
Hand Towel Dispenser White



552538
Tork PeakServe Mini Continuous
Hand Towel Dispenser Black



H5 PeakServe

Switching from Tork C-fold to Tork Xpress Multifold will help reduce waste by **15%⁴**



463002
Tork Xpress Multifold
Hand Towel Dispenser Stainless Steel



302030
Tork Xpress® Countertop
Multifold Hand Towel Dispenser



H2 Multifold (only image line)

Tork Coreless rolls reduces packaging by **77%²**



473200
Tork Twin Coreless Mid-size Toilet Roll
Dispenser White



473208
Tork Twin Coreless Mid-size Toilet Roll
Dispenser Black



T7 Coreless Midsize

Tork Foam Soap systems help reduce soap consumption by up to **50%³**



466000
Tork Skincare
Dispenser Stainless Steel



571501
Tork Skincare
Dispenser White



571508
Tork Skincare
Dispenser Black



S4 Skincare

Tork SmartOne® reduces toilet paper consumption by up to **40%⁵**



684000
Tork SmartOne Mini
Toilet Roll Dispenser White



685000
Tork SmartOne Twin Mini Toilet Roll
Dispenser White



684008
Tork SmartOne
Toilet Roll Dispenser Black



685008
Tork SmartOne Twin Mini Toilet Roll
Dispenser Black

T8 & T9 SmartOne



¹ Comparing average for Tork 471114 and 290265 with Tork 100589 based on weight. Internal research.

² Claim valid for Europe only. Disclaimer: As compared to the packaging weight of Tork 2ply Advanced conventional toilet paper, which includes cores and two layers of plastic packaging.

³ Essity test: Using Tork Foam vs Tork Liquid Soap in an Elevation dispenser.

⁴ Comparing average for Tork 471114 and 290265 with Tork 120289 and 471117 based on weight. Internal research.

⁵ Tork SmartOne Twin Mini dispensers compared to Traditional maxi Jumbo Dispensers. Internal research on 7729 users in Europe. Reduction accounted in square meters per visit.