


Elevate your business with sustainable hygiene management



Essity – the maker of Tork

Essity is a leading global hygiene and health company. We are dedicated to improving well-being through our products and services.

Sales are conducted in approximately 150 countries under the leading global brands TENA and Tork, and other strong brands, such as JOBST, Leukoplast, Libero, Libresse, Lotus, Nosotras, Saba, Tempo, Vinda and Zewa. Essity has about 46,000 employees.

The company's headquarters is located in Stockholm, Sweden, and Essity is listed on Nasdaq Stockholm. Essity breaks barriers to well-being and contributes to a healthy, sustainable and circular society.

More information at www.essity.com



Essity recognitions and memberships in sustainability

Sustainability Award
Silver Class 2022
S&P Global



Essity is committed to develop targets to reach net-zero greenhouse gas emissions by 2050 at the latest



Essity has joined the U.N. Global Compact's "Business Ambition for 1.5°C" to develop targets to reach net zero emissions by 2050 for the entire value chain, in line with Science Based Targets initiative (SBTi) criteria. This includes an upgraded target in line with "Well-below 2°C" scenario and means the company commits to reducing its Scope 1 and Scope 2 emissions with 35% by 2030 from 2016.

To learn more: essity.com/sustainability



Watch the Essity Journey to Net Zero video

Introduction	4
Hygiene	4
Tork Vision Cleaning/Product Identification	5
Sustainability	6
Product Attributes and Certifications	7
Segment Solutions	8-9
Washroom	11
Hand Towels	12-18
Soaps and Sanitisers	19-25
Toilet Paper	26-28
Bins	29
Wiping and cleaning	30
Portion Control Centrefeed (Tork Reflex™)	32-33
Centrefeed Free Flow	34
Performance Dispensers and Accessories for Wipers	35
Washstation System	36-37
Tork excelCLEAN™	38
Food Service Cloths	39
Tabletop	40
Dispenser Napkins	41-43

Tork Clean Care – hygiene services and tools designed for you

The Tork Clean Care™ programme is a combination of knowledge, supportive tools, training, great products and services that empower you to deliver Sustainable Hygiene to your workplace.



Research and knowledge
based on close collaborations with our customers, NGOs, research and other facts we think you'll find interesting and useful



Tools, tips and training
to help you raise hygiene standards



Product and service recommendations
to guide you to the best products and services for your type of business



Good hygiene is everyone's business

"With the Tork Clean Care programme we invite everyone to become hygiene heroes, and actively work toward safer workplaces.

Because regardless of what you do, good hygiene is now everyone's business."

Did you know – improved hygiene can lead to:

- Less sick leave
- Improved food safety
- Increased customer, staff and guest satisfaction
- Reduced healthcare-associated infections
- Employee well-being

Hygiene is key to the safety and well-being of people, business and society



71%

of employees expect their employer to provide extra cleaning rounds to ensure hygiene¹



55%

of parents perceive unhygienic conditions to be the main barrier for their children to use school toilets²



80%

of healthcare workers say they would like to improve their hand hygiene compliance³



64%

of foodborne illness outbreaks are associated with food prepared in a restaurant⁴

¹ Survey conducted by United Minds in cooperation with CINT in April 2020. ² Essity Essentials Initiative Survey 2018.

³ Tork Survey, 2019. ⁴ CDC Surveillance for Foodborne Disease Outbreaks Report 2017.

Tork Vision Cleaning, the world's leading facility management solution

What if you could save 20% of your cleaning hours and dedicate them to providing a safer, more hygienic environment?

Knowing when and where your facility needs attention is essential to securing the safety of your users. Our facility management solution features offers that range from people counters to monitor facility flow to people counters and connected dispensers that monitor traffic and essential supplies to a real-time data solution that helps you obtain your cleaning efficiency goals. Regardless of the size of your facility, our solution offers help you to upgrade to a reliable, digital solution.



91%
reduction in dispenser checks – saving hundreds of hours per year¹

At least
20%
Cleaning hours saved²

+30%
Higher customer satisfaction³

Fully stocked washrooms on average
99%
of the time⁴

Easily identify the products you need

Our Tork® Systems are identified with System IDs to seamlessly match dispensers and product refills. They consist of a letter (key below) and a number and are clearly marked on Tork packaging and in this catalogue.

A = Aircare
B = Bin
C = Couch Roll
F = Facial Tissue
H = Hand Towels
M = Centrefeed
N = Napkins
S = Soaps and Sanitisers
T = Toilet Paper
V = Seat Covers
W = Wipers

Our Tork refill products come in three quality tiers.

Premium
Our top quality tier, characterised by exceptional softness and quick absorption. The products are recognised by their superior look and feel, as well as their style and high performance.

Advanced
Effectively balances cost and performance. These high-performance products are soft, attractive and reliable.

Universal
Meets the basic needs of customers, offering good value for money and low maintenance.

Look for these symbols throughout the catalogue which indicate which dispenser systems best handle certain washroom capacity levels.

Low/medium traffic



High traffic



High peak traffic⁵



¹ Based on customer feedback for dispenser checks over 6 months before vs after installing Tork Vision Cleaning (between June-December 2019).

² Measured across 16 sites connected to Tork Vision Cleaning, with each dispenser check taking approx. 20 seconds.

³ Based on the documented results achieved by three Tork Vision Cleaning customers, measured before and after the implementation of Tork Vision Cleaning.

⁴ Measurement of visitor satisfaction in two Tork Vision Cleaning washrooms and two traditionally maintained and equipped washrooms at ISSA/Interclean exhibition, May 2016.

⁵ Measured across nearly 13,000 connected dispensers between June-December 2019, based on time per month that a dispenser is in an empty status against total time per month.

⁶ High peak traffic includes influx of guests within a short period of time.

NOTE: Tork Vision Cleaning was formerly known as Tork EasyCube®

Minimise your environmental impact Maximise your business performance

Reduced plastics and packaging, smaller carbon footprints and less waste.

Tork is committed to developing innovative, sustainable hygiene solutions that are better for business and the planet.



90%

of Tork packaging
is made from
renewable materials

Did you know?

Less wasteful
products can
improve efficiency
and reduce costs



Sustainable hygiene solutions for business

Tork delivers innovative hygiene, efficiency and sustainability.



**Tork Heavy-Duty
Cleaning Cloth,
99% Biobased**

930150

99% biobased¹, while the packaging is made from recycled materials



**Tork Clarity
Hand Washing
Foam Soap**

520201

99% of the ingredients are from natural origins²



**Tork PeakServe®
Continuous Hand
Towels**

100589

50% compressed for more efficient transportation³



**Tork Xpressnap
Fit® Tabletop
Napkin Dispenser**

272900

Cuts unused napkins thrown away by over 50%⁴



**Tork Coreless
Mid-Size Toilet
Paper**

680000

With no wrap, plug, or core, there's less packaging and waste



By 2025 we will use at least 30% recycled plastic in our product packaging.

A majority already do



Read the Essity Sustainability Report at essity.com/sustainability

Read about Tork Sustainability at tork.co.za/sustainability or tork.ie/sustainability

¹ Tork Heavy-Duty Cleaning Cloth, 99% Biobased: TUV Austria, OK Biobased certified product.

² Tork Clarity Hand Washing Foam Soap: Tork Clarity formulation following the ISO16128.

³ Tork PeakServe Continuous Hand Towels: Compared to Tork H2 Universal refills 150299.

⁴ Tork Xpressnap Fit Tabletop Napkin Dispenser: 2-ply napkin in Tabletop dispenser compared to Fastfold (Tork Dispenser: 271800 and Tork Refill: 10933).

Product attributes and certifications

Watch for these identifications throughout the catalogue.



Tork Vision Cleaning¹

These dispensers are compatible with our data-driven cleaning solution. It empowers cleaning teams with new and smarter ways of working.



Tork Easy Handling™

Ergonomically designed solutions for easier carrying, opening and disposing of packaging to make daily work easier.



Tork Run Out Indicator

Tork Run Out Indicator makes sure dispensers don't run out when they're not supposed to.



EU Ecolabel (EU Flower)

The EU ecolabel is the European Union's labelling scheme, which certifies products that meet high environmental standards.

www.ecolabel.eu



Forest Stewardship Council® (FSC®)

FSC certification ensures that products come from responsibly managed forests that provide environmental, social and economic benefits.

www.fsc.org



HACCP International

HACCP International is a leading food science organisation specialising in the HACCP food safety methodology and its application within food and related industries.

haccp-international.com



For Wiping

Food Safety Label

Products carrying this symbol are approved for short-term food contact.



QuickDry

QuickDry™

Our strongest, most absorbent paper, for more efficient drying with less waste.



Easy to use

Many Tork Hygiene Systems are certified by the Swedish Rheumatism Association (SRA) and proven to be easy to use, making hygiene accessible for all, even for children, elderly and people with limited hand function.



Aviation Certified

Aviation

Our most prestigious cloths are certified according to AMS 3819C (Aerospace Material Standard) live up to the high quality requirements demanded by Aviation industry.



Allergy Friendly

Allergy friendly certified by the European Centre for Allergy Research Foundation.



OK Biobased

OK Biobased offers an independent, high-quality guarantee of the renewability of raw materials and products.

¹ Tork Vision Cleaning was formerly known as Tork EasyCube®.

Segment-focused, needs-driven solutions

Tork is dedicated to understanding the challenges our customers in key segments face and providing solutions that answer their specific needs. We focus on four segments: Commercial, HoReCa, Industry, and Healthcare.

Commercial

Key challenges in the Commercial segment include providing a high-quality experience in a demanding environment as well as finding ways to improve efficiency and reaching targets on sustainability.

Tork helps provide a healthy, hygienic end-user experience through user-friendly hygiene solutions that are easy to maintain and help save time, thereby giving facility managers peace of mind and enhancing the company's sustainability image.

71%

of guests at high-traffic venues have had a bad washroom experience¹

89%

of all dispenser checks are unnecessary²

Subsegments



Office Buildings



Education



Recreation



Passenger Terminals

HoReCa

Hygiene is now much more top-of-mind for consumers and therefore a top priority and a key challenge for operators. This is in addition to attracting, retaining and training staff, an increased demand for sustainability, and ensuring positive guest experiences for repeat business- all while aiming for positive reviews.

Tork solutions help HoReCa establishments stay ahead of industry challenges by allowing them to work smarter and hassle-free, promote hygiene, reduce cross contamination, and showcase sustainability.

56%

say poor cleanliness and hygiene make them avoid a restaurant²

92%

of diners read online reviews before picking a restaurant³

Subsegments



Foodservice



Hotels and Lodging

¹ Based on an IPSOS survey of 3000 people in USA, UK, Germany, France, Poland and Sweden who have visited a high traffic venue in the past 9 months.

² Essity power of hands survey 2019 amongst 6,817 respondents across the globe.

³ 75 Significant Restaurant Statistics 2019 & 2020 Finances Online.

Industry

Key challenges in the Industrial segment include continuous drive to improve productivity, increasing employee health and safety standards, attracting and retaining employees, and meeting sustainability goals.

Tork solutions improve productivity, sustain good hygiene practices and reduce environmental impact.

90%

of operators agree that providing professional industrial wipers located close-by will help workplace organization and my work satisfaction⁴

89%

of operators agree that having robust professional wiper dispensers placed exactly where they need them would support efficient cleaning and preventative maintenance⁴

98%

of production managers in food processing agreed well stocked hygiene and cleaning dispensers, placed exactly where needed, can increase hygiene compliance⁴

Subsegments



Manufacturing



Food and Beverage



Transport and Maintenance

Healthcare

Key challenges in the Healthcare segment include infection prevention, cleaning and care staff efficiency and staffing.

Tork solutions reduce the spread of germs with touch-free systems, reduce waste, and improve sustainability by offering 100% recycled and third-party certified products.

5-10%

of all hospital patients are affected. In the EU alone there 3.5m reported Hospital Associated Infections (HAI) a year and at least 80,000 fatalities (about 200 deaths/day) from (HAI)⁵

€7 billion

per year in Europe, (considering direct costs only) in lost revenue for every infection caught in nursing home or other healthcare setting⁶

Subsegments



Longterm Care



Hospitals

⁴ Tork machine operator research, carried out by Psyma (July 2019).

⁵ www.who.int

⁶ Center for Disease Control.



Tork is the leading global brand in workplace hygiene, inspiring and supporting you to think ahead so you're always ready for business. From rethinking the ultimate guest experience, to reimagining cleaning efficiencies and ways to become more sustainable, Tork is always finding new and better ways to improve your business.

To get ahead of the competition, you need to think ahead – and Tork is the partner to help you do that.

Find out more and see the full Tork offering at tork.co.za



Washroom

Making washrooms work for your business

Whether you want to make an impression, show you care for your visitors, maintain hygiene standards or keep control of costs, we've got something that's right for you.



Innovative design lines

Tork Image™ Design

Impress your guests with a truly high-end washroom environment. Stylish stainless steel with anti-fingerprint coating looks great and stays clean.


Tork Elevation®

A seamless, complete and functional dispenser line with a modern feel. Available in black or white.



Tork PeakServe Continuous Hand Towel system (H5)

Restroom experience is important, and the world has never paid more attention to cleaning and hygiene than now. The Tork PeakServe™ Continuous Hand Towel system offers the highest capacity¹ on the market with up to 250% more towels². Together with one-at-a-time dispensing this means fewer runouts and many more people served between refills. And since people only touch the towels they use, you get a very hygienic hand drying solution that helps you secure the new hygiene standard.



250%
more hand
towels for
less refilling
and a better
washroom flow²

- Tork PeakServe Continuous hand towels are excellent for high and peak traffic washrooms
- Faster dispensing serves guests in less than three seconds — 4 times minimising queues in the washroom
- Free up space in storage rooms and cleaning trollies with refills that are compressed by 50%³
- Increase recessed cabinets capacity by up to 40% with Tork PeakServe Recessed Cabinet Adapters⁴
- Ensure a hand towel is always available with the slimmest and smallest high capacity dispenser on the market⁵

¹ Compared to competitor's longest roll towel in Europe.

² Based on an IPSOS survey of 3000 people in USA and European countries who have visited high-traffic venues between January and September 2016.

³ Compared to Tork H2 Universal refills 150299.

⁴ Compared with using Tork Advanced 1 ply Folded Hand Towels in recessed cabinets (applicable for EU and NA).

⁵ Tork PeakServe Mini Continuous Hand Towel Dispenser



Tork PeakServe™ Continuous Hand Towel



- Highest capacity, up to 2,100 towels per dispenser, ensures hand towels are always available
- Serves hand towels in less than 3 seconds
- Top up in use allows dispensers to be refilled at your convenience
- Smooth, one-at-a-time dispensing lowers consumption and ensures that hand hygiene is accessible to all with Easy-to-use certification¹
- 3 dispensing formats to serve washrooms with different traffic flows, layouts, and sizes with the same refill

Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	CON/TRP		
552500	Tork PeakServe™ Continuous Hand Towel Dispenser	Elevation	H5	White	ABS	731×370×101	1	●	●
552508	Tork PeakServe™ Continuous Hand Towel Dispenser	Elevation	H5	Black	ABS	731×370×101	1	●	●
552550	Tork PeakServe™ Mini Continuous Hand Towel Dispenser	Elevation	H5	White	ABS	491×367×101	1	●	●
552558	Tork PeakServe™ Mini Continuous Hand Towel Dispenser	Elevation	H5	Black	ABS	491×367×101	1	●	●
552512	Tork PeakServe™ Large Recessed Cabinet Adapter		H5	White	ABS	519×365×96	1	●	
552511	Tork PeakServe™ Small Recessed Cabinet Adapter		H5	White	ABS	519×365×96	1	●	
205627	Tork PeakServe™ Recessed Adapter Lower Mounting Bar	Accessory	H5	Black	ABS	328×87×72	1		
205629	Tork PeakServe™ Spacer	Accessory	H5	Black	Plastic	265×32×14	1		



100585

- Hand towels compressed by 50% allow you to carry and store twice as much
- Two refill qualities to meet the needs and quality of your washroom environment

Refills

Art. No	Name	System ID	Quality	Colour	No. of Plies	Panels/ Fold	Sheet Size LxW (cm)	Sheets/ Bundle	Bundles/ TRP	Sheets/ TRP	Pack-aging					
100585	Tork PeakServe® Continuous Hand Towel	H5	Universal	White	1	Continuous	22.5×20.1	410	12	4 920	Carry Pack	●	●	●	●	●

¹ Easy-to-use certification on H5 standard and H5 mini dispensers.

Tork Matic Hand Towel Roll system (H1)

Developed for easy maintenance and refilling, Tork Matic® dispenser system is simple to understand and operate for cleaning staff as well as for visitors. Ideal for medium traffic washroom, it is available in manual or sensor in three attractive styles. Depending on whether handsfree hygiene, making an impression or a cost-effective service is required.



High-capacity
system = up to
1 400
hand towels

- Controlled consumption
- Tork Matic™ manual and Intuition™ Sensor models available
- Multiple sheet length settings on Intuition Sensor
- Protected paper in the Intuition Sensor dispenser for optimal hygiene
- Large offer of dispensers and refills ensuring a combination that can suit all needs

Tork Matic™ Hand Towel Roll



- High capacity, ideal for washrooms with frequent use
- Delivers one sheet at a time dispensing, reduces consumption and cost
- Touch-free sensor driven system helps to reduce potential cross contamination
- Sensor dispenser conceals towel until activated, reducing potential contamination even further

Dispensers

Art.No	Name	Design Line	System ID	Colour	Material	Size H x W x D (mm)	CON/TRP		
551100	Tork Matic™ Hand Towel Roll Dispenser – with Intuition™ sensor	Elevation	H1	White	ABS	368x331x206	1	●	●
551108	Tork Matic™ Hand Towel Roll Dispenser – with Intuition™ sensor	Elevation	H1	Black	ABS	368x331x206	1	●	●
551000	Tork Matic™ Hand Towel Roll Dispenser	Elevation	H1	White	ABS	372x337x203	1	●	●
551008	Tork Matic™ Hand Towel Roll Dispenser	Elevation	H1	Black	ABS	372x337x203	1	●	●
460001	Tork Matic™ Hand Towel Roll Dispenser – with Intuition sensor	Image Design	H1	Metallic/Black	Stainless Steel/ABS	373x345x204	1	●	●



- Premium and Advanced white qualities with a coloured leaf embossing for a better impression
- Blue Advanced quality certified food contact, ideal to trace in a food processing environment
- Extra long Universal quality for economy

Refills

Art.No	Name	System ID	Quality	Colour		No. of Plies	Width (cm)	Roll Length (m) No. of Sheets	No. of Sheets with Dispensers: A 551100 & 551108 B 551000 & 551008 C 460001	Rolls/TRP	Pack-aging					
290067	Tork Matic™ Soft Hand Towel Roll	H1	Advanced	White		2	21	150	A 333-428-600-750 B 612 C 333-428-500-600	6	Carton	●	●	●	●	●
290059	Tork Matic™ Extra Long Hand Towel Roll	H1	Universal	White		1	21	280	A 622-800-1120-1400 B 1143 C 622-800-933-1120	6	Carton	●	●	●	●	●

Tork Xpress Multifold Hand Towel system (H2)

Our top-of-the-line multifold hand towel dispenser comes in two wall-mounted sizes as well as countertop, providing both comfort and hygiene. It's ideal for low to medium traffic washrooms. Choose between three attractive styles: high gloss black or white, or a stainless steel finish.



**Most simple
and intuitive
system to refill**



**Show your
commitment to
sustainability
with Tork Natural
colour towels.
Same high quality
— in a new colour.**

- One sheet at a time dispensing helps to minimize cross contamination
- Hygienic, only touch the towel you use

Tork Xpress™ Multifold Hand Towel



- Extra slim and attractive design
- Easy-to-use certified, making hand hygiene accessible for all, including people with reduced hand strength

Dispensers

Art.No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	CON/ TRP		
552000	Tork Xpress™ Multifold Hand Towel Dispenser	Elevation	H2	White	ABS	444x302x102	1	●	●
552008	Tork Xpress™ Multifold Hand Towel Dispenser	Elevation	H2	Black	ABS	444x302x102	1	●	●
552200	Tork Xpress™ Countertop Multifold Hand Towel Dispenser	Elevation	H2	White	ABS	218x323x116	1		●
552208	Tork Xpress™ Countertop Multifold Hand Towel Dispenser	Elevation	H2	Black	ABS	218x323x116	1		●
460004	Tork Xpress™ Multifold Hand Towel Dispenser	Image Design	H2	Metallic/Black	Stainless Steel/ ABS	468x317x101	1	●	●
460005	Tork Xpress™ Countertop Multifold Hand Towel Dispenser	Image Design	H2	Metallic/Black	Stainless Steel/ ABS	218x323x116	1		●



- Superior comfort with maximum hygiene
- Wide assortment of hand towels featuring the Tork logo and leaf embossing

Refills

Art. No	Name	System ID	Quality	Colour		No. of Plies	Panels/ Fold	Sheet Size LxW (cm)	BundlesxSheets = TRP Content	Packaging					
100289	Tork Xpress™ Soft Multifold Hand Towel	H2	Premium	White	●	2	3 Panels, Z	25.5x21.2	21x150 = 3 150	Carry Pack	●	●	●	●	●
120289	Tork Xpress™ Soft Multifold Hand Towel	H2	Advanced	White		2	3 Panels, Z	25.5x21	21x180 = 3 780	Carry Pack	●	●	●	●	●
New 130299	Tork Xpress™ Soft Natural Multifold Hand Towel	H2	Advanced	Natural		2	3 Panels, Z	24x21.3	21x180 = 3 780	Carry Pack	●	●	●	●	●
471093	Tork Xpress™ Multifold Hand Towel	H2	Universal	White		1	3 Panels, Z	23.4x21.3	20x250 = 5 000	Carton	●	●	●	●	●

Tork Singlefold Hand Towel

 H3


553000

- Robust design in two sizes
- Simple and convenient dispenser, easy to maintain

Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	CON/TRP
553000	Tork Singlefold Hand Towel Dispenser	Elevation	H3	White	ABS	439x333x136	1







100278



290163

- Wide assortment of Singlefold (V-fold) hand towels with Tork logo and leaf embossing

Refills Singlefold

Art. No	Name	System ID	Quality	Colour	No. of Plies	Panels/ Fold	Sheet Size LxW (cm)	Sheets/ Bundle	Bundles/ TRP	Sheets/ TRP	Packaging				
100278	Tork Extra Soft Singlefold Hand Towel	H3	Premium	White	2	2 Panels V Fold	23x22.6	200	15	3 000	Carton	●	●	●	●
290163	Tork Soft Singlefold Hand Towel	H3	Advanced	White	2	2 Panels V Fold	23x24.8	250	15	3 750	Carton	●	●	●	●



Dispense confidence with Tork Soap & Sanitiser solutions

Tork soap and sanitiser solutions are proven and formulated specifically to help customers meet high, businesscritical hygiene expectations, across various industries. Design award-winning dispensers and smart refill solutions create both aesthetic and hygienic experiences. Tork soap and sanitiser systems are certified Easy to Use to allow access to hand hygiene for all.

Improved hygiene with effective, and sustainable soap and sanitiser formulations

- A complete range of easy-to-use certified dispensers¹ allow access to hand hygiene for all
- Refilling in less than 10 seconds² for maximum efficiency
- Highly effective soap and sanitiser formulations that care for the skin and the environment



¹ Certified by the Swedish Rheumatism association, tested according to The Design for All Test, published in the Swedish Design Research Journal, 2011.

² Based on internal panel test soap refilling time.

Tork Soap & Sanitiser Dispensers



- One flexible dispensing system for foam, liquid and gel soaps & sanitisers
- Proven easy-to-use design by third party certificate¹ -promotes good hand hygiene for all users, even children and elderly
- Helps secure good hand hygiene: Factory-sealed bottle with a new pump for every refill helps reduce risk of contamination and protect the formulations

S4 Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	PC/TRP		
561600	Tork Skincare Dispenser – with Intuition™ sensor	Elevation	S4	White	ABS	278x112x128	6	●	●
561608	Tork Skincare Dispenser - with Intuition™ sensor	Elevation	S4	Black	ABS	278x112x128	6	●	●
561500	Tork Skincare Dispenser	Elevation	S4	White	ABS	292x113x114	12		●
561508	Tork Skincare Dispenser	Elevation	S4	Black	ABS	292x113x114	12		●
460009	Tork Skincare Dispenser - with Intuition™ sensor	Image Design	S4	Metallic/Black	Stainless Steel/ABS	278x116x130	1	●	●
460010	Tork Skincare Dispenser	Image Design	S4	Metallic/Black	Stainless Steel/ABS	289x106x107	1		●



S1/S11 Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	PC/TRP		
560000	Tork Liquid and Spray Soap Dispenser	Elevation	S1/S11	White	ABS	296x112x114	12	●	
560008	Tork Liquid and Spray Soap Dispenser	Elevation	S1/S11	Black	ABS	296x112x114	12	●	
560101	Tork Liquid Soap Dispenser – Arm Lever	Elevation	S1	White	ABS	296x112x114	8		

- Compact dispenser size fits even in the smallest washroom
- Proven easy-to-use design by third party certificate¹ -promotes good hand hygiene for all users, even children and elderly
- Helps secure good hand hygiene: factory-sealed bottle with a new pump for every refill helps reduce risk of contamination and protect the formulations



S2 Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	PC/TRP		
561000	Tork Mini Liquid Soap Dispenser	Elevation	S2	White	ABS	206x112x114	12	●	
561008	Tork Mini Liquid Soap Dispenser	Elevation	S2	Black	ABS	206x112x114	12	●	

¹ Certified by the Swedish Rheumatism association, tested according to The Design for All Test, published in the Swedish Design Research Journal, 2011.

Tork Hand Soaps

Cosmetic Soap Refills Foam



520201



520501

- Highly-effective formulations, with carefully-chosen ingredients
- Sustainable formulations, like Tork Clarity Foam Soap, are made with 99% of ingredients from natural origins and help support your customers' sustainability goals

S4 Cosmetic Soap Refills Foam

Art. No	Name	System ID	Quality	Fragrance	Colour	Benefit	Content/ Bottle (ml)	Bottles/ TRP			
520201	Tork Clarity Hand Washing Foam Soap	S4	Premium	Perfume Free	Dye Free	99% of ingredients from natural origin	1 000	6	●	●	
520501	Tork Mildly Scented Hand Washing Foam Soap	S4	Premium	Fresh Scent	Dye Free	Regular Handwash	1 000	6	●	●	

Cosmetic Soap Refills Liquid



424011



420701

- Highly-effective formulations, with carefully-chosen ingredients

S4 Cosmetic Soap Refills Liquid

Art. No	Name	System ID	Quality	Fragrance	Colour	Benefit	Content/ Bottle (ml)	Bottles/ TRP			
424011	Tork Odor-Control Hand Washing Liquid Soap	S4	Premium	Perfume Free	Dye Free	Odor control, Food Preparation, Handwash	1 000	6	●	●	

S1 Cosmetic Soap Refills Liquid

Art. No	Name	System ID	Quality	Fragrance	Colour	Benefit	Content/ Bottle (ml)	Bottles/ TRP		
420701	Tork Sensitive Hand Washing Mini Liquid Soap	S1	Premium	Perfume Free	Dye Free	Frequent Handwash	1 000	6	●	●

Hand Sanitisers & Accessories

Alcohol Hand Sanitiser Refills Gel¹



914103





420103

- Effective against a variety of problem organisms – conforms with EN 1500 and EN 14476 (all enveloped viruses, such as: HIV, SARS, Corona, HBV, HCV, influenza H1N1, H5N1 etc.
- Moisturising ingredients encourage good hand hygiene behaviour

S4 Alcohol Hand Sanitiser Refills Gel

Art. No	Name	System ID	Quality	Fragrance	Colour	Efficacy	Efficacy Norms	Content/ Bottle (ml)	Bottles/ TRP	
914103	Tork Salubrin Hand Sanitizer	S4	Premium	Perfume Free	Dye Free	Bacteria Yeast & Fungi Virus	EN 1500, EN 1276, EN 1650, EN 14476 (All Enveloped Viruses)	1 000	6	

S1 Alcohol Hand Sanitiser Refills Gel

Art. No	Name	System ID	Quality	Fragrance	Colour	Efficacy	Efficacy Norms	Content/ Bottle (ml)	Bottles/ TRP	
420103	Tork Alcohol Gel Hand Sanitiser	S1	Premium	Perfume Free	Dye Free	Bacteria Yeast & Fungi Mycobacteria Virus	EN 1500, EN 12791, EN 13727, EN 1276, EN 1275, EN 13624, EN 1650, EN 14348, EN 14476 (all enveloped and Rotavirus & Norovirus)	1 000	6	

Alcohol Hand Sanitiser Refills Foam¹



520102


- Effective against a variety of problem organisms – conforms with EN 1500, EN 12791 and EN 14476 (all enveloped viruses, such as: HIV, SARS, Corona, HBV, HCV, influenza H1N1, H5N1 etc.
- Dermatologically-tested, Tork Hand Sanitizing Alcohol Foam is gentle on the skin

S4 Alcohol Hand Sanitiser Refills Foam

Art. No	Name	System ID	Quality	Fragrance	Colour	Efficacy	Efficacy Norms	Content/ Bottle (ml)	Bottles/ TRP	
 520102	Tork Hand Sanitising Alcohol Foam	S4	Premium	Perfume Free	Dye Free	Bacteria Yeast & Fungi Mycobacteria Virus	EN 1500, EN 13727, EN 13624, EN1650, EN 14348 (Tuberculosis), EN 14476 (All Enveloped Viruses)	950	6	

¹ Use biocides safely. Always read the label and product information before use.

Accessories



Stands						
Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	PC/TRP
511060	Tork Sanitiser Stand	S1/S2/S4	Black	Metal	1 321×500×500	1
Accessories for Stands						
Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	PC/TRP
511029	AD-a-Glance® for Tork Sanitiser Stand	S1/S2/S4	Black	Metal/Plastic	364×148×20	10
511039	Twin Dispenser Mount for Tork Sanitiser	S1/S2/S4	Black	Metal	320×108×28	10
Floor Protectors						
Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	PC/TRP
511049	Floor Protector for Tork Sanitiser Stand	S1/S2/S4	Black	Metal/Plastic	212×142×142	1



Shower

Shower Cream



424601

- Refreshing pearly shower cream with a unisex fragrance

S4 Shower Cream

Art. No	Name	System ID	Quality	Fragrance	Colour	Benefit	Content/ Bottle (ml)	Bottles/ TRP		
New 424601	Tork Shower Cream	S4	Premium	Fresh Unisex Scent	Blue	Hair & Body	1 000	6	●	●

Toilet Seat Cleaner


Toilet Seat Cleaner



420302

- For extra hygiene and comfort inside the cubical
- Cleaning for an extra-hygienic toilet seat
- Sealed bottle with single-use pump reduces the risk of cross contamination


S2 Toilet Seat Cleaner

Art. No	Name	System ID	Quality	Colour	Type	Benefit	Content/ Bottle (ml)	Bottles/ TRP	
420302	Tork Toilet Seat Cleaner	S2	Premium	Transparent	Detergent	Extra Hygienic Toilet Seat	475	8	●



Tork SmartOne Toilet Roll systems (T8 and T9)

Specially designed for high-traffic washrooms, the Tork SmartOne™ toilet roll dispenser is the ultimate cost-in-use and hygiene system. Available in white or black.



Reduce paper consumption by up to

40%¹

- High capacity: less maintenance and reduced risk of paper shortage
- Robust design for demanding environments
- Quick disintegration and reduced consumption; minimises risk of pipe blockages

¹ Tork Advanced refill: Statistics from internal research conducted in European countries on 7729 users, Tork Jumbo Toilet Roll against Tork SmartOne® Twin Mini. Reduction accounted in square metres.




Tork SmartOne™ Toilet Roll/Tork SmartOne™ Mini Toilet Roll


 T8/T9

- Single-sheet dispensing helps reduce consumption by up to 40%
- Hygienic: guests only touch the sheet they use
- Robust design with lock to protect the roll and stop pilferage in demanding environments
- Fully enclosed dispenser: users cannot touch the inside - for a more hygienic experience






Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size H×W×D (mm)	CON/TRP	
680000	Tork SmartOne® Toilet Roll Dispenser	Elevation	T8	White	ABS	269×269×156	1	●
680008	Tork SmartOne® Toilet Roll Dispenser	Elevation	T8	Black	ABS	269×269×156	1	●
681000	Tork SmartOne® Mini Toilet Roll Dispenser	Elevation	T9	White	ABS	219×219×156	1	●
681008	Tork SmartOne® Mini Toilet Roll Dispenser	Elevation	T9	Black	ABS	219×219×156	1	●
682000	Tork SmartOne® Twin Mini Toilet Roll Dispenser	Elevation	T9	White	ABS	221×398×156	1	●
682008	Tork SmartOne® Twin Mini Toilet Roll Dispenser	Elevation	T9	Black	ABS	221×398×156	1	●



Tork SmartCore™ – The most convenient way to extract a core – no need for tearing and easier to remove. Tork SmartCore also gives more sheets on the roll while less air in the packaging optimises transport efficiency.

Refills

Art. No	Name	System ID	Quality	Colour	Feature	No. of Plies	Width (cm)	No. of Sheets	Rolls/ TRP	Packaging			
472242	Tork SmartOne™ Toilet Roll	T8	Advanced	White	Tork SmartCore	2	13.4	1 150	6	Plastic	●	●	●
472193	Tork SmartOne™ Mini Toilet Roll	T9	Advanced	White	Tork SmartCore	2	13.4	620	12	Plastic	●	●	●

Tork Mini Jumbo Toilet Roll

T2



555000



460006

- Smart, stub-roll holder allows for full roll consumption
- Optimal roll brake prevents free-spinning rolls and therefore, reduces consumption
- See-through window indicates when it's time to refill

Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	CON/ TRP		
555000	Tork Mini Jumbo Toilet Roll Dispenser	Elevation	T2	White	ABS	275x345x132	1	●	●
460006	Tork Mini Jumbo Toilet Roll Dispenser	Image Design	T2	Metallic/Black	Stainless Steel/ABS	254x355x133	1	●	●



120280



120377

Refills

Art. No	Name	System ID	Quality	Colour	No. of Plies	Width (cm)	Roll Length (m)	Rolls/ TRP	Packaging				
120280	Tork Mini Jumbo Toilet Roll	T2	Advanced 	White	2	9.4	170	12	Plastic	●	●		●
New 120377	Tork Natural Mini Jumbo Toilet Roll Advanced	T2	Advanced 	Natural	2	9.4	170	12	Plastic	●	●		●

Tork Bins, Liners, Bags

B1/B2/B5



563000



563008



460011



226100

- Family look, consistent washroom design
- Completely hidden bin liner, clean appearance
- Lid option with soft closing for extra hygiene

Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	CON/TRP	
563000	Tork Waste Bin 50 Ltr	Elevation	B1	White	ABS	629x389x289	1	●
563008	Tork Waste Bin 50 Ltr	Elevation	B1	Black	ABS	629x389x289	1	●
460011	Tork Waste Bin 50 Ltr	Image Design	B1	Metallic/black	Stainless Steel/ABS	614x395x253	1	●
226100	Tork Waste Bin 20 Ltr		B2	White	Plastic	430x322x205	1	



Wiping and cleaning

The easy choice for the best result

Whether you run a restaurant kitchen or an industrial production line, we understand that every second matters. Tork wipes, cloths and dispensers are designed to get the job done with maximum efficiency – keeping your business running smoothly.



Choosing the right product


We've got a comprehensive range of specialist wipes and cloths, each designed to perform specific tasks (Foodservice, Food Processing, Microfibre Cloth).

Wiping

Mopping up spills, soaking up liquids and picking up dirt and dust with paper.

Cleaning

Removing dirt and stains from surfaces, machines or tools with cloths that are dry or used together with water, solvents or detergents.



Find the right dispensing solution

We have a wipe or cloth for every task, and a wide range of dispensers with fixing options available to make sure you'll always find what you need, where you need it.

Wall mounted



Tork Wall Stand (Refill W1)

652108 Red/Black
652100 Turquoise/White

- Saves floor space
- Easy, ergonomic loading
- Safe and reliable dispensing from the glass fibre reinforced teeth



Tork Maxi Centrefeed Dispenser (Refill W2)

653008 Red/Black
653000 Turquoise/White

- Hygienic dispenser for maxi centrefeed rolls
- Optimised for single hand dispensing



Tork Folded Wiper/Cloth Dispenser (Refill W4)

654008 Red/Black
654000 Turquoise/White

- Protects the wipes and reduces consumption by dispensing one sheet at a time
- Flexible mounting options include wall brackets, suction cups and magnets (page 35)



Tork Centrefeed Dispenser (Refill M2)

559000 White

- Improved hygiene – touch only what you use
- Single hand dispensing for easy use
- Versatile lock mechanism to control misuse
- Mini models ideal when space is limited



Tork Reflex™ Single sheet Centrefeed Dispenser (Refill M4)

473190 White/White

- Touch only what you use – reducing risk of cross contamination
- Easily dispensable using only one hand
- Robust design made to withstand the toughest environments
- Easy-to-clean design featuring removable hood
- Mini models ideal when space is limited



Tork Washstation Roll Towel Dispenser (Refill W6)

651420 Turquoise/White

- Water resistant
- Large capacity with one at a time dispensing
- Built to withstand wet environments



Tork Small Pack Dispenser Bracket (Refill W8)

655100 White

- Space-saving dispenser bracket for server stations, back of house or in storage areas

Portable



Tork Reflex® Portable Centrefeed Dispenser

473186 White Refill
473188 Blue Refill

- Single sheet dispenser on the go
- Easy to hang on a chair or a trolley

Mobile



Tork Floor Stand (Refill W1)

652008 Red/Black
652000 Turquoise/White


- Easy, ergonomic loading
- Safe and reliable dispensing from the glass fiber reinforced teeth
- Save time by adding a matching bin liner holder to the stand (page 35)

Tork Reflex system

You want everyday spills and messes dealt with quickly, without waste or hygiene risks.

Our range of Tork Reflex® dispensers and refills is developed to control the cost of our customers' most common hand and surface wiping tasks.

Includes a Range of HACCP International certified Refill Rolls.



Reduces
wiping paper
usage by up to
37%¹

- Control cost – cut down consumption and waste
- A durable investment suitable for any environment
- Hassle-free refilling with Tork SmartCore™
- Tork run out indicator ensures you're never caught without paper



¹ Essity research conducted over a 4 week period. Tork Reflex Wiping Paper Plus against freeflow Tork Wiping Paper Plus. Reduction calculated in square metres used.

Multipurpose Paper

Wiping

▼ Tork Reflex™ Dispensers



- Improved hygiene – touch only what you take
- Fits into your work flow for one-handed tasks

Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	CON/TRP	
473177	Tork Reflex™ Single Sheet Mini Centrefeed Dispenser	M3	White/White	Plastic	321x191x180	1	
473190	Tork Reflex™ Single Sheet Centrefeed Dispenser	M4	White/White	Plastic	331x255x239	1	
473186	Tork Reflex™ Portable Centrefeed Dispenser Starter Pack	M4	Turquoise/White	Plastic	222x278x236	1	

Refills

▼ Tork Reflex™ Wiping Paper Plus



473474

473472

- Multipurpose paper ideal for mopping up liquids and hand wiping
- Single Sheet Dispensing - reduces consumption by up to 37%

Art. No	Format	System ID	Colour	No. of Plies	Width (cm)	Roll Length (m)	Sheet Length (cm)	Sheets/ Roll	Rolls/ TRP	For Wiping	Ecolabel	FSC	Run out indicator	One hand dispensing	
473474	Mini Centrefeed Roll	M3	White	2	19.4	67	33.5	200	9						
473472	Centrefeed Roll	M4	White	2	19.4	151	33.5	450	6						


▼ Tork Reflex™ Wiping Paper



473242

- Multipurpose paper for light wiping tasks
- Single Sheet Dispensing - reduces consumption by up to 37%

Art. No	Format	System ID	Colour	QuickDry	No. of Plies	Width (cm)	Roll Length (m)	Sheet Length (cm)	Sheets/ Roll	Rolls/ TRP	For Wiping	Ecolabel	FSC	Run out indicator	One hand dispensing	
473242	Centrefeed Roll	M4	White		1	19.8	300	35	857	6						



Tork SmartCore™

Tork Reflex refills (except 473263 and 473264) feature Tork SmartCore core removal – for fast and easy refilling



Run out indicator

- Never run out of paper
- No irritation
- Plan your changes in advance

Dispensers

▼ Tork Elevation/Metal Centrefeed Dispensers

M2



- Easy one-handed operation and controlled consumption
- Sleek black or white dispensers complement any environment, providing a clean, hygienic appearance.
- Ideal for hand and light surface wiping

Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	CON/ TRP
559000	Tork Centrefeed Dispenser	M2	White	Plastic	360x239x227	1

Basic Paper










Wiping

▼ Tork Basic Paper 1 ply



120155

- Roll for basic wiping needs

Art. No	Format	System ID	Colour	No. of Plies	Width (cm)	Roll Length (m)	Sheet Length (cm)	Sheets/ Roll	Rolls/ TRP	 For Wiping	 Eco-label	 FSC	 Run out indicator	 One paper roll per person
120155	Centrefeed Roll	M2	White	1	20	300			6					



Run out indicator

- Never run out of paper
- No irritation
- Plan your changes in advance

Did you know?

Tork has a wipe and dispenser combination for every task, regardless if you're working in a restaurant, hotel, school, hospital, mechanical workshop or any other environment where hand and surface wiping is part of the job.



Dispensers

▼ Tork Performance Dispensers



- All dispensers optimised for Tork Wipers when combined they become the perfect performance tools
- Extra robust construction
- Semi-transparent hoods






Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	CON/ TRP
652000	Tork Floor Stand	W1	Turquoise/White	Plastic/ Metal	1 006x646x530	1
652008	Tork Floor Stand	W1	Red/Black	Plastic/ Metal	1 006x646x530	1
652100	Tork Wall Stand	W1	Turquoise/White	Plastic/ Metal	463x646x274	1
652108	Tork Wall Stand	W1	Red/Black	Plastic/ Metal	463x646x274	1
653000	Tork Maxi Centrefeed Dispenser	W2	Turquoise/White	Plastic	447x328x302	1
653008	Tork Maxi Centrefeed Dispenser	W2	Red/Black	Plastic	447x328x302	1
654000	Tork Folded Wiper/Cloth Dispenser	W4	Turquoise/White	Plastic	374x427x206	1
654008	Tork Folded Wiper/Cloth Dispenser	W4	Red/Black	Plastic	374x427x206	1
655100	Tork Small Pack Dispenser	W8	White	Plastic	145.8x214x107.3	4

▼ Tork Wiping Paper



130100

- Multipurpose paper for light wiping tasks

Art. No	Format	System ID	Colour	 Quick-Dry	No. of Plies	Width (cm)	Roll Length (m)	Sheet Length (cm)	Sheets/ Roll	Rolls/ TRP	 For Wiping	 Ecolabel	 FSC	
130100	Giant Roll	W1	White		1	24.5	1 000			1	●	●	●	

Tork Food Processing Washstation System

You face some of the toughest challenges

That's why you need dispensers and refills you can rely on. The purpose-built, HACCP International certified Tork Washstation Dispenser System is precisely engineered to help mitigate risks, increase operational efficiencies, and handle the pressures of a rigorous environment.



Dispensers

W6

▼ Tork Washstation Dispenser



651420

- Durable, water-resistant design holds up well in wet, harsh environments
- High-capacity design requires fewer refills
- Hygienic hands-free dispensing
- Easy to wipe or spray down without removing from wall
- Easy mounting with clear backplate

Art. No	Name	System ID	Colour	Material	Size HxWxD (mm)	CON/TRP	
651420	Tork Washstation Dispenser	W6	Turquoise/White	Plastic	459x319x268	1	

Refills

Washstation Paper

Wiping

▼ Tork Basic Paper



130001

130002

- Strong and absorbent wiping paper
- High footage rolls mean less time on refills
- Wipers can stand up to high humidity, so they're suitable for harsh environments
- Food contact certified rolls guarantee high-quality paper and product safety
- Blue paper is visible and offer traceability in food materials therefore it improves safety of the production in food processing


Art. No	Format	System ID	Colour	No. of Plies	Width (cm)	Roll Length (m)	Sheet Length (cm)	Sheets/ Roll	Rolls/ TRP					
130001	Tork Basic Paper	W6	White	1	19.5	250	24.5	1 020	6	●	●	●	●	●
130002	Tork Basic Paper	W6	Blue	1	19.5	250	24.5	1 020	6	●	●	●	●	●



Tork exelCLEAN

Professional results, no matter how tough the challenge

With Tork exelCLEAN™ you get a quality range of low-linting, high performance cloth wipers. You also get the same reliable performance every time. No more spending time searching through rags for the “right ones”. Tork exelCLEAN benefits your business by your business by increasing employee satisfaction, reducing costs and improving working conditions.



Did you know?

Our Tork exelCLEAN and patented foam-spun technologies produce nonwoven cloths setting the standard of excellence for safer, healthier and more efficient workplaces.

Could your cleaning process be more efficient?

Independent tests have proven that Tork exelCLEAN cleaning cloths out-perform rags and rentals by saving time, effort and solvents used for the same task. Using them means up to:

35% less time
41% less solvents
31% less effort

Improved durability:

Refined to improve high-performance durability with a new, uniform construction.

More efficient:

Our Top-Paks are now compressed to save up to 26% storage space and transportation, requiring less refills, and ensuring the product is there when you need it.

More flexible packaging:

New improved portable boxes with reinforced handle and larger opening to easily access cloths – even with gloves on.



OK Biobased certification:

OK Biobased program certification confirms the plant based composition of the product. The product is OK Biobased certified and high performing in terms of cleaning, while offers sustainability benefits at the same time.

Multipurpose Cloths / Industrial Cloths

Cleaning

▼ Tork Heavy-Duty Cleaning Cloths 99% Biobased



930150



930179

- Meet the demands of both productivity and sustainability
- Strong, absorbent multipurpose cloth for heavier cleaning tasks
- 99% biobased, slowing down carbon dioxide atmospheric build-up, while performing cleaning tasks as effectively as ever¹

Art. No	Format	System ID	Color	exelCLEAN	Roll Length (m)	Sheet Size LxW (cm)	Sheets/ Pack	Packs/ TRP	For Wiping	FSC	OK Biobased	TÜV
930150	Folded 99% biobased – Small Pack	W8	White	●		31.5x38.5	50	8	●	●		●
New 930179	Folded 99% biobased – Small Pack	W4	White	●		41.5x35.5	105	4	●	●	●	●

Food Service Cloths

Cleaning

▼ Tork Kitchen Cleaning Cloth



473179

- Thick cotton-based cloth, suitable for most kitchen cleaning tasks
- Heat resistance
- Soft and highly absorbent
- 100% biobased product slowing down carbon dioxide atmospheric build-up, while performing cleaning tasks as effectively as ever³

Art. No	Format	System ID	Colour	Sheet Size LxW (cm)	Sheets/ Pack	Packs/TRP	For Wiping	FSC	OK Biobased	TÜV
473179 ²	Tork Kitchen Cleaning Cloth	W4	White	41.5x35.5	75	4	●	●	●	●

▼ Tork Coloured Long-Lasting Cleaning Cloths



194450



194550



194650



194750

- Durable and absorbent cleaning cloth
- Can be used repeatedly without tearing
- Available in five colours to help prevent cross-contamination

Art. No	Format	System ID	Colour	Sheet Size LxW (cm)	Sheets/ Roll/Pack	Rolls/Packs /TRP	For Wiping	FSC
194450	Tork Coloured Long-lasting Cleaning cloth - Blue	W8	Blue	30x38.5	40	8	●	●
194550	Tork Coloured Long-lasting Cleaning cloth - Green	W8	Green	30x38.5	40	8	●	●
194650	Tork Coloured Long-lasting Cleaning cloth - Yellow	W8	Yellow	30x38.5	40	8	●	●
194750	Tork Coloured Long-lasting Cleaning cloth - Red	W8	Red	30x38.5	40	8	●	●

¹ 100% biobased product slowing down carbon dioxide atmospheric build-up, while performing cleaning tasks as effectively as ever.

² Previous Art. No 473178

³ Product certified with OK Biobased by TÜV Austria.

Tabletop

Making it easy to create a great experience

It's not enough just to provide satisfactory service – you need to create a great experience to keep reviews positive and customers coming through the door. When doing this, we know the details matter, and we can help you get them right.



Product ranges to meet different needs

Self-service with napkin dispensing systems

When customers dispense their own napkins, refilling, waste management and storage need to be effortless, easy and convenient.

Full-service with single-serve napkins and tableware

The quality feel of your table setting is one of many important things that creates a restaurant's ambiance.



Tork Xpressnap Napkin systems

Designed for busy self-service environments where napkins need to be available close at hand. Tork Xpressnap™ and Tork Xpressnap Snack™ support a faster, more efficient guest experience when hygiene and swift maintenance are critical. One-at-a-time dispensing helps you control consumption and costs.



Reduces
napkin usage
by at least
25%¹



- A wide range of stylish, modern dispensers to fit your needs
- Improved hygiene, as your guests only touch what they take
- Promote your brand, offer or generate extra revenue with the AD-a-Glance® Display panels

Visit adaglance.torkglobal.com for inspiration!

¹ Tork Xpressnap (N4/N10) compared to traditional napkin dispensers.

N4 Dispensers and Refills



Tork Xpressnap											N4
Art. No	Name	Design Line	System ID	Colour	Material	Size HxWxD (mm)	Capacity Pcs (1 ply 1/4 refill)	AD-a-Glance	Mount-able	CON/TRP	FSC
272611	Tork Xpressnap™ Tabletop Napkin Dispenser	Signature	N4	Black	Plastic	169×200×141	275	●		4	
272511	Tork Xpressnap™ Counter Napkin Dispenser	Signature	N4	Black	Plastic	145×191×307	550	●		1	
272211	Tork Xpressnap™ Stand Napkin Dispenser	Signature	N4	Black	Plastic	622×235×235	1 100	●	●	1	
272250	Tork Xpressnap™ Drive Thru Napkin Dispenser	Signature	N4	Black	Plastic	622×235×254	900	●	●	1	



White	Natural
10840	12840

Refills													
Art. No	Name	System ID	Quality	Colour	No. of Plies	Folding	Sheet Size Unfolded LxW (cm)	Pcs/ Bundle	Pcs/ CON	Pcs/TRP	For Wiping	Ecobabel	FSC
12840	Tork Xpressnap™ Natural Dispenser Napkin	N4	Advanced	Natural	1	1/4	21.3×33.0	225	1 125 (5×225)	9 000 (8×5×225)	●	●	●
10840	Tork Xpressnap™ White Dispenser Napkin	N4	Universal	White	1	1/4	21.3×33.0	225	1 125 (5×225)	9 000 (8×5×225)	●	●	●

Tork Xpressnap Fit

The smarter napkin solution that helps you increase efficiency and promote hygiene

Tork Xpressnap Fit® is our most compact dispenser napkin system yet, designed to reduce refill time and free up space.

Fewer refills and less cleaning means more time for you to focus on your guests and your business.



Cuts unused napkins thrown away by more than **50%**^{1,2}

Tork Xpressnap Fit™ Dispensers

N14



272900

272901

- Durable and easy-to-clean dispensers reduce time for maintenance and protect napkins from dirt and spills
- Compact design provides more table space for guests
- Cuts napkin inventory space by **up to 35%**²
- Reduces napkin refill time by **46%**¹
- Serve almost **2x** as many guests between refills¹

Dispensers

Art. No	Name	Design Line	System ID	Colour	Material	Size LxWxH (mm)	Capacity Pcs	AD-a-Glance	Mountable	CON/TRP
272900	Tork Xpressnap Fit™ Tabletop Napkin Dispenser	Signature	N14	Black	Plastic	141x113x170	168	●		4
272901	Tork Xpressnap Fit™ Counter Napkin Dispenser	Signature	N14	Black	Plastic	326x121x143	324	●		1



15830

- A full-size napkin is folded to fit the small-footprint dispenser
- Specially-designed fold makes the first napkin easy to grab after dispenser refills
- Leaf embossing enhances the guest experience and easy to recognise

Refills

Art. No	Name	System ID	Quality	Colour	No. of Plies	Sheet Size Unfolded LxW (cm)	Pcs/Bundle	Pcs/CON	Pcs/TRP	For Wiping	Recycled	FSC	Tork Easy Handling
15830	Tork Xpressnap Fit™ White Dispenser Napkin	N14	Advanced	White	2	21.3x16.5	120	720 (6x120)	4 320 (6x6x120)	●	●	●	●

¹ 2-ply napkin in Tabletop dispenser compared to Fastfold (Tork Dispenser: 271800 and Tork Refill: 10933).

² 2-ply napkin in Counter dispenser compared to Counterfold (Tork Dispenser: 271600 and Tork Refill: 10935).

How else can we help?
Get in touch to talk
about your business.

www.tork.co.za
tork.rsa@essity.com



Scan the code
for the online version.
Fewer copies printed =
less impact on the
environment

