

# Tork carbon neutral dispensers certified by

reduced with certified renewable electricity and compensated with climate projects



ClimatePartner  
certified product

climate-id.com/9VIUDN



Think ahead.

Switching from Tork C-fold to **Tork PeakServe®** will help reduce waste with **28%<sup>1</sup>**



**552500** Tork PeakServe Continuous Hand Towel Dispenser White  
**552508** Tork PeakServe Mini Continuous Hand Towel Dispenser Black  
**552550** Tork PeakServe Mini Continuous Hand Towel Dispenser White  
**552558** Tork PeakServe Mini Continuous Hand Towel Dispenser Black

## H5 PeakServe

Switching from Tork C-fold to Tork Xpress Multifold will help reduce waste with **15%<sup>6</sup>**



**460004** Tork Xpress Multifold Hand Towel Dispenser Stainless Steel  
**460005** Tork Xpress® Countertop Multifold Hand Towel Dispenser

## H2 Xpress Multifold (only Image line)

**Tork Reflex®** single sheet dispensing reduces consumption by up to **37%<sup>2</sup>**



**473190** Tork Reflex Single Sheet Centrefeed Dispenser White  
**473177** Tork Reflex Single Sheet Mini Centrefeed Dispenser White  
**473180** Tork Reflex Single Sheet Centrefeed Dispenser Turquoise  
**473167** Tork Reflex Single Sheet Mini Centrefeed Dispenser Turquoise

## M3 & M4 Reflex

**Tork SmartOne®** reduces toilet paper consumption by up to **40%<sup>3</sup>**



**681000** Tork SmartOne Mini Toilet Roll Dispenser White  
**680000** Tork SmartOne Mini Toilet Roll Dispenser White  
**682000** Tork SmartOne Twin Mini Toilet Roll Dispenser White



**681008** Tork SmartOne Toilet Roll Dispenser Black  
**680008** Tork SmartOne Toilet Roll Dispenser Black  
**682008** Tork SmartOne Twin Mini Toilet Roll Dispenser Black

## T8 & T9 SmartOne

**Tork Coreless rolls** less packaging **77%<sup>4</sup>**



**558040** Tork Twin Coreless Mid-size Toilet Roll Dispenser White



**558048** Tork Twin Coreless Mid-size Toilet Roll Dispenser Black

## T7 Coreless Midsize

Tork Foam Soap systems helps reduce consumption by up to **50%<sup>5</sup>**



**460010** Tork Skincare Dispenser Stainless Steel



**561500** Tork Skincare Dispenser White  
**561508** Tork Skincare Dispenser Black

## S4 Skincare

Bottle is collapsible, leading to **70% less waste volume<sup>7</sup>**



**560101** Tork Liquid Soap Dispenser White  
**560109** Tork Liquid Soap Dispenser  
**560000** Tork Liquid and Spray Soap Dispenser White  
**560008** Tork Liquid and Spray Soap Dispenser Black  
**561000** Tork Mini Liquid Soap Dispenser White  
**561008** Tork Mini Liquid Soap Dispenser Black

## S1 & S2 Liquid Soap Dispensers

- 1 Comparing average for Tork 471114 and 290265 with Tork 100589 based on weight. Internal research.
- 2 Tork Reflex compared to ordinary centrefeed roll. Statistics from internal research conducted over a 4 week period.
- 3 Tork SmartOne Twin Mini dispensers compared to Traditional maxi Jumbo Dispensers. Internal research on 7729 users in Europe. Reduction accounted in square meters per visit.
- 4 Claim valid for Europe only. Disclaimer: As compared to the packaging weight of Tork 2ply Advanced conventional toilet paper, which includes cores and two layers of plastic packaging.
- 5 Essity test: Using Tork Foam vs Tork Liquid Soap in an Elevation dispenser.
- 6 Comparing average for Tork 471114 and 290265 with Tork 120289 and 471117 based on weight. Internal research.
- 7 Based on Essity test.