

# Tork carbon neutral dispensers certified by

reduced with certified renewable electricity and compensated with climate projects



ClimatePartner  
certified product  
[climate-id.com/9VIUDN](https://climate-id.com/9VIUDN)



Think ahead.

Switching from Tork C-fold to **Tork PeakServe®** will help reduce waste with **28%<sup>1</sup>**



**552500**  
Tork PeakServe Continuous  
HT Disp Wh



**552508**  
Tork PeakServe Mini Contin.  
HT Disp Bl



**552550**  
Tork PeakServe Mini Contin.  
HT Disp Wh



**552558**  
Tork PeakServe Mini Contin.  
HT Disp Bl



## H5 PeakServe

Switching from Tork C-fold to Tork Xpress Multifold will help reduce waste with **15%<sup>6</sup>**



**460004**  
Tork Xpress Multifold  
Hand Towel Disp SS



**460005**  
Tork Xpress® Countertop  
Multifold Hand Towel Dispenser



## H2 Multifold (only image line)

**Tork Reflex®** single sheet dispensing reduces consumption by up to **37%<sup>2</sup>**



**473190**  
Tork Reflex Sing Sh Cf disp  
White



**473177**  
Tork Reflex Sing Min Cf disp  
White



**473180**  
Tork Reflex Sing Sh Cf disp  
Turquoise



**473167**  
Tork Reflex Sing Min Cf disp  
Turquoise

## M3 & M4 Reflex

**Tork SmartOne®** reduces toilet paper consumption by up to **40%<sup>3</sup>**



**681000**  
Tork SmartOne Mini  
TR Disp White



**680000**  
Tork SmartOne Mini  
TR Disp White



**682000**  
Tork SmartOne Twin Mini TR Disp White



**681008**  
Tork SmartOne  
TR Disp Black



**680008**  
Tork SmartOne  
TR Disp Black



**682008**  
Tork SmartOne Twin Mini TR Disp Black

## T8 & T9 SmartOne

**Tork Coreless** rolls less packaging **77%<sup>4</sup>**



**558040**  
Tork Twin Coreless Mid TR Dis White



**558048**  
Tork Twin Coreless Mid TR Dis Black



## T7 Coreless Midsize

Tork Foam Soap systems helps reduce consumption by up to **50%<sup>5</sup>**



**460010**  
Tork Skincare  
Dispenser SS



**561500**  
Tork Skincare  
Dispenser White



**561508**  
Tork Skincare  
Dispenser Black



## S4 Skincare

Bottle is collapsible, leading to **70%<sup>7</sup>** less waste volume



**560101**  
Tork liquid soap disp w  
bracket, White



**560109**  
Tork Liquid Soap  
Dispenser



**560000**  
Tork Liquid and Spray  
Soap Dispenser Wh



**560008**  
Tork Liquid and Spray  
Soap Dispenser Black



**561000**  
Tork Mini Liquid Soap  
Dispenser White



**561008**  
Tork Mini Liquid Soap  
Dispenser Black



## S1 & S2 Liquid Soap Dispensers

<sup>1</sup> Comparing average for Tork 471114 and 290265 with Tork 100589 based on weight. Internal research.

<sup>2</sup> Tork Reflex compared to ordinary centrefeed roll. Statistics from internal research conducted over a 4 week period.

<sup>3</sup> Tork SmartOne Twin Mini dispensers compared to Traditional maxi Jumbo Dispensers. Internal research on 7729 users in Europe. Reduction accounted in square meters per visit.

<sup>4</sup> Claim valid for Europe only. Disclaimer: As compared to the packaging weight of Tork 2ply Advanced conventional toilet paper, which includes cores and two layers of plastic packaging

<sup>5</sup> Essity test: Using Tork Foam vs Tork Liquid Soap in an Elevation dispenser

<sup>6</sup> Comparing average for Tork 471114 and 290265 with Tork 120289 and 471117 based on weight. Internal research.

<sup>7</sup> Based on Essity test.