

## Better hygiene for better business performance



## Hygiene is not only essential, it is a way to improve business performance

Tork empowers you to rethink the overall experience, improve workplace satisfaction, make cleaning more efficient and reimagine ways to become more sustainable. We are committed to giving all people equal access to sustainable hygiene solutions.

The Tork brand offers professional hygiene products and services to customers worldwide, ranging from restaurants and healthcare facilities to offices, schools and industries. Our products include dispensers, paper hand towels, toilet tissue, soap, sanitizers, air fresheners, napkins, and wipers—plus software solutions for data-driven cleaning.



---

## Help finding the right products

Refer to the Tork System Identifiers/Refill IDs to seamlessly match dispensers and product refills. They consist of a letter (key below) and a number and are clearly marked on all Tork packaging and throughout this catalog.

**A = Air Freshener**

**F = Facial Tissue**

**H = Hand Towels**

**M = Centerfeed**

**N = Napkins**

**S = Soap and Sanitizer**

**T = Toilet Paper**

**V = Seat Covers**

**W = Wipers**

---

Our Tork refill products come in three quality tiers.

### **Premium**

Our top quality tier, characterized by exceptional softness and quick absorption. The products are recognized by their superior look and feel, as well as their style and high performance.

### **Advanced**

Effectively balances cost and performance. These high-performance products are soft, attractive and reliable.

### **Universal**

Meets the basic needs of customers, offering good value for money and low maintenance.



# Product attributes and certifications

Watch for these identifications throughout the catalog.



Shown as:  in product charts

## ECOLOGO®

[www.ul.com/el](http://www.ul.com/el)

UL Environment's ECOLOGO® Program helps build and strengthen trust in sustainable products. Certification to one of UL's rigorous, multi-attribute, lifecycle-based standards indicates that a product has undergone third-party auditing and verification to stringent, science-based performance criteria, making it a more sustainable choice.

- UL certifies commercial and household toilet and facial tissue, napkins, and hand and kitchen towel products under its UL 175 Sanitary Paper Standards for an overall reduced environmental impact.
- These standards address recycled content and chlorine-free bleaching processes.
- Standard criteria also includes "downstream" effects such as effluent content, air emissions, solid waste reduction, and energy consumption.
- The holistic approach incorporated in this certification matches our philosophy of environmental stewardship.



Shown as:  in product charts

## Green Seal

[www.GreenSeal.org](http://www.GreenSeal.org)

Green Seal® is an independent non-profit organization dedicated to safeguarding the environment and transforming the marketplace by promoting the manufacture, purchase, and use of environmentally responsible products and services.

- The Green Seal Standard for Sanitary Paper Products, GS-1, establishes environmental, health, and social requirements for products such as bathroom tissue, facial tissue, paper towels, napkins, and placemats for both institutional and retail markets.
- The standard addresses the life cycle issues for sanitary paper products. The life-cycle approach is used to ensure that all significant environmental impacts are considered in the development of a standard, from raw materials extraction through manufacturing to use and disposal.

### Green Seal-Certified Paper Products:

These products meet Green Seal™ Standard GS-1 based on chlorine-free processing, energy and water efficiency, and content of 100% recovered material with a minimum of 25% post-consumer material for bath tissue and 50% post-consumer material for napkins and towel.

### Green Seal-Certified Hand Soaps:

These products meet Green Seal™ Standard GS-41A based on effective performance and protective limits on VOCs and human & environmental toxicity.



Identified as Mixed or Recycled

## Forest Stewardship Council® (FSC®)

<https://us.fsc.org/en-us/certification>

FSC ([www.fsc.org](http://www.fsc.org)) certification ensures that products come from responsibly managed forests and other controlled sources that provide environmental, social and economic benefits. FSC Chain-of-Custody certification traces the path of products from forests through the supply chain.

Over the past 20 years, FSC® has earned a reputation as the most rigorous, credible forest certification system. FSC is the only forest certification system governed by an open membership (General Assembly) where interests are equally balanced by economic, social and environmental chambers.

- Certifiers assess forest management using the FSC standards. Certifiers are independent of FSC and the companies they are auditing. This third-party verification is crucial to the integrity of the FSC system.
- Forest Management certification provides assurance that forests are being managed to the highest environmental and social standards.
- Chain-of-Custody certification provides assurance that products bearing the FSC label directly support responsible forest management.
- **FSC Mix (FSC M) and FSC Recycled (FSC R)** certifications are available for all Essity mills in North America.




Shown as:  in product charts

## Biodegradable Products Institute™ (BPI)

[www.BPIworld.org](http://www.BPIworld.org)

Biodegradable Products Institute™ (BPI) compostability testing reviews the materials to ensure they will properly break down in the commercial composting process. One of the largest independent compost certification groups in North America.

- All Tork Universal and Advanced napkins, including custom print, are certified compostable. These napkins can be safely disposed of and are compostable in municipal or industrial aerobic facilities.



Shown as:  in product charts

## USDA Certified Biobased Product

[www.biopreferred.gov](http://www.biopreferred.gov)

The BioPreferred Program is a USDA-led initiative that aims to facilitate the development and expansion of markets for biobased products. The increased development, purchase, and use of biobased products will reduce our Nation's reliance on petroleum, and increase the use of renewable agricultural materials.

- The BioPreferred Program is transforming the marketplace for biobased products through two initiatives: mandatory purchasing requirements for Federal Agencies and Federal contractors and voluntary product certification and labeling.



Shown as:  in product charts

## CMA Compostable Hand Towels

All Tork hand towels are verified compostable by a third party. Towels are accepted at CMA-I and CMA-S facilities. Hand towels also meet compostable requirements under ASTM D6400 and D6868 test standards.

Identified as "EPA CPG" in recycled content section

## EPA Environmental Purchasing Compliant

[www.epa.gov/smm/comprehensive-procurement-guideline-cpg-program](http://www.epa.gov/smm/comprehensive-procurement-guideline-cpg-program)

The U.S. Environmental Protection Agency (EPA) Comprehensive Procurement Guidelines (CPG) has set the minimum amount of post-consumer waste to be used in products that are made with the recovered materials.



## USGBC

These certifications help a facility earn credits toward LEED certification. [usgbc.org](http://usgbc.org)

- Forest Stewardship Council® (FSC®)
- ECOLOGO®
- Green Seal
- EPA Environmental Purchasing Compliant
- USDA Certified Biobased Product

# Product attributes and certifications

Watch for these identifications throughout the catalog.



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)



Shown as:   
in product charts

## Easy to use

Many Tork Hygiene Systems are certified by the Swedish Rheumatism Association (SRA) and proven to be easy to use, making hygiene accessible for all, even for children, elderly and people with limited hand function.



Shown as:   
in product charts

## ADA-compliant

ADA guarantees that people with disabilities have the same opportunities as everyone else to participate in the mainstream of American life.



Shown as:   
in product charts

## Tork Easy Handling®

Ergonomically designed solutions for easier carrying, opening and disposing of packaging to make daily work easier.



Shown as:   
in product charts

## Tork Vision Cleaning<sup>1</sup>

The world's leading facility management solution for data-driven cleaning. It empowers cleaning teams with new and smarter ways of working. **GBAC STAR registered.**



## Septic Safe

End users who have septic systems require Toilet Paper that does not clog those systems. Essity Professional Hygiene North America certifies that our Toilet Paper products are safe for use in septic systems.



TorkSelect

## TorkSelect Systems

TorkSelect represents our value-added, high-performing dispenser Systems. TorkSelect Systems deliver the following benefits:

- Lowered cost by reducing usage
- Labor savings
- Advanced hygiene features
- Advanced environmental benefits
- Enhanced image



Shown as:   
in product charts

## Carbon neutral

[www.climate-id.com/en-gb/9VIUDN](http://www.climate-id.com/en-gb/9VIUDN)

Climate neutral certified by ClimatePartner<sup>2</sup>.



Shown as:   
in product charts

## National Sanitation Foundation®

[www.nsf.org](http://www.nsf.org)

NSF provides standards development, product certification, auditing, education and risk management for public health and the environment.



Shown as:   
in product charts

## HACCP International

[haccp-international.com](http://haccp-international.com)

HACCP International specializes in certification of food safe equipment, products and services that support food businesses.



Shown as:   
in product charts

## exelCLEAN®

Our patented exelCLEAN foam-spun technology creates a unique internal structure, giving Tork cleaning cloths a faster and more hygienic result.



AMS 3819E  
Certified

Shown as:   
in product charts

## Aerospace Material Standard (AMS 3819E)

Products certified for aviation use.

<sup>1</sup> Tork Vision Cleaning was formerly known as Tork EasyCube®

<sup>2</sup> A range of dispensers are carbon neutral, certified by ClimatePartner. The carbon emissions have been reduced with certified renewable electricity and compensated with climate projects.



# Table of contents

|                            |           |
|----------------------------|-----------|
| <b>Washroom</b>            | <b>6</b>  |
| Hand Towels                | 10-21     |
| Air Fresheners             | 22-23     |
| Soap and Sanitizer         | 24-27     |
| Toilet Paper               | 28-34     |
| Toilet Seat Covers         | 34        |
| Facial Tissue              | 35        |
| <b>Wiping and Cleaning</b> | <b>36</b> |
| Dispensers                 | 38        |
| Wiping                     | 39-42     |
| ShopMax                    | 42        |
| Cleaning                   | 43-46     |
| Microfibers                | 47        |
| Foodservice Towels         | 48-49     |
| Everwipe by Tork           | 50-51     |
| Centerfeed                 | 52-54     |
| Perforated Towels          | 54        |
| <b>Tabletop</b>            | <b>55</b> |
| Dispenser Napkins          | 56-61     |
| Dinner Napkins             | 62-63     |
| Guest Towel                | 62        |
| Beverage Napkins           | 63        |



# Washroom

## Making washrooms work for your business

Whether you want to make an impression, show you care for your visitors, maintain hygiene standards or keep control of costs, we've got something that's right for you.



## Make sure your washrooms deliver a great experience

Tork solutions deliver better hygiene and increase efficiency. Every business has different washroom requirements. We can help you find a hygienic, cost-effective combination of products that is just right for your customer.




Many of our washroom dispensers are Tork Vision Cleaning enabled as indicated in the charts.





## Tork Value-Added products and dispensers

Tork Value-Added Systems help you improve hygiene, enhance image, reduce usage and waste, and protect the environment. Tork Elevation, Tork Image Design, Xpress, Intuition, Tork PeakServe, Matic, Xpressnap, and Tork Performance dispensers signify the very best Tork has to offer. Our Value-Added Systems provide a range of quality refills from our softest leaf-printed Premium products to our most sustainable natural Universal products delivering the flexibility to address a variety of customer needs. Our Premium soap and sanitizer products and specialty wipers offer superior solutions.



## Tork Standard products and dispensers

Tork Standard products deliver quality and reliability at an affordable price. Customers will have dispensers they can count on and a range of Universal and Advanced refill products to choose from, including 100% recycled, third-party certified products that help them lighten their environmental footprint.





## What is the Tork Washroom

Making the right impression while caring for your customers and colleagues is easy with our high-quality washroom ranges. Our tried and tested combinations give you an easy choice.

### Tork Hand Towels

Walking out of a restroom with wet hands makes for an unpleasant experience. Make sure your colleagues and customers can get clean, dry hands and get back to business by stocking up on the right paper hand towels.

**Drying hands with Tork paper towels will reduce more bacteria.\***  
The smart dispenser leaves the next user a clean, untouched sheet.



### Tork Air Fresheners

It's easy to keep your restrooms constantly fresh. Tork air fresheners are designed to deliver a pleasant restroom experience. Tork Constant Air Freshener makes refilling easy and cleaning more efficient.




### Tork Soap and Sanitizer

Secure the new hygiene standard with our quality and effective skincare solutions. Our specially formulated products and award-winning dispensers paired with industry-leading Tork paper products to promote hand hygiene.



### Tork Toilet Paper

Surprise restroom guests with great hospitality in the one of the most overlooked of places. Whether your priority is luxury, easy maintenance or cost-effectiveness, you can select from a range of toilet paper roll qualities and always find one that meets your needs.



\* When washing with soap, water, followed by drying with a paper towel, vs only using soap and water. Based on modified EN 1499 standard, tested with E.Coli., using Tork Mild Soap refill art. 420501 and Tork PeakServe® refill art. 100585.

## Innovative design lines

### Tork Image™ Design

Impress your guests with a truly high-end restroom environment. Stylish stainless steel with anti-fingerprint coating looks great and stays clean.



### Tork Elevation®


A seamless, complete and functional dispenser line with a modern feel. Available in black or white.





# Tork PeakServe Continuous Hand Towel system (H5)

Restroom experience is important, and the world has never paid more attention to cleaning and hygiene than now. The Tork PeakServe® Continuous™ Hand Towel system offers the highest capacity<sup>1</sup> on the market with up to 250% more towels<sup>2</sup>. Together with one-at-a-time dispensing this means fewer run-out and many more people served between refills. And since people only touch the towels they use, you get a very hygienic hand drying solution that helps you secure the new hygiene standard.



**250%**  
more hand towels  
for less refilling  
and a better  
restroom flow<sup>2</sup>

## Tork PeakServe Automatic Dispenser

**An automatic hand towel dispenser you can rely on**

The new Tork PeakServe Automatic is designed for maximum reliability, to save cleaners' time and provide a superior user experience. It has the longest battery life<sup>3</sup> and is 99.99% jam-free.<sup>4</sup>

- Tork PeakServe Continuous hand towels are excellent for high and peak traffic restrooms
- Faster dispensing serves guests in less than three seconds — Minimizing lines in washroom by up to 4 times
- Free up space in storage rooms and cleaning carts with refills that are compressed by 50%<sup>5</sup>

<sup>1</sup> Compared to competitor's longest roll towel in North America.

<sup>2</sup> Compared to Tork Universal refills and folded towel dispenser 552000.

<sup>3</sup> Compared to Georgia Pacific enMotion 10 dispenses 200 rolls per battery set (192,000 10-inch towels) and Kimberly-Clark Icon dispenses 150,000 towels. Tork PeakServe Automatic dispenses at least 500,000 paper hand towels per battery set using refill article 105065.

<sup>4</sup> Used with articles 105065 and 105066.

<sup>5</sup> Compared to Tork H2 Universal refills 150299.

## Tork PeakServe Continuous Hand Towel

Refill ID: H5



- Highest capacity, up to 2 100 towels per dispenser, ensures hand towels are always available
- Top up in use allows dispensers to be refilled at your convenience
- Smooth, one-at-a-time dispensing lowers consumption and ensures that hand hygiene is accessible to all with Easy-to-use certification<sup>1</sup>
- Maximize efficiency with one system and one refill across your entire facility thanks to 4 dispensing formats
- Carbon neutral Tork PeakServe Elevation Dispensers in Standard and Mini available, produced with certified renewable electricity and compensated with climate projects
- Tork PeakServe refills have a 22% reduced carbon footprint<sup>2</sup>
- Reliable automatic dispenser with 2x longer battery life time, flexible refilling and 99,99% jam-free dispensing<sup>3</sup>

## Tork PeakServe Continuous Hand Towel Dispensers

Refill ID: H5

| SKU    | Description                             | Design Line | Color | Material      | Size H x W x D (in)                                | Units/Case |   |   |   |   |
|--------|-----------------------------------------|-------------|-------|---------------|----------------------------------------------------|------------|---|---|---|---|
| 552520 | Standard                                | Elevation   | White | Plastic       | 28.74 x 14.57 x 3.98<br>(73.0 x 37.01 x 10.11 cm)  | 1          | ● | ● | ● | ● |
| 552528 | Standard                                | Elevation   | Black | Plastic       | 28.74 x 14.57 x 3.98<br>(73.0 x 37.01 x 10.11 cm)  | 1          | ● | ● | ● | ● |
| 552530 | Mini                                    | Elevation   | White | Plastic       | 19.3 x 14.44 x 3.97<br>(49.02 x 36.68 x 10.08 cm)  | 1          | ● | ● | ● | ● |
| 552538 | Mini                                    | Elevation   | Black | Plastic       | 19.3 x 14.44 x 3.97<br>(49.02 x 36.68 x 10.08 cm)  | 1          | ● | ● | ● | ● |
| 552540 | Automatic                               | Elevation   | White | Plastic       | 25.15 x 14.46 x 4.04<br>(63.88 x 36.73 x 10.26 cm) | 1          | ● | ● | ● | ● |
| 552548 | Automatic                               | Elevation   | Black | Plastic       | 25.15 x 14.46 x 4.04<br>(63.88 x 36.73 x 10.26 cm) | 1          | ● | ● | ● | ● |
| 552522 | Large Recessed Cabinet Adapter          |             | White | Plastic       | 20.43 x 14.37 x 3.78<br>(51.89 x 36.50 x 9.60 cm)  | 1          | ● | ● | ● | ● |
| 552521 | Small Recessed Cabinet Adapter          |             | White | Plastic       | 17.72 x 14.37 x 3.78<br>(45.01 x 36.50 x 9.60 cm)  | 1          | ● | ● | ● | ● |
| 351000 | AC / DC Adapter for Automatic Dispenser |             | Black | Brass/Plastic | 9.41 x 1.3 x 1.3<br>(23.9 x 3.3 x 3.3 cm)          | 1          |   |   |   |   |

## Tork PeakServe Continuous Hand Towel Filler Panels

Refill ID: H5

| SKU    | Description                                   | Color           | Material        | Size H x W x D (in)                               | Units/Case  |   |
|--------|-----------------------------------------------|-----------------|-----------------|---------------------------------------------------|-------------|---|
| 552501 | Standard<br>(for use with 552520 and 552528)  | Stainless Steel | Metal & Plastic | 29.25 x 17.63 x 3.88<br>(74.29 x 44.78 x 9.85 cm) | 1 Panel/Box | ● |
| 552503 | Mini<br>(for use with 552530 and 552538)      | Stainless Steel | Metal & Plastic | 22.52 x 17.63 x 3.88<br>(57.20 x 44.78 x 9.85 cm) | 1 Panel/Box | ● |
| 552505 | Automatic<br>(for use with 552540 and 552548) | Stainless Steel | Metal & Plastic | 25.65 x 17.63 x 3.88<br>(65.15 x 44.78 x 9.85 cm) | 1 Panel/Box | ● |



- Hand towels compressed by 50% allow you to carry and store twice as much<sup>4</sup>
- Two refill qualities to meet the needs and quality of your restroom environment

## Tork PeakServe Continuous Hand Towels

Refill ID: H5

| SKU    | Quality Tier | Color                | Ply | Towel Size W x L (in)             | Towels/Package | Packages/Case | Towels/Case |   |   |       |
|--------|--------------|----------------------|-----|-----------------------------------|----------------|---------------|-------------|---|---|-------|
| 105066 | Premium      | White with Blue Leaf | 1   | 7.91 x 8.85<br>(20.09 x 22.48 cm) | 270            | 12            | 3,240       | ● | ● | Mixed |
| 105065 | Advanced     | White                | 1   | 7.91 x 8.85<br>(20.09 x 22.48 cm) | 410            | 12            | 4,920       | ● | ● | Mixed |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

<sup>1</sup> Easy-to-use certification on H5 standard, H5 mini and H5 automatic dispensers.

<sup>2</sup> Compared to the refill carbon footprint before April 1st 2025 when commencing purchase of renewable electricity, verified and matched through Guarantees of Origin, for our paper making operations. The resulting carbon footprint reductions were quantified in a third party reviewed cradle-to-grave Life Cycle Assessment.

<sup>3</sup> Compared to Georgia Pacific enMotion 10 dispenses 150 rolls per battery set (144,000 10-inch towels) and Kimberly-Clark Icon dispenses 150,000 towels. Tork PeakServe Automatic dispenses at least 500,000 paper hand towels per battery set using refill article 105065. Jam-free testing using articles 105065 and 105066.

<sup>4</sup> Compared to Tork folded towel 150299.



## Tork Matic Hand Towel Roll system (H1)

Developed for easy maintenance and refilling, Tork Matic® dispenser system is simple to understand and operate for cleaning staff as well as for visitors. Ideal for medium traffic restroom, it is available in manual or automatic in three attractive styles. Whether you are looking for hands-free hygiene, want your washroom to make a good impression, or desire cost-effective service, Tork Matic is your solution.



High-capacity  
system = up to  
**1400**  
hand towels

- Controlled consumption
- Tork Matic® Manual and Intuition® Sensor models available
- Multiple sheet length settings on Automatic dispensers
- Protected paper in the Automatic dispenser for optimal hygiene
- Large offer of dispensers and refills ensuring a combination that can suit all needs

Show your  
commitment  
to sustainability  
with Tork natural  
color hand towels.  
Same high quality  
— in a natural color.



## Tork Matic Hand Towel Roll

Refill ID: H1



5511204



5511284



461202



461222



461223



5510202



5510282



461002



461022



461023



351000

- High capacity, ideal for restrooms with frequent use
- Delivers one sheet at a time dispensing, reduces consumption and cost
- Upgraded Automatic Dispenser with improved functionality and longer battery life for reliable dispensing
- One sheet at a time dispensing helps to minimize cross contamination<sup>1</sup>
- Automatic dispenser conceals towel until activated, reducing potential contamination even further
- 99.9% Jam free<sup>2</sup>

## Tork Matic Hand Towel Roll Dispensers

Refill ID: H1

| SKU     | Description                                                                                                                            | Design Line | Color           | Material          | Stub Roll Feature | Refill Indicator | Size H x W x D (in)                                | Units/Case |  |  |  |
|---------|----------------------------------------------------------------------------------------------------------------------------------------|-------------|-----------------|-------------------|-------------------|------------------|----------------------------------------------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 5511204 | Automatic<br>(Batteries not included)                                                                                                  | Elevation   | White           | Plastic           | ●                 | ●                | 14.5 x 13 x 8<br>(36.83 x 33.02 x 20.32 cm)        | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 5511284 | Automatic<br>(Batteries not included)                                                                                                  | Elevation   | Black           | Plastic           | ●                 | ●                | 14.5 x 13 x 8<br>(36.83 x 33.02 x 20.32 cm)        | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 461202  | Automatic<br>(Batteries not included)                                                                                                  | Image       | Stainless Steel | Metal/<br>Plastic | ●                 |                  | 14.69 x 13.58 x 8.03<br>(37.31 x 34.49 x 20.40 cm) | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 461222  | Recessed, Automatic<br>(Batteries not included)                                                                                        | Image       | Stainless Steel | Metal/<br>Plastic | ●                 |                  | 26.97 x 17.60 x 7.99<br>(68.50 x 44.70 x 20.29 cm) | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 461223  | In-Wall Recessed, Automatic<br>(Batteries not included)                                                                                | Image       | Stainless Steel | Metal/<br>Plastic | ●                 |                  | 20.55 x 17.64 x 7.87<br>(52.2 x 44.81 x 19.99 cm)  | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 5510202 | Manual                                                                                                                                 | Elevation   | White           | Plastic           | ●                 | ●                | 14.65 x 13.2 x 8.1<br>(37.21 x 33.53 x 20.57 cm)   | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 5510282 | Manual                                                                                                                                 | Elevation   | Black           | Plastic           | ●                 | ●                | 14.65 x 13.2 x 8.1<br>(37.21 x 33.53 x 20.57 cm)   | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 461002  | Manual                                                                                                                                 | Image       | Stainless Steel | Metal/<br>Plastic | ●                 |                  | 15.75 x 13.58 x 8.07<br>(40.01 x 34.49 x 20.5 cm)  | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 461022  | Recessed                                                                                                                               | Image       | Stainless Steel | Metal/<br>Plastic | ●                 |                  | 26.97 x 17.64 x 7.87<br>(68.5 x 44.81 x 19.99 cm)  | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 461023  | In-Wall Recessed                                                                                                                       | Image       | Stainless Steel | Metal/<br>Plastic | ●                 |                  | 20.55 x 17.64 x 7.87<br>(52.2 x 44.81 x 19.99 cm)  | 1          | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 351000  | AC / DC Adapter for Automatic Dispenser<br>(This SKU is compatible with Elevation Design (5511204 & 5511284) and Tork PeakServe lines) |             | Black           | Brass/<br>Plastic |                   |                  | 9.41 x 1.3 x 1.3<br>(23.9 x 3.3 x 3.3 cm)          | 1          |                                                                                       |                                                                                       |                                                                                       |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)


<sup>1</sup> Used with Tork refill articles 290088, 290089 & 290095. 20220208-001-Tork Matic Claim testing.

<sup>2</sup> When used with Tork refill articles 290088, 290089 & 290095.



## Tork Matic Hand Towel Roll

Refill ID: H1



| Tork Matic Hand Towel Roll Dispenser Accessories |                                                                                                                                                                             |           |                 |          |                                                    |            |                                                                                                   | Refill ID: H1                                                                                        |  |
|--------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|-----------------|----------|----------------------------------------------------|------------|---------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|--|
| SKU                                              | Description                                                                                                                                                                 | Refill ID | Color           | Material | Size H x W x D (in)                                | Units/Case | <br>TorkSelect | <br>ADA Compliant |  |
| 3106440                                          | Recessed Trim Ring Kit for Tork Matic Hand Towel Roll Dispenser, Automatic <i>(for use with 5511204 and 5511284, to be used when recessing dispenser into a wall)</i>       | H1        | Stainless Steel | Metal    | 18.25 x 16.0 x 3.75<br>(46.36 x 40.64 x 9.63 cm)   | 1          |                |                   |  |
| 3106220                                          | Recessed Trim Ring Kit for Tork Matic Hand Towel Roll Dispenser <i>(for use with 5510202, 5510282, to be used when recessing dispenser into a wall)</i>                     | H1        | Stainless Steel | Metal    | 19.75 x 15.75 x 3.75<br>(50.17 x 40.01 x 9.53 cm)  | 1          |                |                   |  |
| 3096020                                          | Steel Filler Panel for Tork Matic Hand Towel Roll Dispenser <i>(for use with 5510202, 5510282, to be used when recessing dispenser into a folded towel cabinet)</i>         | H1        | Stainless Steel | Metal    | 22.56 x 17.63 x 3.88<br>(57.30 x 44.78 x 9.86 cm)  | 1          |                |                   |  |
| 3096040                                          | Filler Panel for Tork Matic Hand Towel Roll Dispenser, Automatic <i>(for use with 5511204 and 5511284, to be used when recessing dispenser into a folded towel cabinet)</i> | H1        | Stainless Steel | Metal    | 22.56 x 17.63 x 3.88<br>(57.30 x 44.78 x 9.86 cm)  | 1          |                |                   |  |
| 309051                                           | Recess Unit with Bin for Tork Recessed Dispensers <i>(for use with Image Design H1/H11 Recessed dispensers &amp; Elevation H1 dispensers + filler panels)</i>               | H1        | Stainless Steel | Metal    | 56.0 x 17.125 x 9.0<br>(142.24 x 43.50 x 22.86 cm) | 1          |               |                  |  |



- A range of towel options
- Adjustable towel length with the sensor dispenser
- Natural color to show your guests you care for the environment
- Premium, Advanced and Universal quality levels
- Sustainable certifications

| Tork Matic Hand Towel Rolls |             |              |                      |     |                                                                                                                      |                   |                                                          |            |  |  |          | Refill ID: H1    |  |  |  |
|-----------------------------|-------------|--------------|----------------------|-----|----------------------------------------------------------------------------------------------------------------------|-------------------|----------------------------------------------------------|------------|--|--|----------|------------------|--|--|--|
| SKU                         | Description | Quality Tier | Color                | Ply | Towel Size W x L (in)<br><sup>A</sup> 5511204 & 5511284<br><sup>B</sup> 5510202 & 5510282 & 461002 & 461022 & 461023 | Linear Feet/Roll  | Towels/Case                                              | Rolls/Case |  |  |          | Recycled Content |  |  |  |
| 290094                      | Extra Soft  | Premium      | White with Blue Leaf | 2   | <sup>A</sup> 7.7 x adjustable<br>(19.56 cm x adjustable)<br><sup>B</sup> 7.7 x 9.5<br>(19.56 x 24.1 cm)              | 300<br>(91.44 m)  | <sup>A</sup> 2,700<br>(8" setting)<br><sup>B</sup> 2,274 | 6          |  |  | Mixed    |                  |  |  |  |
| 290096                      | Soft        | Premium      | White with Blue Leaf | 2   | <sup>A</sup> 7.7 x adjustable<br>(19.56 cm x adjustable)<br><sup>B</sup> 7.7 x 9.5<br>(19.56 x 24.1 cm)              | 575<br>(175.26 m) | <sup>A</sup> 5,175<br>(8" setting)<br><sup>B</sup> 4,356 | 6          |  |  | Mixed    | EPA CPG          |  |  |  |
| 290095                      | Soft        | Advanced     | White                | 1   | <sup>A</sup> 7.7 x adjustable<br>(19.56 cm x adjustable)<br><sup>B</sup> 7.7 x 9.5<br>(19.56 x 24.1 cm)              | 900<br>(274.32 m) | <sup>A</sup> 8,100<br>(8" setting)<br><sup>B</sup> 6,816 | 6          |  |  | Mixed    |                  |  |  |  |
| 290092A                     |             | Advanced     | White with Gray Leaf | 2   | <sup>A</sup> 7.7 x adjustable<br>(19.56 cm x adjustable)<br><sup>B</sup> 7.7 x 9.5<br>(19.56 x 24.1 cm)              | 525<br>(160.02 m) | <sup>A</sup> 4,722<br>(8" setting)<br><sup>B</sup> 3,978 | 6          |  |  | Recycled | 100%,<br>EPA CPG |  |  |  |
| 290089                      |             | Universal    | White                | 1   | <sup>A</sup> 7.7 x adjustable<br>(19.56 cm x adjustable)<br><sup>B</sup> 7.7 x 9.5<br>(19.56 x 24.1 cm)              | 700<br>(213.36 m) | <sup>A</sup> 6,300<br>(8" setting)<br><sup>B</sup> 5,304 | 6          |  |  | Recycled | 100%             |  |  |  |
| 290088                      |             | Universal    | Natural              | 1   | <sup>A</sup> 7.7 x adjustable<br>(19.56 cm x adjustable)<br><sup>B</sup> 7.7 x 9.5<br>(19.56 x 24.1 cm)              | 700<br>(213.36 m) | <sup>A</sup> 6,300<br>(8" setting)<br><sup>B</sup> 5,304 | 6          |  |  | Recycled | 100%,<br>EPA CPG |  |  |  |

## Tork Hand Towel Roll

## Refill ID: H80



771828

772828

- Electronic and mechanical options
- Durable and easy to maintain
- Delivers a hygienic and efficient dispensing experience

## Tork Hand Towel Roll Dispensers\*

Refill ID: H80

| SKU    | Description                            | Color | Material | Size H x W x D (in)                               | Units/Case |  |  |
|--------|----------------------------------------|-------|----------|---------------------------------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 771828 | Electronic<br>(Batteries not included) | Black | Plastic  | 15.95 x 12.32 x 9.32<br>(40.51 x 31.29 x 23.67cm) | 1          | ●                                                                                   | ●                                                                                   |
| 772828 | Mechanical                             | Black | Plastic  | 15.95 x 12.32 x 9.32<br>(40.51 x 31.29 x 23.67cm) | 1          | ●                                                                                   | ●                                                                                   |



8030630

8031400

8031300

- Y-notch roll towel refills
- Available in white and kraft
- Premium, Advanced and Universal quality levels

## Tork Hand Towel Rolls\*

Refill ID: H80

| SKU     | Quality Tier | Color         | Ply | Towel Size W x L (in)       | Linear Feet/ Roll  | Towels/Case            | Rolls/ Case |  |  |  | Recycled Content |  |  |
|---------|--------------|---------------|-----|-----------------------------|--------------------|------------------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 8030630 | Premium      | White         | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 600<br>(182.88 m)  | 4,330<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Mixed                                                                                 |                  |                                                                                       | ●                                                                                     |
| 8031050 | Advanced     | White         | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 1,000<br>(304.8 m) | 7,200<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Mixed                                                                                 |                  |                                                                                       | ●                                                                                     |
| 8038050 | Advanced     | White         | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Mixed                                                                                 |                  |                                                                                       | ●                                                                                     |
| 8031900 | Universal    | White         | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Recycled                                                                              | 100%,<br>EPA CPG |                                                                                       | ●                                                                                     |
| 8031600 | Universal    | White         | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 630<br>(192.02 m)  | 4,536<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Recycled                                                                              | 100%,<br>EPA CPG |                                                                                       | ●                                                                                     |
| 8031400 | Universal    | Natural White | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Recycled                                                                              | 100%,<br>EPA CPG | ●                                                                                     | ●                                                                                     |
| 8031300 | Universal    | Natural       | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Recycled                                                                              | 100%,<br>EPA CPG | ●                                                                                     | ●                                                                                     |
| 8031500 | Universal    | Natural       | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 630<br>(192.02 m)  | 4,536<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Recycled                                                                              | 100%,<br>EPA CPG |                                                                                       | ●                                                                                     |
| 8031000 | Universal    | Natural       | 1   | 8 x 10<br>(20.32 x 25.4 cm) | 1,000<br>(304.8 m) | 7,200<br>(10" setting) | 6           | ●                                                                                     | ●                                                                                     | Recycled                                                                              | 100%,<br>EPA CPG | ●                                                                                     | ●                                                                                     |

\*Available to legacy Wausau/shared customers only.



## Tork Hand Towel Roll

Refill ID: H71



771728



772728

- Electronic and mechanical options
- Durable and easy to maintain
- Delivers a hygienic and efficient dispensing experience

## Tork Hand Towel Roll Dispensers\*

Refill ID: H71

| SKU    | Description                            | Refill ID | Color | Material | Size H x W x D (in)                               | Units/Case |  |  |
|--------|----------------------------------------|-----------|-------|----------|---------------------------------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 771728 | Electronic<br>(Batteries not included) | H71       | Black | Plastic  | 15.95 x 12.32 x 9.32<br>(40.51 x 31.29 x 23.67cm) | 1          |  |  |
| 772728 | Mechanical                             | H71       | Black | Plastic  | 15.95 x 12.32 x 9.32<br>(40.51 x 31.29 x 23.67cm) | 1          |  |  |



7170630



7171400



7171300

- I-notch roll towel refills
- Available in white and kraft
- Premium, Advanced and Universal quality levels

## Tork Hand Towel Rolls\*

Refill ID: H71

| SKU     | Quality Tier | Color         | Ply | Towel Size W x L (in)         | Linear Feet/ Roll  | Towels/Case            | Rolls/ Case |  |  |  | Recycled Content |  |  |
|---------|--------------|---------------|-----|-------------------------------|--------------------|------------------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 7170630 | Premium      | White         | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 600<br>(182.88 m)  | 4,330<br>(10" setting) | 6           |  |  | Mixed                                                                                 |                  |                                                                                       |  |
| 7171050 | Advanced     | White         | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 1,000<br>(304.8 m) | 7,200<br>(10" setting) | 6           |  |  | Mixed                                                                                 |                  |                                                                                       |  |
| 7178050 | Advanced     | White         | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           |  |  | Mixed                                                                                 |                  |                                                                                       |  |
| 7171600 | Universal    | White         | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 630<br>(192.02 m)  | 4,536<br>(10" setting) | 6           |  |  | Recycled                                                                              | 100%,<br>EPA CPG |                                                                                       |  |
| 7171400 | Universal    | Natural White | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           |  |  | Recycled                                                                              | 100%,<br>EPA CPG |  |  |
| 7171300 | Universal    | Natural       | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 800<br>(243.84 m)  | 5,760<br>(10" setting) | 6           |  |  | Recycled                                                                              | 100%,<br>EPA CPG |  |  |
| 7171020 | Universal    | Natural       | 1   | 7.5 x 10<br>(19.05 x 25.4 cm) | 1,000<br>(304.8 m) | 7,200<br>(10" setting) | 6           |  |  | Recycled                                                                              | 100%,<br>EPA CPG |  |  |

\*Available to legacy Wausau/shared customers only.

## Tork Mini Hand Towel Roll

Refill ID: H86



8634550



8621400



8620100

- Y-notch roll towel refills for mini mechanical model
- Available in white and kraft
- Advanced and Universal quality levels

| Tork Mini Hand Towel Rolls* |              |               |     |                              |                   |                        |            |                                                                                     |                                                                                     | Refill ID: H86                                                                      |                  |                                                                                     |                                                                                     |
|-----------------------------|--------------|---------------|-----|------------------------------|-------------------|------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SKU                         | Quality Tier | Color         | Ply | Towel Size W x L (in)        | Linear Feet/Roll  | Towels/Case            | Rolls/Case |  |  |  | Recycled Content |  |  |
| 8634550                     | Advanced     | White         | 1   | 8 x 11<br>(20.32 x 27.94 cm) | 450<br>(137.16 m) | 5,892<br>(11" setting) | 12         | ●                                                                                   | ●                                                                                   | Mixed                                                                               |                  |                                                                                     | ●                                                                                   |
| 8621400                     | Universal    | Natural White | 1   | 8 x 11<br>(20.32 x 27.94 cm) | 425<br>(129.54 m) | 5,556<br>(11" setting) | 12         | ●                                                                                   | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |
| 8620100                     | Universal    | Natural       | 1   | 8 x 11<br>(20.32 x 27.94 cm) | 425<br>(129.54 m) | 5,556<br>(11" setting) | 12         | ●                                                                                   | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG |                                                                                     | ●                                                                                   |
| 8631060                     | Universal    | Natural       | 1   | 8 x 11<br>(20.32 x 27.94 cm) | 550<br>(167.64 m) | 3,600<br>(11" setting) | 6          | ●                                                                                   | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |

## Tork Mini Hand Towel Roll

Refill ID: H76



7674550

- I-notch roll towel for mini mechanical model

| Tork Mini Hand Towel Roll* |              |       |     |                             |                   |                     |             |                                                                                       |                                                                                       | Refill ID: H76                                                                        |                                                                                       |  |
|----------------------------|--------------|-------|-----|-----------------------------|-------------------|---------------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--|
| SKU                        | Quality Tier | Color | Ply | Towel Size W x L (in)       | Linear Feet/ Roll | Towels/Case         | Rolls/ Case |  |  |  |  |  |
| 7674550                    | Advanced     | White | 1   | 7.5 x 11 (19.05 x 27.94 cm) | 450 (137.16 m)    | 5,892 (11" setting) | 12          |  |  | Mixed                                                                                 |  |  |

\*Available to legacy Wausau/shared customers only.

Tork Hand Towel Roll

Refill ID: H21



| Tork Hand Towel Roll Dispensers |                                                           |       |          |                                                    |            | Refill ID: H21                                                                                       |
|---------------------------------|-----------------------------------------------------------|-------|----------|----------------------------------------------------|------------|------------------------------------------------------------------------------------------------------|
| SKU                             | Description                                               | Color | Material | Size H x W x D (in)                                | Units/Case | <br>ADA Compliant |
| 83TR                            | Lever                                                     | Smoke | Plastic  | 12.82 x 12.49 x 8.6<br>(32.56 x 31.72 x 21.84 cm)  | 1          | ●                                                                                                    |
| 84TR                            | Lever Auto Transfer                                       | Smoke | Plastic  | 15.5 x 12.94 x 9.25<br>(39.37 x 32.87 x 23.50 cm)  | 1          | ●                                                                                                    |
| 86ECO                           | Electronic, Touch-Free<br><i>(Batteries not included)</i> | Smoke | Plastic  | 14.39 x 11.78 x 9.12<br>(36.55 x 29.92 x 23.16 cm) | 1          | ●                                                                                                    |



| Tork Hand Towel Rolls |              |         |     |                 |                  |                   |            |                                                                                       |                  |                                                                                       | Refill ID: H21                                                                        |
|-----------------------|--------------|---------|-----|-----------------|------------------|-------------------|------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                   | Quality Tier | Color   | Ply | Roll Width (in) | Linear Feet/Roll | Linear Feet/Case  | Rolls/Case |  | Recycled Content |  |  |
| RB800                 | Advanced     | White   | 1   | 7.875 (20 cm)   | 800 (243.8 m)    | 4,800 (1,463.0 m) | 6          | Recycled                                                                              | 100%             | ●                                                                                     | ●                                                                                     |
| 214405                | Advanced     | White   | 1   | 8.0 (20.32 cm)  | 1,000 (304.8 m)  | 6,000 (1,828.8 m) | 6          | Mixed                                                                                 |                  |                                                                                       | ●                                                                                     |
| RB8002                | Universal    | White   | 1   | 7.875 (20 cm)   | 800 (243.8 m)    | 4,800 (1,463.0 m) | 6          | Recycled                                                                              | 100%             | ●                                                                                     | ●                                                                                     |
| RB10002               | Universal    | White   | 1   | 7.875 (20 cm)   | 1,000 (304.8 m)  | 6,000 (1,828.8 m) | 6          | Recycled                                                                              | 100%             | ●                                                                                     | ●                                                                                     |
| RK800E                | Universal    | Natural | 1   | 7.875 (20 cm)   | 800 (243.8 m)    | 4,800 (1,463.0 m) | 6          | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     | ●                                                                                     |
| RK8002                | Universal    | Natural | 1   | 7.875 (20 cm)   | 800 (243.8 m)    | 4,800 (1,463.0 m) | 6          | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     | ●                                                                                     |



# Tork Xpress Multifold Hand Towel system (H2)

Serve more people. Run out less.

Our top-of-the-line multifold hand towel dispenser comes in two wall-mounted sizes as well as countertop, providing both comfort and hygiene. It's ideal for low to medium traffic restrooms. Choose between three attractive styles: high gloss black or white, or a stainless steel finish.

Spend less time servicing the washroom. Cleaning takes up time that could be better spent – especially when it comes to maintaining hygiene systems. It helps to have a high quality solution that's both easy to use and to service.



**71%**  
of cleaners wish  
that dispenser  
systems were  
easier to refill<sup>1</sup>

## Tork Xpress hand towel system and compressed refills

### Fit more in. Run out less.

The Tork Xpress® hand towel system is intuitive and easy to use. And its space-saving dispensers can now hold twice as many towels<sup>2</sup>, when using Tork Xpress compressed refills. They're the same high quality towels, but compressed by 50%.<sup>3</sup>

- One sheet at a time dispensing helps to minimise cross contamination
- Carbon neutral Tork Xpress® Image Design™ dispensers available, reduced with certified renewable electricity and compensated with climate projects

<sup>1</sup> Problem detection study conducted in US, UK, Mexico and China, 2020

<sup>2</sup> Compared to equivalent Tork standard folded towels in H2 Mini Dispenser

<sup>3</sup> Compared to equivalent Tork standard folded towels

## Tork Multifold Hand Towel

Refill ID: H2



- The simplest and most intuitive Tork hand towel dispenser to refill<sup>1</sup>
- Extra slim and attractive design
- Easy-to-use certified, making hand hygiene accessible for all, including people with reduced hand strength
- Tork Premium Multifold Towel carbon footprint has been reduced by 15%<sup>2</sup>

## Tork Xpress Multifold Hand Towel Dispensers

Refill ID: H2

| SKU    | Description | Design Line | Color           | Material       | Size H x W x D (in)                            | Units/Case |   |   |   |
|--------|-------------|-------------|-----------------|----------------|------------------------------------------------|------------|---|---|---|
| 463002 | Standard    | Image       | Stainless Steel | Metal/ Plastic | 18.625 x 13 x 3.9375 (47.31 x 33.02 x 10.0 cm) | 1          | ● | ● | ● |
| 553020 | Standard    | Elevation   | White           | Plastic        | 17.5 x 11.9 x 4.0 (44.4 x 30.2 x 10.2 cm)      | 1          |   | ● | ● |
| 553028 | Standard    | Elevation   | Black           | Plastic        | 17.5 x 11.9 x 4.0 (44.4 x 30.2 x 10.2 cm)      | 1          |   | ● | ● |
| 553120 | Mini        | Elevation   | White           | Plastic        | 11.6 x 11.9 x 4.0 (29.5 x 30.2 x 10.1 cm)      | 1          |   | ● | ● |
| 553128 | Mini        | Elevation   | Black           | Plastic        | 11.6 x 11.9 x 4.0 (29.5 x 30.2 x 10.1 cm)      | 1          |   | ● | ● |
| 302030 | Countertop* | Image       | Stainless Steel | Metal/ Plastic | 7.92 x 12.68 x 4.56 (20.12 x 32.21 x 11.58 cm) | 1          | ● |   | ● |
| 302020 | Countertop* | Elevation   | White           | Plastic        | 7.92 x 12.68 x 4.56 (20.12 x 32.21 x 11.58 cm) | 1          |   |   | ● |
| 302028 | Countertop* | Elevation   | Black           | Plastic        | 7.92 x 12.68 x 4.56 (20.12 x 32.21 x 11.58 cm) | 1          |   |   | ● |

\*Not compatible with H2 compressed and 424835 refills



- Serve twice as many users before refilling<sup>3</sup>
- Smaller bundles designed for easier handling
- Save space in storage, on cleaning carts and during transportation with bundles that are 50%<sup>4</sup> compressed

## Tork Xpress Compressed Multifold Hand Towel

Refill ID: H2

| SKU    | Description | Quality Tier | Color                | Ply | Panels | Towel Size W x L (in)    | Towels/Package | Packages/Case | Towels/Case |   |  |       |   |
|--------|-------------|--------------|----------------------|-----|--------|--------------------------|----------------|---------------|-------------|---|--|-------|---|
| 420590 | Compressed  | Premium      | White with Blue Leaf | 1   | 3      | 8.3 x 9.5 (21.08 x 8 cm) | 200            | 12            | 2,400       | ● |  | Mixed | ● |
| 424834 | Compressed  | Advanced     | White with Gray Leaf | 1   | 3      | 8.3 x 9.5 (21.08 x 8 cm) | 250            | 12            | 3,000       | ● |  | Mixed | ● |
| 424835 | Compressed  | Advanced     | White                | 1   | 3      | 8.3 x 9.5 (21.08 x 8 cm) | 250            | 16            | 4,000       | ● |  | Mixed | ● |



- Superior comfort with maximum hygiene
- Wide assortment of hand towels featuring the leaf embossing

## Tork Xpress Multifold Hand Towel

Refill ID: H2

| SKU    | Description | Quality Tier | Color                | Ply | Panels | Towel Size W x L (in)           | Towels/Package | Packages/Case | Towels/Case |   |  |       |               |
|--------|-------------|--------------|----------------------|-----|--------|---------------------------------|----------------|---------------|-------------|---|--|-------|---------------|
| 101298 | Extra Soft  | Premium      | White with Blue Leaf | 2   | 4      | 9.125 x 12.8 (23.18 x 32.51 cm) | 94             | 16            | 1,504       | ● |  | Mixed | ●             |
| MB579  | Soft        | Premium      | White with Blue Leaf | 2   | 3      | 9.125 x 9.5 (23.18 x 24.13 cm)  | 135            | 16            | 2,160       | ● |  | Mixed | EPA CPG       |
| 420580 |             | Premium      | White                | 1   | 3      | 9.0 x 9.5 (22.86 x 24.13 cm)    | 250            | 12            | 3,000       | ● |  | Mixed | ●             |
| 101293 | Soft        | Advanced     | White with Gray Leaf | 2   | 3      | 9.125 x 9.5 (23.18 x 24.13 cm)  | 189            | 16            | 3,024       | ● |  | Mixed | 100%, EPA CPG |
| 424824 |             | Advanced     | White                | 1   | 3      | 9.0 x 9.5 (22.86 x 24.13 cm)    | 250            | 16            | 4,000       | ● |  | Mixed | ●             |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

<sup>1</sup> Tork Xpress Multifold compared to Tork Matic and Tork PeakServe.


<sup>2</sup> On average, compared to the average of all Tork H2 premium tier refill carbon footprint before April 1st 2025 when commencing purchase of renewable electricity, verified and matched through Guarantees of Origin, for our paper making operations. The resulting carbon footprint reductions were quantified in a third party reviewed cradle-to-grave Life Cycle Assessment.

<sup>3</sup> Compared to equivalent Tork standard folded towels, based on each guest using two towels.

<sup>4</sup> Compared to equivalent Tork standard folded towels.

## Tork Multifold Hand Towel

Refill ID: H2



## Tork Xpress Recessed Cabinet Towel Adapters

Refill ID: H2

| SKU    | Description         | Color | Material | Size H x W x D (in)                             | Units/Case |  |  |
|--------|---------------------|-------|----------|-------------------------------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 309695 | Large               | White | Plastic  | 19.65 x 10.039 x 3.7<br>(49.91 x 25.5 x 9.4 cm) | 1          | ●                                                                                   | ●                                                                                   |
| 309696 | Medium              | White | Plastic  | 17.32 x 10.039 x 3.7<br>(43.99 x 25.5 x 9.4 cm) | 1          | ●                                                                                   | ●                                                                                   |
| 309697 | Small               | White | Plastic  | 5.078 x 10.94 x 3.7<br>(12.9 x 27.79 x 9.4 cm)  | 4          |                                                                                     | ●                                                                                   |
| 555123 | Compressed Adapter* | White | Plastic  | 2.3 x 9.6 x 3.6<br>(5.842 x 24.384 x 9.144 cm)  | 1          | ●                                                                                   | ●                                                                                   |

\*Compatible with old Elevation H2 dispensers and compressed refills, SKUs: 552028, 552228, 552020, 552120



## Tork Multifold and C-Fold Hand Towel Dispenser

Refill ID: H2

| SKU  | Color | Material | Size H x W x D (in)                             | Units/Case |
|------|-------|----------|-------------------------------------------------|------------|
| 73TR | Smoke | Plastic  | 18 x 11.75 x 6.25<br>(45.72 x 29.85 x 15.88 cm) | 1          |

## Tork Multifold Hand Towels

Refill ID: H2

| SKU    | Quality Tier | Color   | Ply | Panels | Towel Size W x L (in)             | Towels/Package | Packages/Case | Towels/Case |  | Recycled Content |  |  |  |
|--------|--------------|---------|-----|--------|-----------------------------------|----------------|---------------|-------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| MB540A | Universal    | White   | 1   | 3      | 9.125 x 9.5<br>(23.18 x 24.13 cm) | 250            | 16            | 4,000       | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     |                                                                                       | ●                                                                                     |
| MK530A | Universal    | Natural | 1   | 3      | 9.125 x 9.5<br>(23.18 x 24.13 cm) | 250            | 16            | 4,000       | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     |                                                                                       | ●                                                                                     |
| MK520A | Universal    | Natural | 1   | 3      | 9.125 x 9.5<br>(23.18 x 24.13 cm) | 250            | 16            | 4,000       | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     | ●                                                                                     | ●                                                                                     |



# Tork Constant Air Freshener

## Improve your customers restroom experience

The Tork Constant Air Freshener system is designed to deliver a constant, pleasant restroom experience for guests. Our air fresheners help control odors and make it easy to keep your restrooms constantly fresh.



**Not just  
fresh –  
constantly  
fresh**



- Designed to deliver a constant, pleasant experience, which helps to avoid restroom complaints
- Flexible placement, helps improve efficiency
- Three carefully selected scents that eliminate bad odors, rather than just masking them

## Tork Constant Air Freshener

Refill ID: A3



- No spray and fade effect due to unique distribution technology<sup>1</sup>
- Flexible placement at reachable height for easy refilling
- Adjustable intensity (30, 60, 90 days) to suit any size restroom
- Propellant-free system, using only fragrance oils

## Tork Constant Air Freshener Dispensers

Refill ID: A3

| SKU                                                                                     | Description | Design Line | Color | Material | Size<br>H x W x D (in)                         | Units/Case |  |  |
|-----------------------------------------------------------------------------------------|-------------|-------------|-------|----------|------------------------------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  256021 | Electronic  | Elevation   | White | Plastic  | 3.85 x 4.68 x 5.74<br>(9.8 x 11.89 x 14.58 cm) | 6          | ●                                                                                   | ●                                                                                   |
|  256023 | Electronic  | Elevation   | Black | Plastic  | 3.85 x 4.68 x 5.74<br>(9.8 x 11.89 x 14.58 cm) | 6          | ●                                                                                   | ●                                                                                   |

## Tork Constant Air Freshener Starter Pack

Refill ID: A3

| SKU                                                                                      | Description                                          | Design Line | Color | Material | Starter Pack Dimensions<br>H x W x D (in)     | Units/Case |  |
|------------------------------------------------------------------------------------------|------------------------------------------------------|-------------|-------|----------|-----------------------------------------------|------------|-------------------------------------------------------------------------------------|
|  256020 | Starter Pack with 1 dispenser and 1 refill (Blossom) | Elevation   | Black | Plastic  | 15 x 6.88 x 13.58<br>(38.1 x 17.47 x 34.5 cm) | 6          | ●                                                                                   |

## Tork Constant Air Freshener Refills

Refill ID: A3

| SKU                                                                                       | Description      | Fragrance  | Format        | Units/Case | Fragrance intensity |  |
|-------------------------------------------------------------------------------------------|------------------|------------|---------------|------------|---------------------|---------------------------------------------------------------------------------------|
|  257020 | Breeze           | Fresh      | Fragrance oil | 6          | — ▮ ▮ ▮ +           | ●                                                                                     |
|  257021 | Blossom          | Floral     | Fragrance oil | 6          | — ▮ ▮ ▮ +           | ●                                                                                     |
|  257022 | Odor Neutralizer | Lemongrass | Fragrance oil | 6          | — ▮ ▮ ▮ +           | ●                                                                                     |

<sup>1</sup> Patented technology based on a proven fuel technology used in the pharmaceutical industry, where precise doses are essential to treat human beings and animals.

# Tork Soap and Sanitizer solutions

Meet your hand hygiene needs without compromising on sustainability

Tork soap and sanitizer solutions are proven and formulated to help customers meet their hygiene expectations, whilst reducing the impact on the environment.

Our dispensing systems offer flexibility and are easy-to-use certified, optimizing operational efficiency and creating a hygienic experience for all.



**One system  
Multiple  
hand hygiene  
solutions**

**Tork Clarity Hand Washing  
Foam Soap (401800)**

**99%**  
of ingredients  
from natural  
origin<sup>1</sup>



- Flexible, with a wide range of refills and variable dose sizes to optimize consumption and hygiene to suit your needs
- Refilling in less than 10 seconds<sup>2</sup> for maximum efficiency
- Highly effective formulations that care for the skin and the environment

<sup>1</sup> Clarity formulation following the ISO16128

<sup>2</sup> Based on internal panel test soap refilling time.



## Tork Soap and Sanitizer

Refill ID: S4



- One flexible dispensing system for foam, liquid soaps and sanitizers
- Proven Easy-to-use design certified by a third party<sup>1</sup>, promoting good hand hygiene for all users, including children and the elderly
- Helps secure good hand hygiene: factory-sealed bottle with a new pump for every refill helps reduce risk of contamination and protects the formulations

| Tork Soap and Sanitizer Dispensers |                                       |             |                 |                   |                                             | Refill ID: S4 |   |   |   |   |
|------------------------------------|---------------------------------------|-------------|-----------------|-------------------|---------------------------------------------|---------------|---|---|---|---|
| SKU                                | Description                           | Design Line | Color           | Material          | Size H x W x D (in)                         | Units/Case    |   |   |   |   |
| 581500                             | Manual<br>(Formerly 571501)           | Elevation   | White           | Plastic           | 11.42 x 4.41 x 3.9<br>(29 x 11.2 x 9.9 cm)  | 6             | ● | ● | ● | ● |
| 581508                             | Manual<br>(Formerly 571508)           | Elevation   | Black           | Plastic           | 11.42 x 4.41 x 3.9<br>(29 x 11.2 x 9.9 cm)  | 6             | ● | ● | ● | ● |
| 466000                             | Manual                                | Image       | Stainless Steel | Metal and Plastic | 11.4 x 4.2 x 4.2<br>(29.9 x 10.6 x 10.7 cm) | 4             | ● | ● | ● | ● |
| 571600                             | Automatic<br>(Batteries not included) | Elevation   | White           | Plastic           | 10.9 x 4.4 x 5<br>27.8 x 11.2 x 12.8 cm     | 4             | ● | ● | ● | ● |
| 571608                             | Automatic<br>(Batteries not included) | Elevation   | Black           | Plastic           | 10.9 x 4.4 x 5<br>27.8 x 11.2 x 12.8 cm     | 4             | ● | ● | ● | ● |
| 466100                             | Automatic<br>(Batteries not included) | Image       | Stainless Steel | Metal and Plastic | 10.9 x 4.6 x 5.1<br>27.8 x 11.6 x 13 cm     | 4             | ● | ● | ● | ● |



| Tork Hygiene Stand                                 |       |          |                                               |            |                                                                                                     | Refill ID: S4                                                                                          |  |
|----------------------------------------------------|-------|----------|-----------------------------------------------|------------|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|--|
| SKU                                                | Color | Material | Size H x W x D (in)                           | Units/Case | <br>TorkSelect | <br>ADA Compliant |  |
| 670058                                             | Black | Metal    | 53.13 x 18 x 22.5 (134.95 x 45.72 x 57.15 cm) | 1          |                |                   |  |
| Mounting Kit for Tork Soap and Sanitizer Dispenser |       |          |                                               |            |                                                                                                     | Refill ID: S4                                                                                          |  |
| 570010                                             | White | Plastic  | 11 x 7 x 0.4 (27.94 x 17.78 x 1.02 cm)        | 4          |                |                                                                                                        |  |
| 570018                                             | Black | Plastic  | 11 x 7 x 0.4 (27.94 x 17.78 x 1.02 cm)        | 4          |                |                                                                                                        |  |
| Tork Drip Tray                                     |       |          |                                               |            |                                                                                                     | Refill ID: S4                                                                                          |  |
| 570078                                             | Gray  | Plastic  | 15.25 x 5.75 x 4 (38.735 x 14.605 x 10.16 cm) | 1          |                                                                                                     |                                                                                                        |  |
| 570088                                             | Black | Plastic  | 15.25 x 5.75 x 4 (38.735 x 14.605 x 10.16 cm) | 1          |                                                                                                     |                                                                                                        |  |
| 570090                                             | White | Plastic  | 4.5 x 4 x 3 (11.43 x 10.16 x 7.62 cm)         | 12         |                |                                                                                                        |  |
| 570098                                             | Black | Plastic  | 4.5 x 4 x 3 (11.43 x 10.16 x 7.62 cm)         | 12         |                |                                                                                                        |  |
| 580100                                             | White | Plastic  | 4.5 x 3.92 x 7.30 (11.43 x 9.96 x 18.55 cm)   | 6          |                |                   |  |
| 580180                                             | Black | Plastic  | 4.5 x 3.92 x 7.30 (11.43 x 9.96 x 18.55 cm)   | 6          |                |                   |  |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

<sup>1</sup> Certified by the Swedish Rheumatism association, tested according to The Design for All Test, published in the Swedish Design Research Journal, 2011.

## Tork Soap

Refill ID: S4



- Highly effective formulations, with carefully-chosen ingredients
- Refill bottles collapse as the contents are used, helping to reduce waste

## Tork Hand Washing Soap

Refill ID: S4

| SKU                                                                                       | Description               | Color     | Fragrance    | Unit Size | Units/Case |  |  |  |  |  |  |
|-------------------------------------------------------------------------------------------|---------------------------|-----------|--------------|-----------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 400031                                                                                    | Extra Mild Liquid Soap    | Colorless | None         | 1 Liter   | 6          | ●                                                                                   | ●                                                                                   | ●                                                                                   |                                                                                     | ●                                                                                   | ●                                                                                   |
| 401811                                                                                    | Extra Mild Foam Soap      | Colorless | None         | 1 Liter   | 6          | ●                                                                                   | ●                                                                                   | ●                                                                                   |                                                                                     | ●                                                                                   | ●                                                                                   |
| 401800                                                                                    | Clarity Foam Soap         | Colorless | None         | 1 Liter   | 6          | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 400020                                                                                    | Odor-Control, Liquid Soap | Colorless | None         | 1 Liter   | 6          | ●                                                                                   | ●                                                                                   | ●                                                                                   |                                                                                     | ●                                                                                   | ●                                                                                   |
| 400032                                                                                    | Luxury Liquid Soap        | Pink      | Light Floral | 1 Liter   | 6          | ●                                                                                   | ●                                                                                   | ●                                                                                   |                                                                                     |                                                                                     | ●                                                                                   |
| 400033                                                                                    | Hair and Body Wash        | Orange    | Clean        | 1 Liter   | 6          | ●                                                                                   | ●                                                                                   |                                                                                     |                                                                                     |                                                                                     | ●                                                                                   |
| 401815                                                                                    | Antimicrobial Foam Soap   | Colorless | None         | 1 Liter   | 6          | ●                                                                                   |                                                                                     |                                                                                     |                                                                                     | ●                                                                                   | ●                                                                                   |
|  401804 | Mildly Scented Foam Soap  | Colorless | Fresh Scent  | 1 Liter   | 6          | ●                                                                                   |                                                                                     |                                                                                     |                                                                                     |                                                                                     | ●                                                                                   |

## Tork Sanitizer

Refill ID: S4



- Dermatologically tested
- No added fragrances or dyes
- Helps to remove harmful bacteria and germs

## Tork Hand Sanitizing Foam

Refill ID: S4

| SKU    | Description          | Refill ID | Color     | Fragrance | Unit Size | Units/Case |  |  |  |  |  |  |
|--------|----------------------|-----------|-----------|-----------|-----------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 400217 | 70% Alcohol Strength | S4        | Colorless | None      | 1 Liter   | 6          | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 400022 | 70% Alcohol Strength | Tabletop  | Colorless | None      | 18 oz     | 12         | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |                                                                                       |
| 401813 | Alcohol-Free         | S4        | Colorless | None      | 1 Liter   | 6          | ●                                                                                     |                                                                                       |                                                                                       |                                                                                       | ●                                                                                     | ●                                                                                     |

Tork Counter Mount Soap System

Refill ID: S26



- Sensor dispensing for touch-free hand hygiene
- Easy to service, front load dispenser for speedy refilling
- Refill bottle designed for easy gripping for smooth changeovers
- High capacity 2L refill bottles

| Tork Counter Mount Foam Soap Dispenser             |                                                        |                |           |                                                 |            |                                                                                                   | Refill ID: S26                                                                      |                                                                                                                        |                                                                                            |
|----------------------------------------------------|--------------------------------------------------------|----------------|-----------|-------------------------------------------------|------------|---------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| SKU                                                | Color                                                  | Faucet Finish  | Material  | Size H x W x D (in)                             | Units/Case | <br>TorkSelect |  | <br>ADA Compliant                   |                                                                                            |
| 571718                                             | Black                                                  | Chrome Plated  | Plastic   | 15.276 x 14.685 x 5.827 (38.8 x 37.3 x 14.8 cm) | 1          |                |  |                                     |                                                                                            |
| 571719                                             | Black                                                  | Brushed Nickel | Plastic   | 15.276 x 14.685 x 5.827 (38.8 x 37.3 x 14.8 cm) | 1          |                |  |                                     |                                                                                            |
| Tork Hand Washing Soap                             |                                                        |                |           |                                                 |            |                                                                                                   | Refill ID: S26                                                                      |                                                                                                                        |                                                                                            |
| SKU                                                | Description                                            | Color          | Fragrance | Unit Size                                       | Units/Case | <br>TorkSelect |  | <br>GREEN SEAL CERTIFIED<br>PRODUCT | <br>NSF |
| 400039                                             | Extra Mild Foam Soap                                   | Colorless      | None      | 2 Liter                                         | 2          |                |  |                                     |         |
| Tork Counter Mount Foam Soap Dispenser Accessories |                                                        |                |           |                                                 |            |                                                                                                   | Refill ID: S26                                                                      |                                                                                                                        |                                                                                            |
| SKU                                                | Description                                            |                |           | Refill ID                                       | Color      | Material                                                                                          | Units/Case                                                                          |                                                                                                                        |                                                                                            |
| 570100                                             | AC Power Adapter for Counter Mount Foam Soap Dispenser |                |           | S26                                             | Black      | ABS Plastic                                                                                       | 10                                                                                  |                                                                                                                        |                                                                                            |





# Tork OptiServe Coreless Toilet Paper System

The Tork OptiServe® range is designed to streamline processes for multiple improvements. Refill dispensers less often and more easily, saving time for other cleaning tasks. Reduce waste and handling with less packaging. Use one solution across your entire facility for optimal operational efficiency.



## 80%

of facilities managers would prefer to use one solution across the entire facility<sup>1</sup>

Switching to Tork OptiServe means multiple improvements:

- ✓ Maximize efficiency
- ✓ Minimize environmental impact
- ✓ Provide an excellent user experience



### Reduce waste

.....  
No core, no wrap and 89% less packaging<sup>2</sup> means much less waste

<sup>1</sup>Based on a 2023 survey of 500+ facility managers, cleaning managers and other stakeholders in US and Europe

<sup>2</sup>Tork Coreless SKU 472880 versus Tork conventional SKU 2461200 as compared to the packaging weight, which includes cores, wraps and cardboard box

All Tork Toilet Paper is Septic Safe, see page 4 for more information.

## Tork OptiServe Coreless Toilet Paper Roll

**Refill ID: T5, T7**



- Wide range of dispensers allows the entire facility to use one refill solution
- No core and no wrap saves handling time
- Translucent cover allows service staff to see at-a-glance when it's time to refill

### Tork OptiServe Coreless High Capacity Toilet Paper Dispensers

**Refill ID: T5, T7**

| SKU               | Description       | Refill ID | Design Line | Color     | Material | Size H x W x D (in)                           | Units/Case |   |   |   |
|-------------------|-------------------|-----------|-------------|-----------|----------|-----------------------------------------------|------------|---|---|---|
| 473620            | 4-Roll Vertical   | T5/T7     | Elevation   | White     | Plastic  | 12.71 x 12.56 x 6.85 (32.28 x 31.9 x 17.4 cm) | 1          | ● | ● | ● |
| 473628            | 4-Roll Vertical   | T5/T7     | Elevation   | Black     | Plastic  | 12.71 x 12.56 x 6.85 (32.28 x 31.9 x 17.4 cm) | 1          | ● | ● | ● |
| 473520            | 2-Roll Vertical   | T5/T7     | Elevation   | White     | Plastic  | 12.71 x 6.73 x 6.85 (32.28 x 16.18 x 17.4 cm) | 1          | ● | ● | ● |
| 473528            | 2-Roll Vertical   | T5/T7     | Elevation   | Black     | Plastic  | 12.71 x 6.73 x 6.85 (32.28 x 16.18 x 17.4 cm) | 1          | ● | ● | ● |
| <b>New</b> 558060 | 2-Roll Horizontal | T5/T7     | Elevation   | White     | Plastic  | 8.228 x 14.173 x 5.078 (20.9 x 36.0 x 12.9cm) | 1          | ● | ● | ● |
| <b>New</b> 558068 | 2-Roll Horizontal | T5/T7     | Elevation   | Black     | Plastic  | 8.228 x 14.173 x 5.078 (20.9 x 36.0 x 12.9cm) | 1          | ● | ● | ● |
| 473430            | 2-Roll Vertical   | T7        | N/A         | Stainless | Metal    | 12.8 x 5.87 x 5.63 (32.5 x 14.9 x 14.3cm)     | 1          | ● | ● | ● |



- Spindle Kits convert stainless surface mount and recessed dispensers into Tork Coreless dispensers

### Tork Coreless High Capacity Spindle Kits

**Refill ID: T7**

| SKU    | Type       | Material        | Size H x W x D (in)                      | Units/Case   |   |   |
|--------|------------|-----------------|------------------------------------------|--------------|---|---|
| 473030 | A          | Metal & Plastic | 5.6 x 1.6 x 1.6 (14.22 x 4.06 x 4.06 cm) | 25 sets of 2 | ● | ● |
| 473020 | B          | Metal & Plastic | 5.9 x 1.6 x 1.6 (14.99 x 4.06 x 4.06 cm) | 25 sets of 2 | ● | ● |
| 473040 | C          | Metal & Plastic | 6.1 x 1.4 x 1.4 (15.49 x 3.56 x 3.56 cm) | 25 sets of 2 | ● | ● |
| 473060 | D          | Metal & Plastic | 4.7 x 1.4 x 1.4 (11.94 x 3.56 x 3.56 cm) | 25 sets of 2 | ● | ● |
| 473080 | For Sensor | Metal & Plastic |                                          | 25 sets of 2 | ● | ● |



- A range of Universal, Advanced and Premium refills
- Coreless toilet paper for zero waste
- High capacity roll for busy washrooms

### Tork Coreless High Capacity Toilet Paper Rolls\*

**Refill ID: T5, T7**

| SKU               | Refill ID | Quality Tier | Color | Ply | Embossing         | Sheet Size W x L (in)       | Sheets/Roll | Rolls/Case |   |          | Recycled Content |   |
|-------------------|-----------|--------------|-------|-----|-------------------|-----------------------------|-------------|------------|---|----------|------------------|---|
| 472884            | T7        | Premium      | White | 2   | Tork Quilted Leaf | 3.66 x 4.0 (9.3 x 10.16 cm) | 750         | 36         | ● | Mixed    |                  | ● |
| 472885            | T7        | Premium      | White | 2   | Tork Quilted Leaf | 3.66 x 4.0 (9.3 x 10.16 cm) | 750         | 12         | ● | Mixed    |                  | ● |
| 472880            | T7        | Advanced     | White | 2   | Tork Quilted Leaf | 3.66 x 4.0 (9.3 x 10.16 cm) | 1,000       | 36         | ● | Recycled | 100%, EPA CPG    | ● |
| 472881            | T7        | Advanced     | White | 2   | Tork Quilted Leaf | 3.66 x 4.0 (9.3 x 10.16 cm) | 1,000       | 12         | ● | Recycled | 100%, EPA CPG    | ● |
| 472882            | T7        | Universal    | White | 2   | N/A               | 3.66 x 4.0 (9.3 x 10.16 cm) | 1,100       | 36         | ● | Recycled | 100%, EPA CPG    | ● |
| 472887            | T5        | Universal    | White | 2   | N/A               | 3.66 x 4.0 (9.3 x 10.16 cm) | 1,500       | 18         | ● | Recycled | 100%, EPA CPG    | ● |
| <b>New</b> 472889 | T5        | Universal    | White | 1   | N/A               | 3.66 x 4.0 (9.3 x 10.16 cm) | 2,600       | 18         | ● | Recycled | 100%, EPA CPG    | ● |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

\*Ordered in unit load quantities only.

## Value-Added – T10, T11 Dispensers and Refills

All Tork Toilet Paper is Septic Safe, see page 4 for more information.

### Tork Toilet Paper Roll with OptiCore

Refill ID: T11



565828



565728

- 3- and 2-roll options designed to minimize maintenance and maximize cost savings for high-traffic areas
- Translucent cover allows service staff to see at-a-glance when it's time to refill

#### Tork Toilet Paper Roll Dispensers for OptiCore

Refill ID: T11

| SKU    | Description         | Color | Material | Size H x W x D (in)                                | Units/Case |  |  |
|--------|---------------------|-------|----------|----------------------------------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 565828 | 3 Roll              | Black | Plastic  | 14.56 x 14.12 x 6.31<br>(36.98 x 35.86 x 16.03 cm) | 1          | ●                                                                                   | ●                                                                                   |
| 565728 | 2-Roll Side-by-Side | Black | Plastic  | 8.81 x 11.06 x 7.18<br>(22.37 x 28.09 x 18.24 cm)  | 1          | ●                                                                                   | ●                                                                                   |



106390

- OptiCore® technology offers a two-part core for controlled-use and more than 25% reduction in core material for more environmentally preferable packaging
- Premium, Advanced, and Universal quality levels

#### Tork Toilet Paper Roll with OptiCore

Refill ID: T11

| SKU    | Quality Tier | Color | Ply | Embossing                | Sheet Size W x L (in)         | Sheets/ Roll | Rolls/ Case |  |  |  | Recycled Content |  |  |
|--------|--------------|-------|-----|--------------------------|-------------------------------|--------------|-------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 106390 | Premium      | White | 2   | Tork Leaves and Stitches | 3.75 x 4<br>(9.53 x 10.16 cm) | 800          | 36          | ●                                                                                   | ●                                                                                     | Mixed                                                                                 |                  |                                                                                       |                                                                                       |
| 162090 | Advanced     | White | 2   | Tork Leaves and Stitches | 3.75 x 4<br>(9.53 x 10.16 cm) | 865          | 36          | ●                                                                                   | ●                                                                                     | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     |                                                                                       |
| 161990 | Universal    | White | 2   | Tork Leaves and Stitches | 3.75 x 4<br>(9.53 x 10.16 cm) | 865          | 36          | ●                                                                                   | ●                                                                                     | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     | ●                                                                                     |
| 112990 | Universal    | White | 1   | Tork Leaves and Stitches | 3.75 x 4<br>(9.53 x 10.16 cm) | 1,755        | 36          | ●                                                                                   | ●                                                                                     | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     | ●                                                                                     |

### Tork High Capacity Toilet Paper Roll with OptiCore

Refill ID: T10



565528

- An attractive solution for high traffic accounts where the flow of traffic demands high footage rolls of product
- Features sliding cover that securely protects both rolls and locks to prevent product pilferage

#### Tork Twin High Capacity Toilet Paper Roll Dispenser for OptiCore

Refill ID: T10

| SKU    | Description       | Color | Material | Size H x W x D (in)                               | Units/Case |  |  |
|--------|-------------------|-------|----------|---------------------------------------------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 565528 | 2-Roll Horizontal | Black | Plastic  | 9.93 x 16.62 x 5.25<br>(25.22 x 42.21 x 13.34 cm) | 1          | ●                                                                                     | ●                                                                                     |



160090

- OptiCore technology offers a two-part core for controlled-use and more than 25% reduction in core material for more environmentally preferable packaging
- High sheet count for maximum capacity

#### Tork High Capacity Toilet Paper Roll with OptiCore

Refill ID: T10

| SKU    | Quality Tier | Color | Ply | Embossing | Sheet Size W x L (in)          | Sheets/ Roll | Rolls/ Case |  |  |  | Recycled Content |  |  |
|--------|--------------|-------|-----|-----------|--------------------------------|--------------|-------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 160090 | Universal    | White | 2   | N/A       | 3.75 x 3.5<br>(9.53 x 8.89 cm) | 2,000        | 12          | ●                                                                                   | ●                                                                                     | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     | ●                                                                                     |



All Tork Toilet Paper is Septic Safe, see page 4 for more information.

## Tork High Capacity Toilet Paper Roll

**Refill ID: T26**



555620



555628



473070

- Automatic roll shift makes it easy for guests to access the new roll and prevents stub roll waste
- Compact design saves space

| Tork High Capacity Toilet Paper Dispensers |                 |             |       |          |                                                |            | Refill ID: T26                                                                                 |                                                                                                   |
|--------------------------------------------|-----------------|-------------|-------|----------|------------------------------------------------|------------|------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|
| SKU                                        | Description     | Design Line | Color | Material | Size H x W x D (in)                            | Units/Case |  TorkSelect |  ADA Compliant |
| 555620                                     | 2-Roll Vertical | Elevation   | White | Plastic  | 14.2 x 6.3 x 6.46<br>(36.07 X 16.0 x 16.41 cm) | 1          | ●                                                                                              | ●                                                                                                 |
| 555628                                     | 2-Roll Vertical | Elevation   | Black | Plastic  | 14.2 x 6.3 x 6.46<br>(36.07 X 16.0 x 16.41 cm) | 1          | ●                                                                                              | ●                                                                                                 |

| Tork 2-Roll High Capacity Toilet Paper Adapters |                                                 |       |          |                                      | Refill ID: T26 |
|-------------------------------------------------|-------------------------------------------------|-------|----------|--------------------------------------|----------------|
| SKU                                             | Description                                     | Color | Material | Size H x W x D (in)                  | Units/Case     |
| 473070                                          | Adapter to convert Tork T26 to Tork T7 Coreless | Black | Plastic  | 8 x 10 x 2 (20.32 x 25.40 x 5.08 cm) | 12             |



110292A

- High capacity rolls reduce service outages
- Easy start tail seal to prevent waste
- Embossed rolls enhance softness


| Tork High Capacity Toilet Paper Rolls |              |       |     |                     |                             |              |             |                                                                                                  |                                                                                                   |                                                                                           | Refill ID: T26   |                                                                                       |
|---------------------------------------|--------------|-------|-----|---------------------|-----------------------------|--------------|-------------|--------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|
| SKU                                   | Quality Tier | Color | Ply | Embossing           | Sheet Size W x L (in)       | Sheets/ Roll | Rolls/ Case |  TorkSelect |  Tork Select |  FSC | Recycled Content |  |
| 110292A                               | Advanced     | White | 2   | Leaves and Stitches | 3.77 x 3.75 (9.58x 9.53 cm) | 1,000        | 36          | ●                                                                                                | ●                                                                                                 | Recycled                                                                                  | 100%, EPA CPG    | ●                                                                                     |

## Value-Added & Standard – T24, T34 Dispensers and Refills

All Tork Toilet Paper is Septic Safe, see page 4 for more information.

### Tork Conventional Toilet Paper Roll

Refill ID: T24



#### Tork Toilet Paper Dispensers

Refill ID: T24

| SKU  | Description       | Color | Material | Size H x W x D (in)                            | Units/Case | ADA Compliant |
|------|-------------------|-------|----------|------------------------------------------------|------------|---------------|
| 55TR | 2-Roll Vertical   | Smoke | Plastic  | 12.75 x 7.5 x 7 (32.39 x 19.05 x 17.78 cm)     | 1          | ●             |
| 59TR | 2-Roll Horizontal | Smoke | Plastic  | 8.25 x 12.75 x 5.57 (20.96 x 32.39 x 14.61 cm) | 1          | ●             |

#### Tork Toilet Paper Rolls

Refill ID: T24

| SKU     | Quality Tier | Color | Ply | Embossing           | Sheet Size W x L (in)        | Sheets/Roll | Rolls/Pack | Rolls/Case | TORK TOILET PAPER | FSC      | Recycled Content | Recycled |
|---------|--------------|-------|-----|---------------------|------------------------------|-------------|------------|------------|-------------------|----------|------------------|----------|
| 2465100 | Premium Soft | White | 2   | Leaves and Stitches | 4.0 x 3.75 (10.16 x 9.53 cm) | 400         | 1          | 80         | ●                 | Mixed    |                  |          |
| 2465110 | Premium      | White | 2   | Leaves and Stitches | 4.0 x 3.75 (10.16 x 9.53 cm) | 450         | 1          | 80         | ●                 |          | EPA CPG          |          |
| 2465120 | Premium      | White | 2   | Leaves and Stitches | 4.0 x 3.75 (10.16 x 9.53 cm) | 450         | 1          | 48         | ●                 |          | EPA CPG          |          |
| 2461200 | Advanced     | White | 2   | Leaves and Stitches | 4.0 x 3.75 (10.16 x 9.53 cm) | 500         | 1          | 80         | ●                 | Recycled | 100%, EPA CPG    | ●        |
| TM6130S | Advanced     | White | 2   | Leaves and Stitches | 4.0 x 3.75 (10.16 x 9.53 cm) | 500         | 1          | 48         | ●                 | Recycled | 100%, EPA CPG    | ●        |

#### Tork Toilet Paper Rolls

Refill ID: T24

| SKU     | Quality Tier | Color | Ply | Embossing           | Sheet Size W x L (in)        | Sheets/Roll | Rolls/Case | Rolls/Case | FSC      | Recycled Content | Recycled |
|---------|--------------|-------|-----|---------------------|------------------------------|-------------|------------|------------|----------|------------------|----------|
| 240150  | Advanced     | White | 2   | Overall             | 4.0 x 4.0 (10.16 x 10.16 cm) | 176         | 4          | 96         | Recycled | 100%, EPA CPG    |          |
| 1102910 | Advanced     | White | 1   | Leaves and Stitches | 3.94 x 3.75 (10 x 9.53 cm)   | 2,000       | 1          | 36         | Recycled | 100%, EPA CPG    | ●        |
| TM1601A | Universal    | White | 2   | Leaves and Stitches | 4.0 x 3.5 (10.67 x 8.9 cm)   | 500         | 1          | 48         | Recycled | 100%, EPA CPG    | ●        |
| TM1616S | Universal    | White | 2   | Leaves and Stitches | 4.0 x 3.5 (10.16 x 8.9 cm)   | 500         | 1          | 96         | Recycled | 100%, EPA CPG    | ●        |

### Tork Conventional Toilet Paper Roll

Refill ID: T34



240616

#### Tork Toilet Paper Rolls


Refill ID: T34

| SKU    | Quality Tier | Color | Ply | Embossing           | Sheet Size W x L (in)        | Sheets/Roll | Rolls/Case | FSC      | Recycled Content | Recycled |
|--------|--------------|-------|-----|---------------------|------------------------------|-------------|------------|----------|------------------|----------|
| 240616 | Universal    | White | 2   | Leaves and Stitches | 3.75 x 4.0 (9.53 x 10.16 cm) | 616         | 48         | Recycled | 100%, EPA CPG    | ●        |
| 240123 | Universal    | White | 1   | Leaves and Stitches | 3.75 x 4.0 (9.53 x 10.16 cm) | 1,232       | 48         | Recycled | 100%, EPA CPG    | ●        |

All Tork Toilet Paper is Septic Safe, see page 4 for more information.

## Tork Jumbo Toilet Paper Roll

Refill ID: T1



- See-through window indicates when it's time to refill

| Tork Jumbo Toilet Paper Roll Dispensers |                   |              |       |     |           |                   |                                               |                   |             |                                                                                                | Refill ID: T1                                                                                  |                                                                                                   |                  |                                                                                     |
|-----------------------------------------|-------------------|--------------|-------|-----|-----------|-------------------|-----------------------------------------------|-------------------|-------------|------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|
| SKU                                     | Description       | Design Line  |       |     | Color     | Material          | Size H x W x D (in)                           |                   |             | Units/Case                                                                                     |  TorkSelect |  ADA Compliant |                  |                                                                                     |
| 554020A                                 | 1-Roll Plus Stub  | Elevation    |       |     | White     | Plastic           | 14.2 x 17.2 x 5.2<br>(36.0 x 43.7 x 13.2 cm)  |                   |             | 1                                                                                              |             |                |                  |                                                                                     |
| 554028A                                 | 1-Roll Plus Stub  | Elevation    |       |     | Black     | Plastic           | 14.2 x 17.2 x 5.2<br>(36.0 x 43.7 x 13.2 cm)  |                   |             | 1                                                                                              |             |                |                  |                                                                                     |
| 247549A                                 | 2-Roll Horizontal | N/A          |       |     | Black     | Plastic           | 13 x 21.5 x 5.5<br>(33.02 x 54.61 x 13.97 cm) |                   |             | 4                                                                                              |             |                |                  |                                                                                     |
| Tork Jumbo Toilet Paper Roll            |                   |              |       |     |           |                   |                                               |                   |             |                                                                                                | Refill ID: T1                                                                                  |                                                                                                   |                  |                                                                                     |
| SKU                                     | Description       | Quality Tier | Color | Ply | Embossing | Roll Width (in)   | Roll Dia. (in)                                | Linear Feet/ Roll | Rolls/ Case |  TorkSelect |             |                | Recycled Content |  |
| 12021502                                |                   | Advanced     | White | 2   | N/A       | 3.48<br>(8.84 cm) | 10.0<br>(25.4 cm)                             | 1,600 (487.7 m)   | 6           |             |             | Recycled                                                                                          | 100%,<br>EPA CPG |  |

## Tork Mini Jumbo Toilet Paper Roll

Refill ID: T2



- Smart, stub-roll holder allows for full roll consumption
- Optimal roll brake prevents free-spinning rolls and therefore, reduces consumption
- See-through window indicates when it's time to refill

| Tork Mini Jumbo Toilet Paper Roll Dispensers |                   |             |                 |               |                                                    |            |                                                                                       | Refill ID: T2                                                                         |                                                                                       |  |
|----------------------------------------------|-------------------|-------------|-----------------|---------------|----------------------------------------------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--|
| SKU                                          | Description       | Design Line | Color           | Material      | Size H x W x D (in)                                | Units/Case |  |  |  |  |
| 465500                                       | 1-Roll Plus Stub  | Image       | Stainless Steel | Metal/Plastic | 9.875 x 14 x 5.125<br>(25.08 x 35.56 x 13.02 cm)   | 1          |  |  |  |  |
| 555020A                                      | 1-Roll Plus Stub  | Elevation   | White           | Plastic       | 10.8 x 13.6 x 5.2<br>(27.5 x 34.5 x 13.2 cm)       | 1          |  |  |  |  |
| 555028A                                      | 1-Roll Plus Stub  | Elevation   | Black           | Plastic       | 10.8 x 13.6 x 5.2<br>(27.5 x 34.5 x 13.2 cm)       | 1          |  |  |  |  |
| 5555200                                      | 2-Roll Horizontal | Elevation   | White           | Plastic       | 10.125 x 17 x 5.6875<br>(25.72 x 43.18 x 14.45 cm) | 1          |  |  |  |  |
| 5555290                                      | 2-Roll Horizontal | Elevation   | Black           | Plastic       | 10.125 x 17 x 5.6875<br>(25.72 x 43.18 x 14.45 cm) | 1          |  |  |  |  |



- High capacity allows for fewer refills and reduced labor
- Large size reduces pilferage

| Tork Mini Jumbo Toilet Paper Rolls |                  |              |       |     |           |                 |                |                               |             |                                                                                       |                                                                                       |                                                                                       | Refill ID: T2    |                                                                                       |
|------------------------------------|------------------|--------------|-------|-----|-----------|-----------------|----------------|-------------------------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|
| SKU                                | Description      | Quality Tier | Color | Ply | Embossing | Roll Width (in) | Roll Dia. (in) | Linear Feet/ Roll             | Rolls/ Case |  |  |  | Recycled Content |  |
| 11020602                           | Soft, Perforated | Advanced     | White | 2   | N/A       | 3.48 (8.84 cm)  | 7.4 (18.7 cm)  | 1,075 Sheets<br>751 (228.9 m) | 12          |  |  | Mixed                                                                                 | EPA CPG          |                                                                                       |
| 12024402                           |                  | Advanced     | White | 2   | N/A       | 3.48 (8.84 cm)  | 7.4 (18.7 cm)  | 751 (228.9 m)                 | 12          |  |  | Recycled                                                                              | 100%, EPA CPG    |  |
| 12013903                           |                  | Advanced     | White | 1   | N/A       | 3.48 (8.84 cm)  | 7.4 (18.7 cm)  | 1,200 (365.7 m)               | 12          |  |  | Recycled                                                                              | 100%, EPA CPG    |  |



## Standard – T22, V1 Dispensers and Refills

All Tork Toilet Paper is Septic Safe, see page 4 for more information.

## Tork Jumbo Toilet Paper

Refill ID: T22



56TR



66TR



TJ0922A

### Tork Jumbo Toilet Paper Roll Dispensers

Refill ID: T22

| SKU  | Description       | Color | Material | Size H x W x D (in)                             | Units/Case |  ADA Compliant |
|------|-------------------|-------|----------|-------------------------------------------------|------------|---------------------------------------------------------------------------------------------------|
| 56TR | 2-Roll Horizontal | Smoke | Plastic  | 11.83 x 19.29 x 5.510<br>(30.05 x 49.0 x 14 cm) | 1          | ●                                                                                                 |
| 66TR | 1-Roll            | Smoke | Plastic  | 12 x 10.63 x 5.75<br>(30.48 x 27.00 x 14.61 cm) | 1          | ●                                                                                                 |

### Tork Jumbo Toilet Paper Roll

Refill ID: T22

| SKU     | Quality Tier | Color | Ply | Roll Width (in) | Roll Dia. (in) | Linear Feet/Roll | Rolls/Case |  FSC Recycled | Recycled Content |  |
|---------|--------------|-------|-----|-----------------|----------------|------------------|------------|--------------------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|
| TJ0922A | Universal    | White | 2   | 3.36 (8.53 cm)  | 8.8 (22.35 cm) | 1,000 (304.8 m)  | 12         | Recycled                                                                                         | 100%,<br>EPA CPG | ●                                                                                   |

## Tork Toilet Seat Covers

Refill ID: V1



1951001



TC0020

### Toilet Seat Cover Dispenser

Refill ID: V1

| SKU     | Color | Material | Size H x W x D (in)                            | Units/Case |  ADA Compliant |
|---------|-------|----------|------------------------------------------------|------------|-----------------------------------------------------------------------------------------------------|
| 1951001 | Smoke | Plastic  | 11.5 x 16 x 3.125<br>(29.21 x 40.64 x 7.94 cm) | 12         | ●                                                                                                   |

### Tork Toilet Seat Cover

Refill ID: V1

| SKU    | Quality Level | Color | Ply | Fold | Sheet Size W x L (in)           | Sheets/Package | Package/Case | Sheets/Case |  FSC Recycled | Recycled Content |
|--------|---------------|-------|-----|------|---------------------------------|----------------|--------------|-------------|----------------------------------------------------------------------------------------------------|------------------|
| TC0020 | Universal     | White | 1   | 1/2  | 14.5 x 17<br>(36.83 x 43.18 cm) | 250            | 20           | 5,000       | Recycled                                                                                           | 100%             |

## Tork Facial Tissue

- Box protects the tissue, keeps it clean and dry
- Flat and cube box formats available
- 2-ply tissue delivers additional softness, thickness and absorbency



6910101



6920101



6830100



TF6810

| SKU     | Description | Quality Tier  | Color | Ply | Tissue Size W x L (in)       | Tissues/Box | Boxes/Case | Tissues/Case |  | Recycled Content |  |
|---------|-------------|---------------|-------|-----|------------------------------|-------------|------------|--------------|-------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|
| 6910101 | Cube        | Premium       | White | 2   | 7.875 X 8.2 (20 x 20.83 cm)  | 86          | 36         | 3,096        | Mixed                                                                               | 100%, EPA CPG    |                                                                                     |
| 6920101 | Flat        | Premium       | White | 2   | 7.9 x 8.2 (20.07 x 20.83 cm) | 100         | 30         | 3,000        | Mixed                                                                               | 100%, EPA CPG    |                                                                                     |
| 6830100 | Cube        | Advanced Soft | White | 2   | 7.875 X 8.2 (20 x 20.83 cm)  | 86          | 36         | 3,096        | Recycled                                                                            | 100%, EPA CPG    | ●                                                                                   |
| TF6810  | Flat        | Advanced      | White | 2   | 7.9 x 8.2 (20.07 x 20.83 cm) | 100         | 30         | 3,000        | Recycled                                                                            | 100%, EPA CPG    | ●                                                                                   |



TF6710A

| SKU     | Description | Quality Tier | Color | Ply | Tissue Size W x L (in)       | Tissues/Box | Boxes/Case | Tissues/Case |  | Recycled Content |  |
|---------|-------------|--------------|-------|-----|------------------------------|-------------|------------|--------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|
| TF6710A | Flat        | Universal    | White | 2   | 7.9 x 8.2 (20.07 x 20.83 cm) | 100         | 30         | 3,000        | Recycled                                                                              | 100%, EPA CPG    | ●                                                                                     |

# Wiping and Cleaning

The easy choice for the best result

Whether you run a restaurant kitchen or an industrial production line, we understand that every second matters. Tork wipes, cloths and dispensers are designed to get the job done with maximum efficiency – keeping your business running smoothly.



## Choosing the right product

We've got a comprehensive range of specialist wipes and cloths, each designed to perform specific tasks (Foodservice, Food Processing, Wet Wipes, Low Lint Cloths, Microfibre Cloths).

### Wiping

Mopping up spills, soaking up liquids and picking up dirt and dust with paper.

### Cleaning

Removing dirt, stains and microorganisms from surfaces, machines or tools with cloths that are dry or used together with water, solvents or detergents.

### Sanitizing & Disinfecting

Sanitizing and or Disinfecting involve hygienically cleaning a surface by removing or killing harmful microorganisms.

### Polishing

Creating a protected and shiny surface with the help of a cloth that applies polish onto the surface and is then rubbed to obtain a good finish.



## Find the right dispensing solution

We have a wipe or cloth for every task, and a wide range of dispensers with fixing options available to make sure you'll always find what you need, where you need it.

### Wall mounted



**Tork Wall Stand  
(Refill W1)**  
6521281 Red/Black

- Saves floor space
- Easy, ergonomic loading
- Fast, safe, reliable, dispensing for high traffic environments



**Tork Maxi  
Centerfeed  
Dispenser  
(Refill W2)**  
653028 Red/Black  
653020 Turquoise/White

- Hygienic dispenser for maxi centerfeed rolls
- Optimized for single hand dispensing



**Tork Folded  
Wiper/Cloth  
Dispenser  
(Refill W4)**  
6540281 Red/Black  
654021 Turquoise/White  
207328 Black

- Protects the wipes and reduces consumption by dispensing one sheet at a time
- Durable and slim, perfect for wall-mounted convenience



**Tork Centerfeed  
Dispenser  
(Refill M2)**  
659028 Red/Black  
659020 Turquoise/White  
559020A White  
559028A Black

- Improved hygiene – touch only what you use
- Reliable dispensing with wet hands
- Single hand dispensing for easy use



**Tork Mini  
Centerfeed  
Dispenser  
(Refill M1)**  
558028A Black

- Improved hygiene – touch only what you use
- Single hand dispensing for easy use



**Tork Washstation  
Roll Towel  
Dispenser  
(Refill W6)**  
651228 Red/Black  
651220 Turquoise/White

- Water resistant
- Large capacity with one at a time dispensing
- Built to withstand wet environments
- HAACP Certified



**Tork Small Pack  
Dispenser  
Bracket  
(Refill W8)**  
655300 White

- Space-saving dispenser bracket for server stations, back of house or in storage areas



**Tork Pop-Up  
Bracket  
Dispenser  
(Refill W24)**  
2083281 Black

- Durable and slim, perfect for wall-mounted convenience.

### Portable



**Tork Pop-Up Box**  
450175 - White  
303362 - White  
192127 - White  
440245A - Blue  
510176 - White  
5301755 - White  
192475 - Turquoise  
192125A - White  
192126 - White

- Strong construction offers durability
- Strong enough to power through oil, grease and solvents



**Tork Handy Box**  
520374 Gray  
13247501 Blue

- Portable dispenser carton
- Strong and absorbent



**Tork Hand Cleaning  
Wet Wipes**  
192593 Hand Cleaner

- Single sheet dispensing on the go



**Tork  
Centerfeed  
Box**  
450137 White  
450337 Blue

- Portable pack
- Tough on grease and dirt
- Won't leave residue



**Tork  
Centerfeed  
Bucket**  
450340

- Portable dispenser bucket
- Won't tear easily
- Low-linting

### Mobile



**Tork Floor Stand (Refill W1)**  
6520281 Red/Black

- Easy, ergonomic loading
- Fast, safe, reliable, dispensing for high traffic environments



# Tork Performance Dispensers

Increase productivity by giving your operators the cleaning tools they need to proactively maintain their own equipment. Tork Performance® dispensers and wipers help you optimize cleaning processes and improve preventative maintenance.

Learn more at: [torkusa.com/your-business/solutions/overview/manufacturing/challenge-manufacturing/](https://torkusa.com/your-business/solutions/overview/manufacturing/challenge-manufacturing/)



6520281



6521281



653028



653020



659028



659020



6540281



654021



207328



2083281



655300

- All dispensers optimised for Tork Wipers when combined they become the perfect performance tools
- Extra robust construction
- Semi-transparent hoods

| Tork Performance Dispensers |                               |           |            |               |                                                      | Refill ID: M2, W1, W2, W4, W8, W24 |                                                                                       |
|-----------------------------|-------------------------------|-----------|------------|---------------|------------------------------------------------------|------------------------------------|---------------------------------------------------------------------------------------|
| SKU                         | Name                          | Refill ID | Color      | Material      | Size H x W x D (in)<br>(100.61 x 64.59 x 53.01 cm)   | Units/<br>Case                     |  |
| 6520281                     | Floor Stand                   | W1        | Red/Smoke  | Plastic/Steel | 39.61 x 25.43 x 20.87<br>(100.61 x 64.59 x 53.01 cm) | 1                                  | ●                                                                                     |
| 6521281                     | Wall Stand                    | W1        | Red/Smoke  | Plastic/Steel | 18.23 x 25.43 x 10.79<br>(46.30 x 64.59 x 27.41 cm)  | 1                                  | ●                                                                                     |
| 653028                      | Maxi Centerfeed Dispenser     | W2        | Red/Smoke  | Plastic       | 17.6 x 12.91 x 11.89<br>(44.70 x 32.79 x 30.20 cm)   | 1                                  | ●                                                                                     |
| 653020                      | Maxi Centerfeed Dispenser     | W2        | Aqua/White | Plastic       | 17.6 x 12.91 x 11.89<br>(44.70 x 32.79 x 30.20 cm)   | 1                                  | ●                                                                                     |
| 659028                      | Centerfeed Dispenser          | M2        | Red/Smoke  | Plastic       | 14.02 x 9.76 x 9.13<br>(35.61 x 24.79 x 23.19 cm)    | 1                                  | ●                                                                                     |
| 659020                      | Centerfeed Dispenser          | M2        | Aqua/White | Plastic       | 14.02 x 9.76 x 9.13<br>(35.61 x 24.79 x 23.19 cm)    | 1                                  | ●                                                                                     |
| 6540281                     | Folded Wiper/Cloth Dispenser* | W4        | Red/Smoke  | Plastic       | 15.51 x 16.81 x 8.11<br>(39.40 x 42.70 x 20.60 cm)   | 1                                  | ●                                                                                     |
| 654021                      | Folded Wiper/Cloth Dispenser* | W4        | Aqua/White | Plastic       | 15.51 x 16.81 x 8.11<br>(39.40 x 42.70 x 20.60 cm)   | 1                                  | ●                                                                                     |
| 207328                      | Top-Pak Bracket Dispenser*    | W4        | Black      | Plastic       | 7.8 x 16 x 8.6<br>(19.81 x 40.64 x 21.84 cm)         | 1                                  | ●                                                                                     |
| 2083281                     | Pop-Up Dispenser Bracket*     | W24       | Black      | Plastic       | 5 x 13.75 x 3<br>(12.70 x 39.43 x 7.62 cm)           | 6                                  | ●                                                                                     |
| 655300                      | Small Pack Dispenser Bracket  | W8        | White      | Plastic       | 5.74 x 8.42 x 4.22<br>(14.58 x 21.39 x 10.72 cm)     | 4                                  | ●                                                                                     |

\*Ask your Essity Sales Rep for optional magnet kit 206540.



## Industrial Paper

## Refill ID: M2, W1, W2, W4, W24



- Our strongest paper for tough industrial tasks
- Superior absorption
- Protects hands from heat and dirt

| Tork Industrial Paper Wiper |            |                 |       |     |                     |                                   |             |            | Refill ID: M2, W1, W2, W4, W24                                                      |                  |                                                                                     |
|-----------------------------|------------|-----------------|-------|-----|---------------------|-----------------------------------|-------------|------------|-------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|
| SKU                         | Format     | Refill ID       | Color | Ply | Feet/Unit           | Sheet Size W x L (in)             | Sheets/Unit | Units/Case |  | Recycled Content |  |
| 132451A                     | Centerfeed | M2              | Blue  | 4   | 249<br>(75.90 m)    | 10 x 15.75<br>(25.40 x 40.01 cm)  | 190         | 4          |  | 100%             |  |
| 13244101                    | Centerfeed | W1, W2          | Blue  | 4   | 492<br>(149.96 m)   | 11 x 15.75<br>(27.94 x 40.01 cm)  | 375         | 2          |  | 100%             |  |
| 440278                      | Top-Pak    | W4              | Blue  | 4   | 123.0<br>(37.49 m)  | 12.8 x 16.4<br>(32.51 x 41.66 cm) | 90          | 5          |  | 100%             |  |
| 440245A                     | Pop-Up Box | W24             | Blue  | 4   | 123.75<br>(32.72 m) | 8.54 x 16.5<br>(21.69 x 41.91 cm) | 90          | 10         |  | 100%             |  |
| 13247501                    | Handy Box  | Self-Dispensing | Blue  | 4   | 247.5<br>(75.44 m)  | 12.8 x 16.5<br>(32.51 x 41.91 cm) | 180         | 1          |  | 100%             |  |

## Multipurpose Paper

## Refill ID: W1, W2, W24



- Our toughest multipurpose paper for heavier tasks
- Efficient absorption of oil and water
- High wet strength

| Tork Heavy-Duty Paper Wiper |            |           |       |     |                |                                  |              |             | Refill ID: W1, W24                                                                    |                                                                                       |
|-----------------------------|------------|-----------|-------|-----|----------------|----------------------------------|--------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                         | Format     | Refill ID | Color | Ply | Feet/Unit      | Sheet Size W x L (in)            | Sheets/ Unit | Units/ Case |  |  |
| 450304                      | Giant Roll | W1        | Blue  | 1   | 800 (243.84 m) | 11.1 x 12 (28.19 x 30.48 cm)     | 800          | 1           |  |  |
| 450175                      | Pop-Up Box | W24       | White | 1   | 121 (36.88 m)  | 9.25 x 16.25 (23.50 x 41.28 cm)) | 90           | 10          |  |  |
| 192136                      | 1/4 Fold   |           | White | 1   | 60 (18.29 m)   | 12.5 x 13 (31.70 x 33.02 cm)     | 56           | 16          |  |  |



- Multipurpose paper ideal for mopping up liquids and hand wiping

| Tork Paper Wiper Plus |            |           |       |     |                    |                                     |             |            | Refill ID: W1, W2, W24                                                                |                                                                                       |                                                                                       |
|-----------------------|------------|-----------|-------|-----|--------------------|-------------------------------------|-------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                   | Format     | Refill ID | Color | Ply | Feet/Unit          | Sheet Size W x L (in)               | Sheets/Unit | Units/Case |  |  |  |
| 192128                | Centerfeed | W2        | White | 1   | 380<br>(115.82 m)  | 9.8 x 15.2<br>(24.18 x 38.61 cm)    | 300         | 2          |  |  |  |
| 192127                | Pop-Up Box | W24       | White | 1   | 135.4<br>(41.27 m) | 9.25 x 16.25<br>(23.50 x 41.28 cm)) | 100         | 8          |  |  |  |
| 430150A               | 1/4 Fold   |           | White | 1   | 97.5<br>(29.72 m)  | 12.5 x 13<br>(31.70 x 33.02 cm)     | 90          | 12         |  |  |  |
| 430151                | 1/4 Fold   |           | White | 1   | 351<br>(106.99 m)  | 12.5 x 13<br>(31.70 x 33.02 cm)     | 60          | 18         |  |  |  |
| 430304                | Giant Roll | W1        | White | 1   | 800<br>(243.84 m)  | 11.1 x 12<br>(28.19 x 30.48 cm)     | 800         | 1          |  |  |  |

## Multipurpose Paper

Refill ID: M2, W1, W2



- Multipurpose paper for light wiping tasks

| Tork Paper Wiper |            |                 |       |     |                 |                                 |             |            |                                                                                     | Refill ID: M2, W1, W2 |                                                                                     |                                                                                     |
|------------------|------------|-----------------|-------|-----|-----------------|---------------------------------|-------------|------------|-------------------------------------------------------------------------------------|-----------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SKU              | Format     | Refill ID       | Color | Ply | Feet/Unit       | Sheet Size W x L (in)           | Sheets/Unit | Units/Case |  | Recycled Content      |  |  |
| 303362           | Pop-Up Box | Self-Dispensing | White | 4   | 174.4 (53.16 m) | 9.75 x 16.75 (24.77 x 42.55 cm) | 125         | 8          |                                                                                     | 100%                  |                                                                                     |                                                                                     |
| 130211B          | Centerfeed | W1, W2          | White | 2   | 866 (263.96 m)  | 9 x 13 (22.86 x 33.02 cm)       | 800         | 2          | ●                                                                                   | 100%                  | ●                                                                                   | ●                                                                                   |
| 130251A          | Centerfeed | M2              | White | 2   | 419 (127.71 m)  | 9 x 15.5 (22.86 x 39.37 cm)     | 325         | 4          | ●                                                                                   | 100%                  | ●                                                                                   | ●                                                                                   |

## Basic Paper

Refill ID: W24



- For basic wiping needs

| Tork Basic Paper Wiper |            |           |       |     |                 |                              |             |            |                                                                                       | Refill ID: W24   |                                                                                       |                                                                                       |
|------------------------|------------|-----------|-------|-----|-----------------|------------------------------|-------------|------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                    | Format     | Refill ID | Color | Ply | Feet/Unit       | Sheet Size W x L (in)        | Sheets/Unit | Units/Case |  | Recycled Content |  |  |
| 192125A                | Pop-Up Box | W24       | White | 2   | 94 (28.65 m)    | 9 x 10.25 (22.86 x 26.04 cm) | 110         | 18         |                                                                                       | 100%             | ●                                                                                     | ●                                                                                     |
| 192126                 | Pop-Up Box | W24       | White | 1   | 213.5 (65.07 m) | 9 x 10.25 (22.86 x 26.04 cm) | 250         | 24         | Mixed                                                                                 |                  |                                                                                       | ●                                                                                     |

### Did you know?

Tork has a wipe and dispenser combination for every task, regardless if you're working in a restaurant, hotel, school, hospital, mechanical workshop or any other environment where hand and surface wiping is part of the job.



# Tork Food Processing Washstation System

You face some of the toughest challenges. That's why you need dispensers and refills you can rely on. The purpose-built, HACCP International certified Tork Washstation Dispenser System is precisely engineered to help mitigate risks, increase operational efficiencies, and handle the pressures of a rigorous environment.



651228



651220

- Durable, water-resistant design holds up well in wet, harsh environments
- High-capacity design requires fewer refills
- Hygienic hands-free dispensing
- Easy to wipe or spray down without removing from wall
- Easy mounting with clear backplate

## Tork Performance Washstation Dispensers

Refill ID: W6

| SKU    | Description           | Refill ID | Color      | Material | Size H x W x D (in)                                | Units/Case |   |   |
|--------|-----------------------|-----------|------------|----------|----------------------------------------------------|------------|---|---|
| 651228 | Washstation Dispenser | W6        | Red/Smoke  | Plastic  | 18.09 x 12.56 x 10.57<br>(45.95 x 31.9 x 26.85 cm) | 1          | ● | ● |
| 651220 | Washstation Dispenser | W6        | Aqua/White | Plastic  | 18.09 x 12.56 x 10.57<br>(45.95 x 31.9 x 26.85 cm) | 1          | ● | ● |

## Food Processing Washstation Paper

Refill ID: W6



291380

- Higher performance sheets
- High footage roll
- Stands up to high humidity

## Tork Paper Wiper

Refill ID: W6

| SKU    | Format     | Refill ID | Color | Ply | Feet/Unit           | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |   |       |   |   |   |
|--------|------------|-----------|-------|-----|---------------------|----------------------------------|-------------|------------|---|-------|---|---|---|
| 291380 | Roll Towel | W6        | White | 1   | 1,150<br>(350.52 m) | 7.68 x 9.5<br>(19.51 x 24.13 cm) | 1,452       | 4          | ● | Mixed | ● | ● | ● |



291350



291370

- Basic performance sheets
- High footage rolls

## Tork Basic Paper Wiper

Refill ID: W6

| SKU    | Format     | Refill ID | Color   | Ply | Feet/Unit           | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |   | Recycled Content |   |   |   |   |   |
|--------|------------|-----------|---------|-----|---------------------|----------------------------------|-------------|------------|---|------------------|---|---|---|---|---|
| 291350 | Roll Towel | W6        | Natural | 1   | 1,150<br>(350.52 m) | 7.68 x 9.5<br>(19.51 x 24.13 cm) | 1,452       | 4          | ● | 100%, EPA CPG    | ● | ● | ● | ● | ● |
| 291370 | Roll Towel | W6        | White   | 1   | 1,150<br>(350.52 m) | 7.68 x 9.5<br>(19.51 x 24.13 cm) | 1,452       | 4          | ● | 100%, EPA CPG    | ● | ● | ● | ● | ● |



## Tork Dairy Towel



2225001



2234003

- **2225001** - Thick, soft and absorbent; use for scrubbing and washing udders and use after udder prep
- **2234003** - Ideal for cleaning and drying after the pre-dip step; strong enough to remove residual dirt
- **2247020** - Offers good absorption and a sanitary way to dry teats during the prep process

| Tork Dairy Towel |                     |               |     |                    |                                     |             |            |                  |
|------------------|---------------------|---------------|-----|--------------------|-------------------------------------|-------------|------------|------------------|
| SKU              | Format              | Color         | Ply | Feet/Unit          | Sheet Size W x L (in)               | Sheets/Unit | Units/Case | Recycled Content |
| 2225001          | Singlefold          | Natural White | 2   | 125<br>(38.1 m)    | 9 x 10<br>(22.86 x 25.40 cm)        | 150         | 15         | 100%,<br>EPA CPG |
| 2234003          | Singlefold, Pre-Dip | Natural Brown | 1   | 223.3<br>(68.06 m) | 9.125 x 10.25<br>(23.18 x 26.04 cm) | 223         | 12         | 100%,<br>EPA CPG |
| 2247020          | Singlefold          | Natural Brown | 1   | 213.5<br>(65.07 m) | 9.125 x 10.25<br>(23.18 x 26.04 cm) | 250         | 16         | 100%             |

## Tork Windshield Paper Towel



192122

- Excellent for cleaning glass
- Multipurpose towel for light wiping tasks

| Tork Windshield Paper Towel |            |       |     |               |                                     |             |            |                  |  |  |
|-----------------------------|------------|-------|-----|---------------|-------------------------------------|-------------|------------|------------------|--|--|
| SKU                         | Format     | Color | Ply | Feet/Unit     | Sheet Size W x L (in)               | Sheets/Unit | Units/Case | Recycled Content |  |  |
| 192122                      | Singlefold | Blue  | 2   | 119 (36.27 m) | 9.125 x 10.25<br>(23.18 x 26.04 cm) | 140         | 16         | 100%,<br>EPA CPG |  |  |

# Tork ShopMax Wipers

## ShopMax Dry Wipes

Ideal for janitorial, maintenance, and production line wiping and cleaning. Tork ShopMax dry wipes are available in several formats (Self-dispensing centerfeed box, Reusable Dry Wipe Centerfeed Bucket, Shop Roll Towel).



450340



450138



450338



450137



450337



450360



450361


- Solid all-purpose paper wipers that feature cloth-like softness
- Excellent oil and water absorption, easily lifts grease and grime
- Strong construction offers durability, won't tear easily

| ShopMax Dry Wipes |                                                                            |                 |            |     |                                                                                                   |             |                      |  |
|-------------------|----------------------------------------------------------------------------|-----------------|------------|-----|---------------------------------------------------------------------------------------------------|-------------|----------------------|--|
| SKU               | Description                                                                | Refill ID       | Color      | Ply | <sup>A</sup> Bucket Size H x W x D (in)<br><sup>B</sup> Sheet Size W x L (in)                     | Sheets/Unit | Units/Case           |  |
| 450340            | Centerfeed Dry Wipe Bucket<br>(Plastic container with a wiper roll inside) | W22             | Blue       | 1   | <sup>A</sup> 10 x 8.5 x 9 (25.4 x 21.59 x 22.86 cm)<br><sup>B</sup> 9.9 x 13.1 (25.15 x 33.27 cm) | 200         | 2 Buckets<br>2 Rolls |  |
| 450138            | Centerfeed Refill<br>(Refill for 450340)                                   | W22             | White      | 1   | <sup>B</sup> 9.9 x 13.1 (25.15 x 33.27 cm)                                                        | 200         | 2 Rolls              |  |
| 450338            | Centerfeed Refill<br>(Refill for 450340)                                   | W22             | Blue       | 1   | <sup>B</sup> 9.9 x 13.1 (25.15 x 33.27 cm)                                                        | 200         | 2 Rolls              |  |
| 450137            | Centerfeed                                                                 | Self-Dispensing | White      | 1   | <sup>B</sup> 9 x 13 (22.86 x 33.02 cm)                                                            | 200         | 4                    |  |
| 450337            | Centerfeed                                                                 | Self-Dispensing | Blue       | 1   | <sup>B</sup> 9 x 13 (22.86 x 33.02 cm)                                                            | 200         | 4                    |  |
| 450360            | Roll Towel                                                                 | Self-Dispensing | Blue/White | 1   | <sup>B</sup> 11 x 9.4 (27.94 x 23.88 cm)                                                          | 60          | 30                   |  |
| 450361            | Roll Towel, 3 Pack                                                         | Self-Dispensing | Blue/White | 1   | <sup>B</sup> 11 x 9.4 (27.94 x 23.88 cm)                                                          | 55          | 24                   |  |

# Tork exelCLEAN

## Professional results, no matter how tough the challenge

With Tork exelCLEAN® you get a quality range of low-linting, high performance cloth wipers. You also get the same reliable performance every time. No more spending time searching through rags for the “right ones”. Tork exelCLEAN benefits your business by increasing employee satisfaction, reducing costs and improving working conditions.



### Did you know?

Our Tork exelCLEAN® and patented foam-spun technologies produce nonwoven cloths setting the standard of excellence for safer, healthier and more efficient workplaces.

### Could your cleaning process be more efficient?

Independent tests have proven that Tork exelCLEAN cleaning cloths out-perform rags and rentals by saving time, effort and solvents used for the same task. Using them means up to:

**35% less time**  
**41% less solvents**  
**31% less effort**

### Improved durability:

Refined to improve high-performance durability with a new, uniform construction.

### More efficient:

Our Top-Paks are now compressed to save up to 26% storage space and transport, requiring less refills, and ensuring the product is there when you need it.

### More flexible packaging:

New improved portable boxes with reinforced handle and larger opening to easily access cloths – even with gloves on.



### USDA Certified Biobased Product:

The USDA® BioPreferred Program certification confirms the plant based composition of the product. The product is certified by the USDA BioPreferred Program and high performing in terms of cleaning, while offering sustainability benefits. When you see the Tork name with the USDA BioPreferred logo, you'll know the products will serve your business needs—and the planet—well.

## Multipurpose Cloths / Industrial Cloths

## Refill ID: W1, W2, W4, W7, W8, W24



- High absorption capacity
- Protects hands from heat and metal scraps
- Provides a professional cleaning result thanks to the exelCLEAN effect

## Tork Industrial Heavy-Duty Cleaning Cloth, with exelCLEAN technology

Refill ID: W1, W2, W4

| SKU    | Format     | Refill ID | Color | Ply | Feet/Unit          | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |  |       |  |  |  |
|--------|------------|-----------|-------|-----|--------------------|----------------------------------|-------------|------------|--|-------|--|--|--|
| 570105 | Giant Roll | W1        | White | 1   | 554<br>(168.86 m)  | 12.6 x 13.3<br>(32.0 x 33.78 cm) | 500         | 1          |  | Mixed |  |  |  |
| 570137 | Centerfeed | W1, W2    | White | 1   | 133.3<br>(40.63 m) | 12.6 x 10.0<br>(32.0 x 25.4 cm)  | 160         | 1          |  | Mixed |  |  |  |
| 570481 | Top-Pak    | W4        | White | 1   | 81.7<br>(24.90 m)  | 14 x 16.5<br>(35.56 x 41.91 cm)  | 60          | 4          |  | Mixed |  |  |  |



- Strong, absorbent multipurpose cloth for heavier cleaning tasks
- Designed to protect hands from heat and metal scraps
- Provides a professional cleaning result thanks to the exelCLEAN effect

## Tork Heavy-Duty Cleaning Cloth, with exelCLEAN technology

Refill ID: W1, W2, W4

| SKU     | Format     | Refill ID | Color | Ply | Feet/Unit            | Sheet Size W x L (in)               | Sheets/Unit | Units/Case |  |       |  |  |  |  |
|---------|------------|-----------|-------|-----|----------------------|-------------------------------------|-------------|------------|--|-------|--|--|--|--|
| 530105  | Giant Roll | W1        | White | 1   | 914.37<br>(278.70 m) | 12.6 x 13.3<br>(32.0 x 33.78 cm)    | 825         | 1          |  | Mixed |  |  |  |  |
| 530137  | Centerfeed | W2        | White | 1   | 333.33<br>(101.59 m) | 12.6 x 10<br>(32.0 x 25.40 cm)      | 400         | 1          |  | Mixed |  |  |  |  |
| 530182  | Top-Pak    | W4        | White | 1   | 143.0<br>(43.58 m)   | 14 x 16.5<br>(35.56 x 41.91 cm)     | 105         | 4          |  | Mixed |  |  |  |  |
| 5301755 | Pop-Up Box | W24       | White | 1   | 107.5<br>(32.77 m)   | 8.27 x 16.125<br>(21.01 x 40.96 cm) | 80          | 5          |  | Mixed |  |  |  |  |
| 5301505 | 1/4 Fold   |           | White | 1   | 54.16<br>(16.51 m)   | 12.6 x 13<br>(32 x 33 cm)           | 50          | 6          |  | Mixed |  |  |  |  |



- Meet the demands of both productivity and sustainability
- Strong, absorbent multipurpose cloth for heavier cleaning tasks
- 99% biobased, slowing down carbon dioxide atmospheric build-up, while performing cleaning tasks as effectively as ever\*

## Tork Heavy-Duty Cleaning Cloth – 99% Biobased, with exelCLEAN technology

Refill ID: W4, W8

| SKU    | Format     | Refill ID | Color | Ply | Feet/Unit         | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |  |  |  |  |  |  |
|--------|------------|-----------|-------|-----|-------------------|----------------------------------|-------------|------------|--|--|--|--|--|--|
| 930151 | Small Pack | W8        | White | 1   | 63.2<br>(19.26 m) | 12.4 x 15.2<br>(31.5 x 38.6 cm)  | 50          | 8          |  |  |  |  |  |  |
| 930181 | Top-Pak    | W4        | White | 1   | --                | 14 x 16.34<br>(35.56 x 41.50 cm) | 105         | 4          |  |  |  |  |  |  |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

\*Product is USDA Certified Biobased

## Multipurpose Cloths / Industrial Cloths

## Refill ID: W1, W2, W4, W7, W8, W24



- exelCLEAN delivers a professional cleaning result
- Strong, absorbent multipurpose cloth for heavier cleaning tasks
- Compatible with most cleaning solvents

| Tork Industrial Cleaning Cloth, with exelCLEAN technology |            |           |       |     |                        |                                   |             |            | Refill ID: W1, W2, W4, W7, W8                                                       |                                                                                     |                                                                                     |                                                                                     |                                                                                     |
|-----------------------------------------------------------|------------|-----------|-------|-----|------------------------|-----------------------------------|-------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SKU                                                       | Format     | Refill ID | Color | Ply | Feet/Unit              | Sheet Size W x L (in)             | Sheets/Unit | Units/Case |  |  |  |  |  |
| 520305                                                    | Giant Roll | W1        | Gray  | 1   | 1,163.75<br>(354.71 m) | 12.6 x 13.3<br>(32.0 x 33.78 cm)  | 1,050       | 1          | ●                                                                                   | Mixed                                                                               | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 520337                                                    | Centerfeed | W2        | Gray  | 1   | 416.7<br>(127.01 m)    | 12.6 x 10.0<br>(32.0 x 25.4 cm)   | 500         | 1          | ●                                                                                   | Mixed                                                                               | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 520681                                                    | Top-Pak    | W4        | Gray  | 1   | 163.4<br>(49.80 m)     | 14 x 16.5<br>(35.56 x 41.91 cm)   | 120         | 4          | ●                                                                                   | Mixed                                                                               | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 520350                                                    | Small Pack | W8        | Gray  | 1   | 69.48<br>(21.18 m)     | 12.6 x 15.16<br>(32.0 x 38.51 cm) | 55          | 8          |                                                                                     | Mixed                                                                               | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 520374                                                    | Handy Box  | W7        | Gray  | 1   | 286.0<br>(87.17 m)     | 14 x 16.34<br>(35.56 x 41.5 cm)   | 210         | 1          |                                                                                     | Mixed                                                                               | ●                                                                                   | ●                                                                                   | ●                                                                                   |



- Soft, flexible cloth for light-to-medium industrial tasks
- Provides a professional cleaning result thanks to the exelCLEAN effect

| Tork Cleaning Cloth, with exelCLEAN technology |            |           |       |     |                     |                                  |              |             | Refill ID: W1, W2, W24                                                                |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                                                                                       |
|------------------------------------------------|------------|-----------|-------|-----|---------------------|----------------------------------|--------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                                            | Format     | Refill ID | Color | Ply | Feet/Unit           | Sheet Size W x L (in)            | Sheets/ Unit | Units/ Case |  |  |  |  |  |  |
| 510105                                         | Giant Roll | W1        | White | 1   | 1,219<br>(371.55 m) | 12.6 x 13.3<br>(32.0 x 33.78 cm) | 1,100        | 1           | ●                                                                                     | Mixed                                                                                 | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 510137                                         | Centerfeed | W2        | White | 1   | 416.6<br>(126.98 m) | 12.6 x 10<br>(32.0 x 25.40 cm)   | 500          | 1           | ●                                                                                     | Mixed                                                                                 | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 510176                                         | Pop-Up Box | W24       | White | 1   | 134.4<br>(40.96 m)  | 8.27 x 16.125<br>(21 x 40.96 cm) | 100          | 10          |                                                                                       | Mixed                                                                                 | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |



- Tork Light-Duty Cleaning Cloth is an economical and better choice of cloth for lighter cleaning tasks
- Provides a professional cleaning result thanks to the exelCLEAN effect

| Tork Light-Duty Cleaning Cloth, with exelCLEAN technology |            |           |       |     |                                  |             |            |                                                                                      | Refill ID: W1, W24                                                                    |                                                                                       |                                                                                       |                                                                                       |                                                                                       |
|-----------------------------------------------------------|------------|-----------|-------|-----|----------------------------------|-------------|------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                                                       | Format     | Refill ID | Color | Ply | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |  |  |  |  |  |  |
| 500105                                                    | Giant Roll | W1        | White | 1   | 12.4 x 9.84<br>(31.5 x 25 cm)    | 1,450       | 1          | ●                                                                                    | Mixed                                                                                 | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |
| 500176                                                    | Pop-Up Box | W24       | White | 1   | 8.27 x 16.125<br>(21 x 40.96 cm) | 120         | 10         |                                                                                      | Mixed                                                                                 | ●                                                                                     | ●                                                                                     | ●                                                                                     | ●                                                                                     |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)



## Tork Specialty Non-Wovens Cloths

Refill ID: W4, W24



- Low-Lint
- Strong and absorbent
- Works well with solvents, detergents and disinfectants

| Tork Low-Lint Cleaning Cloth |                |                 |           |     |                 |                                 |             |            | Refill ID: W4, W24                                                                  |                                                                                     |                                                                                     |                                                                                     |
|------------------------------|----------------|-----------------|-----------|-----|-----------------|---------------------------------|-------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SKU                          | Format         | Refill ID       | Color     | Ply | Feet/Unit       | Sheet Size W x L (in)           | Sheets/Unit | Units/Case |  |  |  |  |
| 192480                       | Top-Pak        | W4              | Turquoise | 1   | 163.4 (49.80 m) | 14 x 16.5<br>(35.56 x 41.91 cm) | 120         | 4          |  | Mixed                                                                               |  |  |
| 192475                       | Pop-Up Box     | W24             | Turquoise | 1   | 137.5 (41.91 m) | 9 x 16.5<br>(22.86 x 41.91 cm)  | 100         | 8          |                                                                                     | Mixed                                                                               |  |  |
| 192481                       | Flat Pack      | Self-Dispensing | Blue      | 1   | 250 (76.2 m)    | 12 x 12<br>(38.48 x 38.48 cm)   | 250         | 1          |                                                                                     |                                                                                     |                                                                                     |                                                                                     |
| 192483                       | Centerfeed Box | Self-Dispensing | Blue      | 1   | 300 (91.44 m)   | 9 x 15<br>(22.86 x 38.1 cm)     | 240         | 4          |                                                                                     |                                                                                     |                                                                                     |                                                                                     |



192593

- Tough on grease and dirt
- Silicone opening and smart re-sealable lid – keeps your wipes from drying out
- Portion control with easy one-wipe-at-a-time dispensing
- No need to rinse afterward; won't leave a residue
- The hand cleaner is gentle enough on your skin for frequent usage

| Tork Hand Cleaning Wet Wipes |                 |       |     |                                |             |            |                                                                                       |  |
|------------------------------|-----------------|-------|-----|--------------------------------|-------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| SKU                          | Refill ID       | Color | Ply | Sheet Size W x L (in)          | Sheets/Unit | Units/Case |                                                                                       |                                                                                       |
| 192593                       | Self-Dispensing | White | 1   | 10.6 x 10.6 (26.92 x 26.92 cm) | 58          | 4          |  |                                                                                       |

# Tork Microfibers

Microfibers are very fine so that they have a lot of surface area, which increases the absorbency. Microfiber cloths have pockets, which easily pick up dirt and dust and are also fine enough to pick up microbes. When woven together into a textile cloth, microfibers create a cloth with excellent and efficient cleaning properties.



800200

- Wipes away 99.99% of microorganisms from surfaces-including Cdiff\*
- Designed for one-time use and disposal
- Can be used dry or with cleaning solutions, sanitizers, and disinfectants
- Low lint

## Tork Microfiber Disposable Cleaning Cloths

| SKU    | Color                 | Material   | Efficacy       | Sheet Size W x L (in)      | Sheets/Unit | Units/Case |
|--------|-----------------------|------------|----------------|----------------------------|-------------|------------|
| 800200 | White with Blue Print | Microfiber | Microorganisms | 11.6 x 13.4 (34 x 29.5 cm) | 40          | 8          |

\*Use with disinfectants (not included in this pack) as directed by local authorities and guidelines. Refer to disinfectant manufacturer's instructions for application of disinfectant with microfiber cloths. Methods are modified versions of industry standard methods (^EN16615 and ASTM E-2362-16 and E-2967-15). Tested with S. aureus, P. aeruginosa, E. hirae, C. albicans, C. difficile. For Environmental surfaces – not medical devices (does not sterilize).

# Tork Foodservice Towels

## Solutions that keep up with your pace

We understand the high-tempo nature of working in a modern restaurant or catering facility. In these environments, wiping and cleaning tasks can involve everything from grease-covered stove tops, grills and working surfaces of different kinds to cleaning dining areas, service counters and other areas that guests and staff come into contact with.



As well as maintaining hygiene, our range of wipers keep your kitchen, restaurant, bar or café looking fresh at all times.

### **Back-of-house:**

Throughout the day, oil and grease, stains and spills must be thoroughly cleaned from various surfaces, stainless steel equipment and tiles. Whether it's picking up spills or cleaning oil, grease, or food particles, Tork has a wiper for the job.

### **Front-of-house:**

In foodservice cross-contamination is a constant concern. Tork foodservice cleaning towels come in a variety of colors, which allows you to designate areas of use, which greatly mitigates this concern.

## Foodservice Towels

Refill ID: W8



655300

- Space-saving dispenser brackets perfect for server stations, back of house, or storage areas
- Keep small-pack foodservice towels accessible where you need them, when you need them

## Torq Small Pack Dispenser Bracket

Refill ID: W8

| SKU    | Refill ID | Color | Material | Size H x W x D (in)                              | Units/Case |  |
|--------|-----------|-------|----------|--------------------------------------------------|------------|-------------------------------------------------------------------------------------|
| 655300 | W8        | White | Plastic  | 5.74 x 8.42 x 4.22<br>(14.58 x 21.39 x 10.72 cm) | 4          |                                                                                     |



192191



192291



192192



192292



192193



192293



192194

- **Odor Resistant technology** – inhibits the growth of odor-causing bacteria in the foodservice towel, which keeps the towel fresh longer
- Poly packed wipers protect the wipers until they are used

## Torq Odor Resistant Foodservice Cleaning Towel\*

Refill ID: W8

| SKU    | Format     | Refill ID       | Color                       | Ply | Feet/Unit      | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |  |
|--------|------------|-----------------|-----------------------------|-----|----------------|----------------------------------|-------------|------------|-------------------------------------------------------------------------------------|
| 192191 | 1/4 Fold   | Self-Dispensing | White/Red Stripe            | 1   | 300 (91.44 m)  | 13 x 24 (33.02 x 60.96 cm)       | 150         | 1          | ●                                                                                   |
| 192291 | Small Pack | W8              | White/Red Stripe            | 1   | 98.3 (29.96 m) | 11.75 x 14.75 (29.85 x 37.47 cm) | 50          | 4          | ●                                                                                   |
| 192192 | 1/4 Fold   | Self-Dispensing | Blue/Blue Stripe            | 1   | 300 (91.44 m)  | 13 x 24 (33.02 x 60.96 cm)       | 150         | 1          | ●                                                                                   |
| 192292 | Small Pack | W8              | Blue/Blue Stripe            | 1   | 98.3 (29.96 m) | 11.75 x 14.75 (29.85 x 37.47 cm) | 50          | 4          | ●                                                                                   |
| 192193 | 1/4 Fold   | Self-Dispensing | Red/Red Stripe              | 1   | 300 (91.44 m)  | 13 x 24 (33.02 x 60.96 cm)       | 150         | 1          | ●                                                                                   |
| 192293 | Small Pack | W8              | Red/Red Stripe              | 1   | 98.3 (29.96 m) | 11.75 x 14.75 (29.85 x 37.47 cm) | 50          | 4          | ●                                                                                   |
| 192194 | 1/4 Fold   | Self-Dispensing | Heavy-Duty White/Red Stripe | 1   | 87 (26.52 m)   | 13 x 21 (33.02 x 53.34 cm)       | 50          | 1          | ●                                                                                   |

\*192191, 192291, 192192, 192292, 192193, 192293 and 192194 can only be sold in the US



192181A



192183



192185



192187



192197

- Ideal for use with a wide range of cleaning, degreasing and sanitizing chemicals
- Sturdy towels provide good absorption, pick up dirt and mop up spills effectively

## Torq Foodservice Towel

Refill ID: W8

| SKU     | Format     | Refill ID       | Color       | Ply | Feet/Unit        | Sheet Size W x L (in)            | Sheets/Unit | Units/Case |  |
|---------|------------|-----------------|-------------|-----|------------------|----------------------------------|-------------|------------|---------------------------------------------------------------------------------------|
| 192181A | 1/4 Fold   | Self-Dispensing | Blue/White  | 1   | 430 (131.06 m)   | 13 x 21 (33.02 x 53.34 cm)       | 240         | 1          | ●                                                                                     |
| 192183  | Small Pack | W8              | Blue/White  | 1   | 98.3 (29.96 m)   | 11.75 x 14.75 (29.85 x 37.47 cm) | 80          | 4          | ●                                                                                     |
| 192185  | 1/4 Fold   | Self-Dispensing | Green/White | 1   | 1,050 (320.04 m) | 11.5 x 21 (29.2 x 53.3 cm)       | 600         | 1          | ●                                                                                     |
| 192187  | 1/4 Fold   | Self-Dispensing | Pink/White  | 1   | 358.3 (109.21 m) | 12 x 21.5 (30.48 x 54.61 cm)     | 200         | 1          | ●                                                                                     |
| 192197  | 1/4 Fold   | Self-Dispensing | White       | 1   | 268.8 (81.9 m)   | 10 x 21.5 (25.4 x 54.61 cm)      | 150         | 1          | ●                                                                                     |

- Versatile and convenient - one product with multiple cleaning functions
- Suitable for use all kind of environments and tasks
- Easy to clean in hard to reach places
- Rinse and reuse again and again
- Abrasiveness can tackle the tough messes
- Breaks up hardened and encrusted messes without scratching surfaces
- Designed to be abrasive and absorbent at the same time



192815

## Torq 2 in 1 Scouring and Cleaning Foodservice Towel

| SKU    | Format   | Refill ID       | Color | Ply | Feet/Unit        | Sheet Size W x L (in)      | Sheets/Unit | Units/Case |  |  |  |  |
|--------|----------|-----------------|-------|-----|------------------|----------------------------|-------------|------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 192815 | 1/4 Fold | Self-Dispensing | White | 1   | 1,260 (384.05 m) | 13 x 21 (33.02 x 53.34 cm) | 120         | 1          | Mixed                                                                                 | ●                                                                                     | ●                                                                                     | ●                                                                                     |

\*Boeing Material Standard (BMS 15-5G). Products certified for aviation use.





# Everwipe by Tork Chem-Ready Wiping System

The Everwipe® by Tork® Chem-Ready Wiping System allows you to create your own wet wipes by placing the wiping roll into the bucket and adding the chemical of your choice. Chem-Ready is cleaner, safer and simpler than traditional open bucket or spray bottle systems.



192840



192841

- Ideal for use with water-based cleaning solutions, sanitizers and disinfectants\*

Everwipe by Tork Chem-Ready Wiping Rolls

Cleaning — Refill ID: W11

| Essity SKU | Description             | Color | Sheet Size<br>L x W (in) | Units/Case | Sheets/Unit | Sheets/Case |  |  |
|------------|-------------------------|-------|--------------------------|------------|-------------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| New 192840 | Chem-Ready Wiping Rolls | White | 12 x 5.25                | 6 Rolls    | 180/Roll    | 1,080       | ●                                                                                     | ●                                                                                     |
| New 192841 | Chem-Ready Wiping Rolls | White | 12 x 10.5                | 6 Rolls    | 90/Roll     | 540         | ●                                                                                     | ●                                                                                     |



192850

- A closed system that greatly reduces the potential for cross-contamination
- Cleaner, safer and simpler than traditional open bucket or spray bottle systems

Everwipe by Tork Chem-Ready Bucket

Refill ID: W11

| Essity SKU | Description        | Color | Material | Volume   | Units/Case |  |
|------------|--------------------|-------|----------|----------|------------|---------------------------------------------------------------------------------------|
| New 192850 | Chem-Ready Buckets | White | Plastic  | 1 Gallon | 5 Buckets  | ●                                                                                     |

\*Follow your cleaning chemical provider's guidance on proper wiper/chemical loading.

## Everwipe by Tork Disinfectant Wipes

Simplify surface hygiene tasks with these multipurpose disinfecting and cleaning wipes. Kills 99.9% of viruses\*, bacteria, and fungi.



192820



192821

## Everwipe by Tork Surface Cleaning Wet Wipes

Ideal for keeping all of your surfaces clean and fresh. Keep your high-traffic areas well stocked and ready for business.



- Quick, easy, effective
- Cleans, disinfects<sup>3</sup> and deodorizes
- Kills Cold<sup>1</sup> and Flu Viruses<sup>+++</sup>
- Kills SARS-CoV-2 (COVID-19 Virus) on hard, non-porous surfaces in 30 seconds!<sup>3</sup>

### Everwipe by Tork Disinfectant Wipes

Disinfecting — Refill ID: Jumbo Rolls: W12

| Essity SKU        | Description                   | Color | Sheet Size L x W (in) | Units/Case  | Sheets/Unit | Sheets/Case |
|-------------------|-------------------------------|-------|-----------------------|-------------|-------------|-------------|
| <b>New</b> 192820 | Disinfectant Wipe Canisters   | White | 7 x 7                 | 6 Canisters | 75/Canister | 450         |
| <b>New</b> 192821 | Disinfectant Wipe Jumbo Rolls | White | 6 x 8                 | 2 Rolls     | 800/Roll    | 1,600       |



192816

- Ideal for light-duty cleaning tasks like wiping grocery carts or gym equipment
- Clean and clear, low streaking formulation



192830

- Cleans and deodorizes with one wipe
- Removes sweat, body oils and grime from surfaces
- Suitable for all types of fitness equipment or most hard, non-porous surfaces

### Everwipe by Tork Surface Cleaning Wet Wipes

Cleaning — Refill ID: W12

| Essity SKU        | Description                                      | Color | Sheet Size L x W (in) | Units/Case | Sheets/Unit | Sheets/Case | NSF |
|-------------------|--------------------------------------------------|-------|-----------------------|------------|-------------|-------------|-----|
| <b>New</b> 192816 | Light-Duty Surface Cleaning Wet Wipe Jumbo Rolls | White | 6 x 8                 | 2 Rolls    | 2,500/Roll  | 5,000       | ●   |
| <b>New</b> 192830 | Surface Cleaning Wet Wipe Jumbo Rolls            | White | 6 x 8                 | 4 Rolls    | 900/Roll    | 3,600       | ●   |



192851

- Centerfeed wall-mounted dispenser
- High capacity
- Fresh white finish, professional appearance



192852

- High capacity
- Portable
- Washable, reusable buckets
- Dishwasher safe



192853

- High capacity
- Easy to refill
- Floorstand
- Durable
- Silver stainless steel finish
- Internal trash bin

### Everwipe by Tork Dispensing Options

Refill ID: W12

| Essity SKU | Description                    | Color  | Material        | Size H x W x D (in)  | Units/Case  |
|------------|--------------------------------|--------|-----------------|----------------------|-------------|
| 192851     | Centerfeed Wet Wipe Dispenser  | White  | Plastic         | 12.75 x 10.5 x 10.0  | 1 Dispenser |
| 192852     | Mobile Wet Wipe Buckets        | White  | Plastic         | 10.5 x 12.5 x 12.5   | 2 Buckets   |
| 192853     | Stainless Steel Wet Wipe Stand | Silver | Stainless Steel | 35.5 x 13.25 x 13.25 | 1 Dispenser |

\* Viruses including Norovirus (Norwalk Virus), Human Rotavirus, Hepatitis B Virus (HBV), Hepatitis C Virus (HCV), Human Immunodeficiency Virus Type 1 (HIV-1), Herpes Simplex Virus 1 (HSV-1), Herpes Simplex Virus 2 (HSV-2)

<sup>3</sup> When used according to disinfection directions

<sup>1</sup> Human Coronavirus (ATCC VR-740)

<sup>+++</sup> Influenza A Virus, H1N1 Influenza A Virus, Human Coronavirus<sup>1</sup>

## Tork Elevation Centerfeed Dispensers

Refill ID: M1, M2



559020A



559028A



558028A

- Easy one-handed operation and controlled consumption
- Sleek black or white dispensers complement any environment, providing a clean, hygienic appearance.
- Ideal for hand and light surface wiping

| Tork Elevation Centerfeed Dispensers |                                 |           |       |          |                                                   |            | Refill ID: M1, M2                                                                   |                                                                                     |
|--------------------------------------|---------------------------------|-----------|-------|----------|---------------------------------------------------|------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SKU                                  | Description                     | Refill ID | Color | Material | Size H x W x D (in)                               | Units/Case |  |  |
| 559020A                              | Centerfeed Towel Dispenser      | M2        | White | Plastic  | 14.39 X 9.42 X 8.95<br>(36.55 X 22.93 X 22.73 cm) | 1          | ●                                                                                   | ●                                                                                   |
| 559028A                              | Centerfeed Towel Dispenser      | M2        | Black | Plastic  | 14.39 X 9.42 X 8.95<br>(36.55 X 22.93 X 22.73 cm) | 1          | ●                                                                                   | ●                                                                                   |
| 558028A                              | Mini Centerfeed Towel Dispenser | M1        | Black | Plastic  | 13.05 x 6.86 x 6.51<br>(33.15 x 17.42 x 16.54 cm) | 1          | ●                                                                                   | ●                                                                                   |

## Multipurpose Paper

Refill ID: M2



100230

- Multipurpose paper ideal for mopping up liquids and hand wiping

## Tork Paper Wiper Plus

Refill ID: M2

| SKU    | Format     | Refill ID | Color | Ply | Towel Size W x L (in)            | Linear Feet/Roll | Towels/Case | Rolls/Case |  |
|--------|------------|-----------|-------|-----|----------------------------------|------------------|-------------|------------|---------------------------------------------------------------------------------------|
| 100230 | Centerfeed | M2        | White | 1   | 7.7 x 11.8<br>(19.56 x 29.97 cm) | 300<br>(91.44 m) | 1,830       | 6          | ●                                                                                     |



130251A

- Multipurpose paper for light wiping tasks

## Tork Paper Wiper

Refill ID: M2

| SKU     | Format     | Refill ID | Color | Ply | Feet/Unit         | Sheet Size W x L (in)          | Sheets/Unit | Units/Case |  | Recycled Content |  |  |
|---------|------------|-----------|-------|-----|-------------------|--------------------------------|-------------|------------|---------------------------------------------------------------------------------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 130251A | Centerfeed | M2        | White | 2   | 419<br>(127.71 m) | 9 x 15.5<br>(22.86 x 39.37 cm) | 325         | 4          | ●                                                                                     | 100%             | ●                                                                                     | ●                                                                                     |

Basic Paper

Refill ID: M1, M2



- Roll for basic wiping needs

Tork Basic Paper Towel

Refill ID: M1, M2

| SKU    | Format          | Refill ID | Color | Ply | Towel Size<br>W x L (in)          | Linear Feet/<br>Roll | Towels/<br>Case | Rolls/<br>Case |  |  | Recycled<br>Content |  |
|--------|-----------------|-----------|-------|-----|-----------------------------------|----------------------|-----------------|----------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------|-------------------------------------------------------------------------------------|
| 121201 | Centerfeed      | M2        | White | 2   | 9 x 11.8<br>(22.86 x 29.97 cm)    | 590 (179.83 m)       | 3,600           | 6              | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |
| 121202 | Centerfeed      | M2        | White | 2   | 8.25 x 11.8<br>(20.96 x 29.97 cm) | 600 (182.88 m)       | 3,660           | 6              | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |
| 121204 | Centerfeed      | M2        | White | 2   | 7.6 x 11.8<br>(19.30 x 29.97 cm)  | 590 (179.83 m)       | 3,600           | 6              | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |
| 120932 | Centerfeed      | M2        | White | 2   | 7.6 x 11.8<br>(19.30 x 29.97 cm)  | 491 (149.66 m)       | 3,000           | 6              | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |
| 121211 | Centerfeed      | M2        | White | 2   | 7.1 x 11.8<br>(18.3 x 29.97 cm)   | 590 (179.83 m)       | 3,600           | 6              | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |
| 120133 | Centerfeed      | M2        | White | 1   | 8.25 x 11.8<br>(20.96 x 29.97 cm) | 983 (299.62 m)       | 6,000           | 6              | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |
| 121225 | Mini Centerfeed | M1        | White | 2   | 8.3 x 11.8<br>(21.08 x 29.97 cm)  | 262 (79.86 m)        | 3,192           | 12             | ●                                                                                   | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   |



## Standard Centerfeed System

Refill ID: M23



93T



RC530

### Dispenser

| SKU | Description                | Refill ID | Color | Material | Size H x W x D (in)                              | Units/Case | ADA Compliant |
|-----|----------------------------|-----------|-------|----------|--------------------------------------------------|------------|---------------|
| 93T | Centerfeed Towel Dispenser | M23       | Smoke | Plastic  | 12.75 x 10.125 x 10<br>(32.39 x 29.72 x 25.4 cm) | 1          |               |

### Refill

| SKU   | Description       | Refill ID | Color | Ply | Towel Size W x L (in)             | Linear Feet/Roll  | Towels/Case | Rolls/Case | Recycled Content | NSF |
|-------|-------------------|-----------|-------|-----|-----------------------------------|-------------------|-------------|------------|------------------|-----|
| RC530 | Basic Paper Towel | M23       | White | 2   | 7.6 x 11.75<br>(19.30 x 29.85 cm) | 519<br>(158.19 m) | 3,180       | 6          | 100%,<br>EPA CPG |     |

## Tork Perforated Roll Towels (Household Roll Towels)



HB9201



HB1990A



HB1995A

- Super soft paper towels that don't leave lint or scratches when wiping up water or other spills
- Strong 2 ply sheets that are highly absorbent so you can reduce the number of towels needed to do the job
- Long lasting Jumbo Roll contains 210 sheet 3 times as many sheets as a standard paper towel

### Tork Perforated Roll Towels

| SKU     | Description           | Color | Ply | Towel Size W x L (in)          | Towels/Roll | Towels/Case | Rolls/Case | Recycled Content | NSF | NSF |
|---------|-----------------------|-------|-----|--------------------------------|-------------|-------------|------------|------------------|-----|-----|
| HB9201  | Handi-Size® Sheet     | White | 2   | 11 x 6.75<br>(27.94 x 17.15cm) | 120         | 3,600       | 30         | 100%,<br>EPA CPG |     |     |
| HB1990A | Perforated Roll Towel | White | 2   | 11 x 8.6<br>(27.94 x 21.91 cm) | 84          | 2,520       | 30         | 100%             |     |     |
| HB1995A | Jumbo Roll            | White | 2   | 11 x 8.6<br>(27.94 x 21.91 cm) | 210         | 2,520       | 12         | 100%             |     |     |

# Tabletop

## Making it easy to create a great experience

It's not enough just to provide satisfactory service – you need to create a great experience to keep reviews positive and customers coming through the door. When doing this, we know the details matter, and we can help you get them right.



## Product ranges to meet different needs

### Self-service with napkin dispensing system

When customers dispense their own napkins, refilling, controlling napkin waste and storage need to be effortless, easy and convenient.

### Full-service with single-serve napkins

The quality feel of your table setting is one of many important things that creates a restaurant's ambiance.





# Tork Xpressnap Napkin systems

Designed for busy self-service environments where napkins need to be available close at hand. Tork Xpressnap® and Tork Xpressnap Fit® support a faster, more efficient guest experience when hygiene and swift maintenance are critical. One-at-a-time dispensing helps you control consumption and costs.



Reduces  
napkin usage  
by at least  
**25%<sup>1</sup>**



- A wide range of stylish, modern dispensers to fit your needs
- Improved hygiene, as your guests only touch what they take
- Get your message across with custom-printed napkins
- Promote your brand, offer or generate extra revenue with the AD-a-Glance® Display panels

Visit [adaglace.torkusa.com](https://adaglace.torkusa.com) for inspiration!

<sup>1</sup> When compared to traditional napkin dispensers. Does not include the drive thru model or Tork Xpressnap Fit® N14 system.



Tabletop/counter  
72900/73350



Tabletop  
6232100/6234100  
6236100



Counter  
6432000/6434000  
6436000



Stand  
6332000/6334000  
6336000



In-Counter  
6032200/6032120  
6032050

## Tork Xpressnap Napkin Dispensers

Refill ID: N4

| SKU     | Description            | Design Line | Color     | Material | Size<br>H x W x D (in)                          | Capacity*                      | AD-a-<br>Glance | Mountable | Units/<br>Case |  |
|---------|------------------------|-------------|-----------|----------|-------------------------------------------------|--------------------------------|-----------------|-----------|----------------|-------------------------------------------------------------------------------------|
| 72900   | Tabletop               | Image       | Walnut    | Wood     | 7.6 x 8 x 5.5<br>(19.30 x 20.32 x 13.97 cm)     | Up to 150<br>(2-ply napkins)   |                 |           | 1              | ●                                                                                   |
| 73350   | Tabletop               | Image       | Aluminium | Metal    | 8.23 x 7.1 x 5.91<br>(20.90 x 18.03 x 15.01 cm) | Up to 150<br>(2-ply napkins)   |                 |           | 1              | ●                                                                                   |
| 6232100 | Tabletop               | Signature   | Black     | Plastic  | 6.7 x 7.9 x 5.6<br>(16.9 x 20.1 x 14.1 cm)      | Up to 250<br>(1-ply napkins)   | ●               |           | 4              | ●                                                                                   |
| 6234100 | Tabletop               | Signature   | Gray      | Plastic  | 6.7 x 7.9 x 5.6<br>(16.9 x 20.1 x 14.1 cm)      | Up to 250<br>(1-ply napkins)   | ●               |           | 4              | ●                                                                                   |
| 6236100 | Tabletop               | Signature   | Red       | Plastic  | 6.7 x 7.9 x 5.6<br>(16.9 x 20.1 x 14.1 cm)      | Up to 250<br>(1-ply napkins)   | ●               |           | 4              | ●                                                                                   |
| 6432000 | Counter                | Signature   | Black     | Plastic  | 5.7 x 7.5 x 12.1<br>(14.48 x 19.05 x 30.73 cm)  | Up to 500<br>(1-ply napkins)   | ●               |           | 1              | ●                                                                                   |
| 6434000 | Counter                | Signature   | Gray      | Plastic  | 5.7 x 7.5 x 12.1<br>(14.48 x 19.05 x 30.73 cm)  | Up to 500<br>(1-ply napkins)   | ●               |           | 1              | ●                                                                                   |
| 6436000 | Counter                | Signature   | Red       | Plastic  | 5.7 x 7.5 x 12.1<br>(14.48 x 19.05 x 30.73 cm)  | Up to 500<br>(1-ply napkins)   | ●               |           | 1              | ●                                                                                   |
| 6332000 | Stand                  | Signature   | Black     | Plastic  | 24.5 x 9.25 x 9.25<br>(62.23 x 23.5 x 23.5 cm)  | Up to 1,000<br>(1-ply napkins) | ●               | ●         | 1              | ●                                                                                   |
| 6334000 | Stand                  | Signature   | Gray      | Plastic  | 24.5 x 9.25 x 9.25<br>(62.23 x 23.5 x 23.5 cm)  | Up to 1,000<br>(1-ply napkins) | ●               | ●         | 1              | ●                                                                                   |
| 6336000 | Stand                  | Signature   | Red       | Plastic  | 24.5 x 9.25 x 9.25<br>(62.23 x 23.5 x 23.5 cm)  | Up to 1,000<br>(1-ply napkins) | ●               | ●         | 1              | ●                                                                                   |
| 6032050 | In-Counter, 5 inches** | Signature   | Black     | Plastic  | 6.5 x 9.9 x 7.00<br>(16.51 x 25.15 x 17.78 cm)  | Up to 250<br>(1-ply napkins)   |                 | ●         | 1              | ●                                                                                   |
| 6032120 | In-Counter, 12 inches  | Signature   | Black     | Plastic  | 13.5 x 9.9 x 7.00<br>(34.29 x 25.15 x 17.78 cm) | Up to 600<br>(1-ply napkins)   |                 | ●         | 1              | ●                                                                                   |
| 6032200 | In-Counter, 20 inches  | Signature   | Black     | Plastic  | 21.5 x 9.9 x 7.00<br>(54.61 x 25.15 x 17.78 cm) | Up to 1,000<br>(1-ply napkins) |                 | ●         | 1              | ●                                                                                   |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

\*Depending on napkin refill used, dispenser capacity will vary.

\*\*Special Order.



# Tork Xpressnap Drive Thru Napkin Dispenser

## Keep your drive thru moving

With the Tork Xpressnap Drive Thru Napkin Dispenser, you can improve efficiency and deliver a more hygienic guest experience. Thanks to multi-napkin dispensing, you will always have a neat bundle of napkins ready to put in a bag - even under time pressure.



**60%** of quick-service restaurant orders are takeout or delivery<sup>1</sup>



**QSR: 100- 200 drive thru orders/ daily**

“Push Button” Drive-Thru 6532000

- **Saves time** with multi-napkin dispensing using intuitive two button design
- **Promotes hygiene** by protecting napkins and reducing the number of touchpoints
- **Reduces waste** by preventing staff from handing out too many napkins
- **Easy to use**<sup>1</sup> when opening, loading, dispensing and cleaning

| Tork Xpressnap Napkin Drive Thru Dispensers |                  |             |       |          |                                               |                                |                 |           |                | Refill ID: N4                                                                         |
|---------------------------------------------|------------------|-------------|-------|----------|-----------------------------------------------|--------------------------------|-----------------|-----------|----------------|---------------------------------------------------------------------------------------|
| SKU                                         | Description      | Design Line | Color | Material | Size<br>H x W x D (in)                        | Capacity <sup>2</sup>          | AD-a-<br>Glance | Mountable | Units/<br>Case |  |
| 6532000                                     | Stand Drive Thru | Signature   | Black | Plastic  | 24.5 x 9.3 x 10.0<br>(62.23 x 23.6 x 35.8 cm) | Up to 1,000<br>(1-ply napkins) | ●               | ●         | 1              | ●                                                                                     |

<sup>1</sup>Technomic September 2025 consumer study  
<sup>2</sup>Depending on napkin refill used, dispenser capacity will vary



101990



119906



DX900



DX906E



908EX

- Refills for different needs and environments
- Our unique, larger 1/4 fold napkins provide extra protection when unfolded
- Bundles are protected in a bag, for improved hygiene and handling
- Custom print option

## Tork Xpressnap Dispenser Napkins

Refill ID: N4

| SKU    | Quality Tier | Color                                     | Ply | Fold | Emboss | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)               | Napkins/<br>Package | Napkins/<br>Case |  |  | Custom<br>print<br>available |  | Recycled<br>Content |  |  |  |  |
|--------|--------------|-------------------------------------------|-----|------|--------|----------------------------------------------------------------------------------------------|---------------------|------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------------------|-------------------------------------------------------------------------------------|---------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 101990 | Advanced     | White                                     | 2   | 1/2  | Micro  | <sup>A</sup> 6.5 x 8.5<br>(16.51 x 21.59 cm)<br><sup>B</sup> 6.5 x 4.25<br>(16.51 x 10.8 cm) | 250/<br>Sleeve      | 8,000            | ●                                                                                 | ●                                                                                   | ●                            | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 119906 | Advanced     | Natural                                   | 2   | 1/2  | Micro  | <sup>A</sup> 6.5 x 8.5<br>(16.51 x 21.59 cm)<br><sup>B</sup> 6.5 x 4.25<br>(16.51 x 10.8 cm) | 250/<br>Sleeve      | 8,000            | ●                                                                                 | ●                                                                                   | ●                            | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| DX900  | Universal    | White                                     | 1   | 1/4  | Linen  | <sup>A</sup> 13 x 8.5<br>(33.02 x 21.59 cm)<br><sup>B</sup> 6.5 x 4.25<br>(16.51 x 10.8 cm)  | 500/Bag             | 6,000            | ●                                                                                 | ●                                                                                   | ●                            | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| DX906E | Universal    | Natural                                   | 1   | 1/4  | Linen  | <sup>A</sup> 13 x 8.5<br>(33.02 x 21.59 cm)<br><sup>B</sup> 6.5 x 4.25<br>(16.51 x 10.8 cm)  | 500/Bag             | 6,000            | ●                                                                                 | ●                                                                                   | ●                            | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   |
| 908EX  | Universal    | Natural<br>with<br>Environmental<br>Print | 1   | 1/4  | Linen  | <sup>A</sup> 13 x 8.5<br>(33.02 x 21.59 cm)<br><sup>B</sup> 6.5 x 4.25<br>(16.51 x 10.8 cm)  | 500/Bag             | 6,000            | ●                                                                                 | ●                                                                                   | ●                            | Recycled                                                                            | 100%,<br>EPA CPG    | ●                                                                                   | ●                                                                                   | ●                                                                                   | ●                                                                                   |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

# Tork Xpressnap Fit

The smarter napkin solution that helps you increase efficiency and promote hygiene

Tork Xpressnap Fit® is our most compact dispenser napkin system yet, designed to reduce refill time and free up space.

Fewer refills and less cleaning means more time for you to focus on your guests and your business.



Cuts unused napkins thrown away by more than **50%\***



7232000



7432000

- Durable and easy-to-clean dispensers reduce time for maintenance and protect napkins from dirt and spills
- Compact design provides more table space for guests
- Cuts napkin inventory space by **up to 50%\***
- Reduces napkin refill time by **46%\***
- Serve almost **2x** as many guests between refills\*

## Tork Xpressnap Fit Dispensers

Refill ID: N14

| SKU     | Description | Design Line | Color | Material | Size<br>H x W x D (in)                      | Capacity* | AD-a-<br>Glance | Units/<br>Case |   |
|---------|-------------|-------------|-------|----------|---------------------------------------------|-----------|-----------------|----------------|---|
| 7232000 | Tabletop    | Signature   | Black | Plastic  | 6.7 x 4.4 x 5.6<br>(17.0 x 11.3 x 14.1 cm)  | Up to 168 | ●               | 4              | ● |
| 7432000 | Counter     | Signature   | Black | Plastic  | 5.6 x 4.8 x 12.8<br>(14.3 x 12.1 x 32.6 cm) | Up to 324 | ●               | 1              | ● |



800700



806700



500700



506700

- A full-size napkin is folded to fit the small-footprint dispenser
- Specially-designed fold makes the first napkin easy to grab after dispenser refills
- Leaf embossing enhances the guest experience and easy to recognize

## Tork Xpressnap Fit Dispenser Napkins

Refill ID: N14

| SKU    | Quality Tier | Color   | Ply | Fold      | Emboss         | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)           | Napkins/<br>Package | Napkins/<br>Case |   |          | Recycled Content |   |
|--------|--------------|---------|-----|-----------|----------------|------------------------------------------------------------------------------------------|---------------------|------------------|---|----------|------------------|---|
| 800700 | Advanced     | White   | 2   | Interfold | Overall & Leaf | <sup>A</sup> 6.5 x 8.39 (16.51 x 21.31 cm)<br><sup>B</sup> 3.24 x 4.21 (8.23 x 10.69 cm) | 120/Sleeve          | 4,320            | ● | Recycled | 100%,<br>EPA CPG | ● |
| 806700 | Advanced     | Natural | 2   | Interfold | Overall & Leaf | <sup>A</sup> 6.5 x 8.39 (16.51 x 21.31 cm)<br><sup>B</sup> 3.24 x 4.21 (8.23 x 10.69 cm) | 120/Sleeve          | 4,320            | ● | Recycled | 100%,<br>EPA CPG | ● |
| 500700 | Universal    | White   | 1   | Interfold | Linen          | <sup>A</sup> 6.5 x 8.39 (16.51 x 21.31 cm)<br><sup>B</sup> 3.24 x 4.21 (8.23 x 10.69 cm) | 240/Sleeve          | 8,640            | ● | Recycled | 100%,<br>EPA CPG | ● |
| 506700 | Universal    | Natural | 1   | Interfold | Linen          | <sup>A</sup> 6.5 x 8.39 (16.51 x 21.31 cm)<br><sup>B</sup> 3.24 x 4.21 (8.23 x 10.69 cm) | 240/Sleeve          | 8,640            | ● | Recycled | 100%,<br>EPA CPG | ● |



Learn more about Tork Focus4 Sustainability product benefits:  
[www.torkglobal.com/us/en/sustainability#focus4materials](http://www.torkglobal.com/us/en/sustainability#focus4materials)

\*1-ply napkin in Tabletop dispenser compared to Tallfold (Tork Dispenser 1TBS and Tork refill: D3052B)

Tork Dispenser Napkins

Refill ID: N6, N7



| Tork Dispenser Napkins |             |              |         |           |     |            |         |                                                                                            |                     | Refill ID: N6/N7 |                                                                                     |                  |                                                                                     |                                                                                     |
|------------------------|-------------|--------------|---------|-----------|-----|------------|---------|--------------------------------------------------------------------------------------------|---------------------|------------------|-------------------------------------------------------------------------------------|------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SKU                    | Description | Quality Tier | Color   | Refill ID | Ply | Fold       | Emboss  | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)             | Napkins/<br>Package | Napkins/<br>Case |  | Recycled Content |  |  |
| D820                   | Soft        | Advanced     | White   | N6        | 1   | Minifold   | Luxri   | <sup>A</sup> 13 x 12<br>(33.02 x 30.48 cm)<br><sup>B</sup> 6.5 x 3.75<br>(16.51 x 9.53 cm) | 500                 | 6,000            | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |
| D826E                  | Soft        | Advanced     | Natural | N6        | 1   | Minifold   | Luxri   | <sup>A</sup> 13 x 12<br>(33.02 x 30.48 cm)<br><sup>B</sup> 6.5 x 3.75<br>(16.51 x 9.53 cm) | 500                 | 6,000            | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |
| D802A                  | Soft        | Advanced     | White   | N7        | 1   | Masterfold | Luxri   | <sup>A</sup> 12 x 17<br>(30.48 x 43.18 cm)<br><sup>B</sup> 5 x 6.5<br>(12.70 x 16.51 cm)   | 500                 | 6,000            | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |
| D806E                  | Soft        | Advanced     | Natural | N7        | 1   | Masterfold | Luxri   | <sup>A</sup> 12 x 17<br>(30.48 x 43.18 cm)<br><sup>B</sup> 5 x 6.5<br>(12.70 x 16.51 cm)   | 500                 | 6,000            | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |
| D780                   |             | Universal    | White   | N7        | 1   | Masterfold | Overall | <sup>A</sup> 13 x 12<br>(33.02 x 30.48 cm)<br><sup>B</sup> 5 x 6.5<br>(12.70 x 16.51 cm)   | 500                 | 6,000            | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |
| D786E                  |             | Universal    | Natural | N7        | 1   | Masterfold | Overall | <sup>A</sup> 13 x 12<br>(33.02 x 30.48 cm)<br><sup>B</sup> 5 x 6.5<br>(12.70 x 16.51 cm)   | 500                 | 6,000            | Recycled                                                                            | 100%,<br>EPA CPG | ●                                                                                   | ●                                                                                   |



## Tork Dinner Napkins



- Impress your restaurant patrons with the exceptional quality and elegance of Premium LinStyle® cloth-like disposable napkins
- Advanced dinner napkins bring class and practicality to casual dining; economical for high-volume applications
- Exclusive taller styling options allow silverware to rest on it with little or no overhang
- Options available for custom print
- Poly or bag packing to keep napkins protected

| Tork Dinner Napkins |             |              |       |     |      |              |                                                                                           |                     |                  |                 |                                                                                     |                     |                                                                                     |
|---------------------|-------------|--------------|-------|-----|------|--------------|-------------------------------------------------------------------------------------------|---------------------|------------------|-----------------|-------------------------------------------------------------------------------------|---------------------|-------------------------------------------------------------------------------------|
| SKU                 | Description | Quality Tier | Color | Ply | Fold | Emboss       | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)            | Napkins/<br>Package | Napkins/<br>Case | Custom<br>print |  | Recycled<br>Content |  |
| 718045              | LinStyle    | Premium      | White | 1   | 1/8  | Linen        | <sup>A</sup> 16.25 x 17 (41.28 x 43.18 cm)<br><sup>B</sup> 4.25 x 8.125 (10.8 x 20.64 cm) | 80/Poly             | 480              | ●               |                                                                                     |                     |                                                                                     |
| 716002              | LinStyle    | Premium      | White | 1   | Flat | Linen        | <sup>A</sup> 15 x 16 (38.1 x 40.64 cm)<br><sup>B</sup> 15 x 16 (38.1 x 40.64 cm)          | 1,000/<br>Box       | 1,000            |                 |                                                                                     |                     |                                                                                     |
| NP7380A             | Extra Soft  | Advanced     | White | 3   | 1/8  | Rose/<br>Key | <sup>A</sup> 17 x 16.125 (43.18 x 40.96 cm)<br><sup>B</sup> 4.25 x 8 (10.8 x 20.32 cm)    | 290/Bag             | 1,740            |                 |                                                                                     | 100%,<br>EPA CPG    | ● ●                                                                                 |
| NP310A              | Soft        | Advanced     | White | 2   | 1/8  | Button       | <sup>A</sup> 15 x 16.25 (38.10 x 41.28 cm)<br><sup>B</sup> 3.75 x 8.125 (9.53 x 20.64 cm) | 375/Bag             | 3,000            | ●               | Recycled                                                                            | 100%,<br>EPA CPG    | ● ●                                                                                 |
| NP528PA             | Soft        | Advanced     | White | 2   | 1/8  | Key          | <sup>A</sup> 15 x 16.75 (38.10 x 42.54 cm)<br><sup>B</sup> 3.75 x 8.5 (9.53 x 21.59 cm)   | 100/Poly            | 2,800            |                 | Recycled                                                                            | 100%,<br>EPA CPG    | ● ●                                                                                 |
| NP5240C             | Soft        | Advanced     | White | 2   | 1/4  | Leaves       | <sup>A</sup> 15 x 16.25 (38.10 x 41.28 cm)<br><sup>B</sup> 7.5 x 8.125 (19.05 x 20.64 cm) | 375/Bag             | 3,000            |                 | Recycled                                                                            | 100%,<br>EPA CPG    | ● ●                                                                                 |

## Tork Valet Guest Towel



- Impress your guests with disposable guest towel designed with the look and feel of real cloth
- Noticeably softer and bulkier than standard guest towels
- No linen service fees, replacement fees, or laundering costs
- Available for custom print; poly packaging protects the napkins

| Tork Valet Guest Towel |             |              |       |     |      |        |                                                                                          |                     |                  |                                                                                       |
|------------------------|-------------|--------------|-------|-----|------|--------|------------------------------------------------------------------------------------------|---------------------|------------------|---------------------------------------------------------------------------------------|
| SKU                    | Description | Quality Tier | Color | Ply | Fold | Emboss | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)           | Napkins/<br>Package | Napkins/<br>Case | Custom<br>print                                                                       |
| 716001                 | LinStyle    | Premium      | White | 1   | 1/6  | Linen  | <sup>A</sup> 11.5 x 17 (29.21 x 43.18 cm)<br><sup>B</sup> 4.375 x 8.5 (11.11 x 21.59 cm) | 100/Poly            | 500              |  |

## Tork Dinner Napkins



| SKU     | Quality Tier | Color                               | Ply | Fold | Emboss  | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)            | Napkins/<br>Package | Napkins/<br>Case | Custom<br>print |  | Recycled<br>Content |                  |     |
|---------|--------------|-------------------------------------|-----|------|---------|-------------------------------------------------------------------------------------------|---------------------|------------------|-----------------|--|---------------------|------------------|-----|
| N7141A  | Universal    | White                               | 1   | 1/4  | Overall | <sup>A</sup> 17 x 17 (43.18 x 43.18 cm)<br><sup>B</sup> 8.5 x 8.5 (21.59 x 21.59 cm)      | 334/<br>Sleeve      | 4,008            |                 |  | Recycled            | 100%,<br>EPA CPG | ● ● |
| N5181A  | Universal    | White                               | 1   | 1/8  | Overall | <sup>A</sup> 15 x 17 (38.10 x 43.18 cm)<br><sup>B</sup> 3.75 x 8.5 (9.53 x 21.59 cm)      | 250/<br>Sleeve      | 3,000            |                 |  | Recycled            | 100%,<br>EPA CPG | ● ● |
| N5186   | Universal    | Natural                             | 1   | 1/8  | Overall | <sup>A</sup> 15 x 17 (38.10 x 43.18 cm)<br><sup>B</sup> 3.75 x 8.5 (9.53 x 21.59 cm)      | 250/<br>Sleeve      | 3,000            |                 |  | Recycled            | 100%,<br>EPA CPG | ● ● |
| 9935705 | Universal    | Natural with<br>Environmental Print | 2   | 1/8  | Pin     | <sup>A</sup> 16.25 x 15 (41.28 x 38.10 cm)<br><sup>B</sup> 3.75 x 8.125 (9.53 x 20.64 cm) | 126/<br>Sleeve      | 3,024            | ●               |  | Recycled            | 100%,<br>EPA CPG | ● ● |

## Tork Beverage Napkins



B1242

- Brighter, whiter look presents an upscale image
- 2-ply facial grade provides a superior look and feel compared to other beverage napkins
- Available for custom print; poly packaging protects the napkins

| SKU   | Description | Quality Tier | Color | Ply | Fold | Emboss | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)             | Napkins/<br>Package | Napkins/<br>Case |  | Recycled<br>Content |                  |     |
|-------|-------------|--------------|-------|-----|------|--------|--------------------------------------------------------------------------------------------|---------------------|------------------|--|---------------------|------------------|-----|
| B1242 | Soft        | Advanced     | White | 2   | 1/4  | Key    | <sup>A</sup> 9.25 x 9.25 (23.5 x 23.5 cm)<br><sup>B</sup> 4.625 x 4.625 (11.75 x 11.75 cm) | 150/Poly            | 6,000            |  | Recycled            | 100%,<br>EPA CPG | ● ● |



B1141A

| SKU    | Quality Tier | Color | Ply | Fold | Emboss  | <sup>A</sup> Open Napkin Size<br><sup>B</sup> Folded Napkin Size<br>W x L (in)               | Napkins/<br>Package | Napkins/<br>Case |  | Recycled<br>Content |                  |     |
|--------|--------------|-------|-----|------|---------|----------------------------------------------------------------------------------------------|---------------------|------------------|--|---------------------|------------------|-----|
| B1141A | Universal    | White | 1   | 1/4  | Overall | <sup>A</sup> 9.375 x 9.375 (23.81 x 23.81 cm)<br><sup>B</sup> 4.68 x 4.68 (11.89 x 11.89 cm) | 500/Poly            | 4,000            |  | Recycled            | 100%,<br>EPA CPG | ● ● |

## Index

|               |    |               |    |               |    |               |    |
|---------------|----|---------------|----|---------------|----|---------------|----|
| 55TR .....    | 32 | 192481 .....  | 46 | 401815 .....  | 26 | 520337 .....  | 45 |
| 56TR .....    | 34 | 192483 .....  | 46 | 420580 .....  | 20 | 520350 .....  | 45 |
| 59TR .....    | 32 | 192593 .....  | 46 | 420590 .....  | 20 | 520374 .....  | 45 |
| 66TR .....    | 34 | 192815 .....  | 49 | 424824 .....  | 20 | 520681 .....  | 45 |
| 73TR .....    | 21 | 192816 .....  | 51 | 424834 .....  | 20 | 530105 .....  | 44 |
| 83TR .....    | 18 | 192820 .....  | 51 | 424835 .....  | 20 | 530137 .....  | 44 |
| 84TR .....    | 18 | 192821 .....  | 51 | 430150A ..... | 39 | 530182 .....  | 44 |
| 86ECO .....   | 18 | 192830 .....  | 51 | 430151 .....  | 39 | 552501 .....  | 11 |
| 93T .....     | 54 | 192840 .....  | 50 | 430304 .....  | 39 | 552503 .....  | 11 |
| 908EX .....   | 59 | 192841 .....  | 50 | 440245A ..... | 39 | 552505 .....  | 11 |
| 72900 .....   | 57 | 192850 .....  | 50 | 440278 .....  | 39 | 552520 .....  | 11 |
| 73350 .....   | 57 | 192851 .....  | 51 | 450137 .....  | 42 | 552521 .....  | 11 |
| 100230 .....  | 52 | 192852 .....  | 51 | 450138 .....  | 42 | 552522 .....  | 11 |
| 101293 .....  | 20 | 192853 .....  | 51 | 450175 .....  | 39 | 552528 .....  | 11 |
| 101298 .....  | 20 | 207328 .....  | 38 | 450304 .....  | 39 | 552530 .....  | 11 |
| 101990 .....  | 59 | 214405 .....  | 18 | 450337 .....  | 42 | 552538 .....  | 11 |
| 105065 .....  | 11 | 240123 .....  | 32 | 450338 .....  | 42 | 552540 .....  | 11 |
| 105066 .....  | 11 | 240150 .....  | 32 | 450340 .....  | 42 | 552548 .....  | 11 |
| 106390 .....  | 30 | 240616 .....  | 32 | 450360 .....  | 42 | 553020 .....  | 20 |
| 110292A ..... | 31 | 247549A ..... | 33 | 450361 .....  | 42 | 553028 .....  | 20 |
| 112990 .....  | 30 | 256020 .....  | 23 | 461002 .....  | 13 | 553120 .....  | 20 |
| 119906 .....  | 59 | 256021 .....  | 23 | 461022 .....  | 13 | 553128 .....  | 20 |
| 120133 .....  | 53 | 256023 .....  | 23 | 461023 .....  | 13 | 554020A ..... | 33 |
| 120932 .....  | 53 | 257020 .....  | 23 | 461202 .....  | 13 | 554028A ..... | 33 |
| 121201 .....  | 53 | 257021 .....  | 23 | 461222 .....  | 13 | 555020A ..... | 33 |
| 121202 .....  | 53 | 257022 .....  | 23 | 461223 .....  | 13 | 555028A ..... | 33 |
| 121204 .....  | 53 | 290088 .....  | 14 | 463002 .....  | 20 | 555123 .....  | 21 |
| 121211 .....  | 53 | 290089 .....  | 14 | 465500 .....  | 33 | 555620 .....  | 31 |
| 121225 .....  | 53 | 290092A ..... | 14 | 466000 .....  | 25 | 555628 .....  | 31 |
| 130211B ..... | 40 | 290094 .....  | 14 | 466100 .....  | 25 | 558028A ..... | 52 |
| 130251A ..... | 40 | 290095 .....  | 14 | 472880 .....  | 29 | 558060 .....  | 29 |
| 130251A ..... | 52 | 290096 .....  | 14 | 472881 .....  | 29 | 558068 .....  | 29 |
| 132451A ..... | 39 | 291350 .....  | 41 | 472882 .....  | 29 | 559020A ..... | 52 |
| 160090 .....  | 30 | 291370 .....  | 41 | 472884 .....  | 29 | 559028A ..... | 52 |
| 161990 .....  | 30 | 291380 .....  | 41 | 472885 .....  | 29 | 565528 .....  | 30 |
| 162090 .....  | 30 | 302020 .....  | 20 | 472887 .....  | 29 | 565728 .....  | 30 |
| 192122 .....  | 42 | 302028 .....  | 20 | 472889 .....  | 29 | 565828 .....  | 30 |
| 192125A ..... | 40 | 302030 .....  | 20 | 473020 .....  | 29 | 570010 .....  | 25 |
| 192126 .....  | 40 | 303362 .....  | 40 | 473030 .....  | 29 | 570018 .....  | 25 |
| 192127 .....  | 39 | 309051 .....  | 14 | 473040 .....  | 29 | 570078 .....  | 25 |
| 192128 .....  | 39 | 309695 .....  | 21 | 473060 .....  | 29 | 570088 .....  | 25 |
| 192136 .....  | 39 | 309696 .....  | 21 | 473070 .....  | 31 | 570090 .....  | 25 |
| 192181A ..... | 49 | 309697 .....  | 21 | 473080 .....  | 29 | 570098 .....  | 25 |
| 192183 .....  | 49 | 351000 .....  | 11 | 473430 .....  | 29 | 570100 .....  | 27 |
| 192185 .....  | 49 | 351000 .....  | 13 | 473520 .....  | 29 | 570105 .....  | 44 |
| 192187 .....  | 49 | 400020 .....  | 26 | 473528 .....  | 29 | 570137 .....  | 44 |
| 192191 .....  | 49 | 400022 .....  | 26 | 473620 .....  | 29 | 570481 .....  | 44 |
| 192192 .....  | 49 | 400031 .....  | 26 | 473628 .....  | 29 | 571600 .....  | 25 |
| 192193 .....  | 49 | 400032 .....  | 26 | 500105 .....  | 45 | 571608 .....  | 25 |
| 192194 .....  | 49 | 400033 .....  | 26 | 500176 .....  | 45 | 571718 .....  | 27 |
| 192197 .....  | 49 | 400039 .....  | 27 | 500700 .....  | 60 | 571719 .....  | 27 |
| 192291 .....  | 49 | 400217 .....  | 26 | 506700 .....  | 60 | 580100 .....  | 25 |
| 192292 .....  | 49 | 401800 .....  | 26 | 510105 .....  | 45 | 580180 .....  | 25 |
| 192293 .....  | 49 | 401804 .....  | 26 | 510137 .....  | 45 | 581500 .....  | 25 |
| 192475 .....  | 46 | 401811 .....  | 26 | 510176 .....  | 45 | 581508 .....  | 25 |
| 192480 .....  | 46 | 401813 .....  | 26 | 520305 .....  | 45 | 651220 .....  | 41 |

|               |    |                |    |              |    |
|---------------|----|----------------|----|--------------|----|
| 651228 .....  | 41 | 6521281 .....  | 38 | NP310A ..... | 62 |
| 653020 .....  | 38 | 6532000 .....  | 58 | NP528PA .... | 62 |
| 653028 .....  | 38 | 6540281 .....  | 38 | NP5240C .... | 62 |
| 654021 .....  | 38 | 6830100 .....  | 35 | NP7380A .... | 62 |
| 655300 .....  | 38 | 6910101 .....  | 35 | RB800 .....  | 18 |
| 655300 .....  | 49 | 6920101 .....  | 35 | RB8002 ..... | 18 |
| 659020 .....  | 38 | 7170630 .....  | 16 | RB10002 .... | 18 |
| 659028 .....  | 38 | 7171020 .....  | 16 | RC530 .....  | 54 |
| 670058 .....  | 25 | 7171050 .....  | 16 | RK800E ..... | 18 |
| 716001 .....  | 62 | 7171300 .....  | 16 | RK8002 ..... | 18 |
| 716002 .....  | 62 | 7171400 .....  | 16 | TC0020 ..... | 34 |
| 718045 .....  | 62 | 7171600 .....  | 16 | TF6710A .... | 35 |
| 771728 .....  | 16 | 7178050 .....  | 16 | TF6810 ..... | 35 |
| 771828 .....  | 15 | 7232000 .....  | 60 | TJ0922A .... | 34 |
| 772728 .....  | 16 | 7432000 .....  | 60 | TM1601A .... | 32 |
| 772828 .....  | 15 | 7674550 .....  | 17 | TM1616S .... | 32 |
| 800200 .....  | 47 | 8030630 .....  | 15 | TM6130S .... | 32 |
| 800700 .....  | 60 | 8031000 .....  | 15 |              |    |
| 806700 .....  | 60 | 8031050 .....  | 15 |              |    |
| 930151 .....  | 44 | 8031300 .....  | 15 |              |    |
| 930181 .....  | 44 | 8031400 .....  | 15 |              |    |
| 1102910 ..... | 32 | 8031500 .....  | 15 |              |    |
| 1951001 ..... | 34 | 8031600 .....  | 15 |              |    |
| 2083281 ..... | 38 | 8031900 .....  | 15 |              |    |
| 2225001 ..... | 42 | 8038050 .....  | 15 |              |    |
| 2234003 ..... | 42 | 8620100 .....  | 17 |              |    |
| 2247020 ..... | 42 | 8621400 .....  | 17 |              |    |
| 2461200 ..... | 32 | 8631060 .....  | 17 |              |    |
| 2465100 ..... | 32 | 8634550 .....  | 17 |              |    |
| 2465110 ..... | 32 | 9935705 .....  | 63 |              |    |
| 2465120 ..... | 32 | 11020602 ..... | 33 |              |    |
| 3096020 ..... | 14 | 12013903 ..... | 33 |              |    |
| 3096040 ..... | 14 | 12021502 ..... | 33 |              |    |
| 3106220 ..... | 14 | 12024402 ..... | 33 |              |    |
| 3106440 ..... | 14 | 13244101 ..... | 39 |              |    |
| 5301505 ..... | 44 | 13247501 ..... | 39 |              |    |
| 5301755 ..... | 44 | B1141A .....   | 63 |              |    |
| 5510202 ..... | 13 | B1242 .....    | 63 |              |    |
| 5510282 ..... | 13 | D780 .....     | 61 |              |    |
| 5511204 ..... | 13 | D786E .....    | 61 |              |    |
| 5511284 ..... | 13 | D802A .....    | 61 |              |    |
| 5555200 ..... | 33 | D806E .....    | 61 |              |    |
| 5555290 ..... | 33 | D820 .....     | 61 |              |    |
| 6032050 ..... | 57 | D826E .....    | 61 |              |    |
| 6032120 ..... | 57 | DX900 .....    | 59 |              |    |
| 6032200 ..... | 57 | DX906E .....   | 59 |              |    |
| 6232100 ..... | 57 | HB1990A ....   | 54 |              |    |
| 6234100 ..... | 57 | HB1995A ....   | 54 |              |    |
| 6236100 ..... | 57 | HB9201 .....   | 54 |              |    |
| 6332000 ..... | 57 | MB540A .....   | 21 |              |    |
| 6334000 ..... | 57 | MB579 .....    | 20 |              |    |
| 6336000 ..... | 57 | MK520A .....   | 21 |              |    |
| 6432000 ..... | 57 | MK530A .....   | 21 |              |    |
| 6434000 ..... | 57 | N5181A .....   | 63 |              |    |
| 6436000 ..... | 57 | N5186 .....    | 63 |              |    |
| 6520281 ..... | 38 | N7141A .....   | 63 |              |    |



## How else can we help? Get in touch to talk about your business.

torkglobal.com/us/en  
1 866 722 8675  
torkusa@essity.com



Scan the code  
for the online version.  
Fewer printed copies =  
less environmental impact

Tork is a global brand of Essity,  
a leading hygiene and health company.  
More information at [www.essity.com](http://www.essity.com).

